

Combination Devices, Residential Grade, Decorator Series, 1) Three Way Pole Rocker, 1) Tamper Resistant Single Receptacle, 15A 120V AC

By Hubbell Wiring Device-Kellems
Catalog # [RCD308WTR](#)



Switches and Lighting Controls, Combination Devices, Residential Grade, Decorator Series, 1) Three Way Pole Rocker, 1) Tamper Resistant Single Receptacle, 15A 120V AC, Side

Application

- Residential

Performance

- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
- Electrical - Endurance - 30,000 cycles minimum
- Electrical - Max. working voltage - 120V
- Electrical - Overload - 1.5 times rating
- Environmental - Flammability - UL V0
- Environmental - Operating temperatures - Maximum continuous 60°C
- minimum -20°C (without impact)
- Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only
- push wire: #14 AWG solid copper wire only

General

| | |
|------------------------------|---|
| Action | Snap Switch |
| Actuator | Rocker |
| Catalog Number | RCD308WTR |
| Contact Configuration | Two Position |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Item Type | Decorator Switch and Receptacle Combo Devices |
| Material - Mounting Hardware | Mounting Screws |
| Number Of Poles | 1) Three Way |
| Operating Cycles | 30,000 Minimum |
| Operating Temperature | Max Continuous- 60 Degrees C, Minimum- -20 Without Impact |

Specifications

- Base and body - PVC
 - Mounting strap - Galvanized steel
 - Rocker - Polycarbonate
 - Terminal screws - Steel
 - Terminals - Brass
- UPC
883778302442

Dimensions

Display Size Standard Size

Electrical Ratings

| | |
|----------------------------|------------|
| Amperage Rating | 15 A |
| Connectivity | Side Wired |
| Contact Rating | 15A |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Voltage Rating | 125 VAC |
| Voltage Rating Description | 125 VAC |
| Wattage | 1875 |

Certifications And Compliance

| | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none">CSA CertifiedUL Listed E3896 |
|----------------------|---|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Residential Catalog](#)
[Specifications - RCD308WTR](#)
[Warranty - tradeSELECT™ and netSELECT®](#)