



Straight Blade Devices, Receptacles, Style Line Decorator, SNAPConnect, Hospital Grade, Isolated Ground, LED Indicator, 15A 125V, 5-15R

By Hubbell Wiring Device-Kellems
Catalog # [SNAP2172IGL](#)



Straight Blade Devices, Receptacles, Style Line Decorator,
SNAPConnect, Hospital Grade, Isolated Ground, LED Indicator,
15A 125V, 2-Pole 3- Wire Grounding, 5-15R, Nylon, Orange

Features

- Audible SNAP, indicates solid connection
- Reduces installation time
- Isolated Ground, LED Indicator

Application

Hospital Grade

General

Color	Orange
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Indicator(s) Type	Green LED
Item Type	Style Line Decorator
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical: Current Interrupting- Certified for current interrupting at full rated current • Electrical: Dielectric Voltage- Withstands 2,000V minimum • Mechanical: Product Identification Ratings are a permanent part of the device • Environmental: Flammability- UL 94V-2 • Environmental: Operating Temperature- Maximum continuous 75°C • minimum -40°C (w/o impact)
Series	Hospital Grade
Style	Style Line Decorator

Dimensions

Dimensions	3.28 in x 1.64 in x 1.1 in
Display Size	Standard Sized Product
Height	1.1 in
Length	3.28 in
Weight	0.2 lb
Width	1.64 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Connectorized
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Conductors	3-Wire Grounding
Number Of Wires	3-Wire
Wire Size	#12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	---

Nema Rating 5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023 Literature - Electrical Products - Healthcare Solutions \(EP-WDK-HC-SALES-AID-BR-EN-2023-00894\)](#)

Type
UPC

Power Indicating LED
783585249315

Warranty - Industrial & Commercial Products



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-SNAP2172IGL-SPEC-EN | REV 1/2024