



NEMA 4 JIC Continuous Hinge Qurater Turn 12X12X10 Carbon Steel - Gray

By Wiegmann
Catalog # [BN4121210CHQT](#)

NEMA 4 JIC Continuous Hinge Qurater Turn 12X12X10 Carbon
Steel - Gray.



*Representative Image

Features

- New 1/4 turn style JIC enclosure makes for easy door seal
- Eliminates the need for exterior clips to secure door shut
- 1/4 turn latch is interchangeable with many locking designs available to better suit the customer
- FTC flange around the entire door opening to channel liquids away
- ANSI 61 gray powder coat finish

Application

Ultimate Mini-Max™ Series enclosures are designed to house and protect electrical and electronic components from harsh, dirty environments. For use in installations where dirt, dust, oil, water and other contaminants are present. Streamlined styling, 1/4 turn latch and attractive durable finish compliment any high tech electronic equipment.

General

Color	Gray
Cover Type	Hinged Cover
Finish Type	Polyester Powder
Latches Type	1/4 Turn
Material	Carbon Steel
Mounting Type	External Mounting Plates
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725880317

Dimensions

Depth	10 in
Height	12 in
Weight	19 lb
Width	12 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	NEMA 4;NEMA 12
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[3D Models - BN4121210CHQT](#)
[Brochures - Ultimate Mini-Max™ JIC Box 1/4 Turn Style](#)
[Brochures - Modify Enclosures and Panels in 3-5 days](#)
[Catalogs - Wiegmann NEMA 4 Enclosures](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - MOD Center Drawings Instructions](#)
[Engineering Drawing - BN4121210CHQT-MOD](#)
[Engineering Drawing - HWDBN4121210CHQT-S](#)
[Sales Drawings - BN4121210CHQT-S](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)

Related Products

[Back Panel \(JIC B Series\) 10.8 X 10.8, Carbon Steel - White](#)
[Back Panel \(JIC B Series\) 10.8 X 10.8, Carbon Steel - Galvanized](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-BN4121210CHQT-SPEC-EN | REV 1/2024