



**TradeSelect, Straight Blade, Single
Panel Mount Receptacle, 50A
125/250V, 3-Pole 4-Wire
Grounding, 14-50R, Black, With
Plate**

By Hubbell Wiring Device-Kellems
Catalog # [RR450WIPCN](#)



TradeSelect, Straight Blade, Single Panel Mount Receptacle,
50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Black, With
Plate

Application

Residential Grade

General

Color	<ul style="list-style-type: none">• White• Noir
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Flanged Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Wiring Device- Kellems
UPC	883778301865

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	50 A
Connectivity	Screw Terminals
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125/250 VAC
Wattage	12500

Conductor Related

Number Of Wires	4-Wire Grounding
Wire Size	#10 AWG Min #6 AWG Max

Certifications and Compliance

Nema Rating	14-50R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Engineering Drawing - RR450WIPCN AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2193_INSTALLINST](#)
[Sales Drawings - WDK_RR450WIPCN_DRAWING_PDF](#)
[Warranty - tradeSELECT™ and netSELECT®](#)

Related Products

[RR450 - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Surface Mount, Black](#)
[RR430PM - TradeSelect, Straight Blade, Single Panel Mount Receptacle, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Black](#)
[RR430F - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 30A 125/250V, 3-Pole 4-Wire Grounding, 14-30R, Flush Mount, Black](#)
[RR435P - TradeSelect, Straight Blade Devices, Residential Grade, Male Plug, 30A 125/250V, 3-Pole 3-Wire Non-Grounding, 14-30P, Polarized](#)
[RR450PM - TradeSelect, Straight Blade, Single Panel Mount Receptacle, 50A 125/250V, 3-Pole 4-Wire Grounding, 14-50R, Black](#)



A proud member of the Hubbell Family.

