

## Floor Boxes

### SystemOne ETERNAL™ Series Concrete Floorboxes

#### 4/5-Gang Recessed

# HUBBELL

#### Features

- 3.75" deep wiring chambers for large AV modules and feed-thru capacity
- External High Capacity Feed-Thru Hubs Sold Separately
- Stamped steel construction, exterior coated with fusion bonded epoxy paint for on grade use, ships with Flush Installation Cover & 1/2" Prepour Cover
- Pre and post pour adjustment
- Round cover, patented labor saving easy mount device plates

#### Ordering Information

Cover Style	Box Type	UPC	Catalog Number
Round	On/ Above Grade	783585695426	CFB45G55RCRE

#### Listings

cULus Listed  
UL 514A Listed

#### Specifications

Box Material	16 gauge galvanized steel
Box Finish	Gray corrosion resistant epoxy paint
Top Mounting Plates	16 gauge galvanized steel
Concrete Cover	16 gauge galvanized steel
Device Chamber Grounding	6" Long #12 AWG Solid Copper Wire
Wiring Chamber Depth	3.75"
Wiring Chamber Volumes	(2) Small 35 IN <sup>3</sup> [574 CM <sup>3</sup> ], (2) Med 69.5 IN <sup>3</sup> [1139 CM <sup>3</sup> ], (2) Large 99 IN <sup>3</sup> [1622 CM <sup>3</sup> ]

#### Performance

##### Mechanical

Depth of Pour, Minimum	6.25" (158.8)
Depth of Pour, Recommended	6.25" (158.8)
Floor Box Cover Series	CFBS1R8xx
Floor Box Height	6.31" [160.2mm]
Floor Box Length	14.14" [359.2mm]
Floor Box Width	11.09" [281.6mm]
Trade Size Knock-Outs: Bottom	(2) ½", ¾", 1", 1¼"
Trade Size Knock-Outs: Ends	(2) ¾", 1", 1¼", 2" (Field installed CFBHUB2 for 2" metallic conduit, CFBHUB200PVC for 2" PVC conduit or CFBHUB125PVC for 1¼" PVC conduit)
Trade Size Knock-Outs: Sides	(2) ¾", 1", 1¼", 2" (Field installed CFBHUB2 for 2" metallic conduit, CFBHUB200PVC for 2" PVC conduit or CFBHUB125PVC for 1¼" PVC conduit)



#### Related Products

(2) 2" PVC field installed hubs, ships with (2) 1-1/2" reducer, (2) 1-1/4" reducers, and (2) 1" reducers/plugs	CFBHUB200PVC
(2) 1-1/4" PVC field installed hubs, ships with (2) 1" reducers, (2) 3/4" reducers, AND (2) 1/2" reducer/plugs	CFBHUB125PVC
2" threaded zinc hub	CFBHUB2
3/4" Prepour stackable ring extensions	CFB8RCVRR075
(1) StyleLine Decorator Opening	FB10MPREC

#### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

