
Z-Wave In-wall Tamper Resistant Smart Outlet





Specifications

Power: 120VAC, 60Hz Signal Frequency: 908.4/916 Maximum Load for the Z-wave Controlled Outlet: 960W Incandescent,1/2 HP Motor 1800W Resistive

Range: Up to 150 feet from controller or closest Z-Wave device

Operating Temperature: 32-104° F (0-40° C) **Warranty:** 2-year limited product warranty

For indoor use only.

Design Features

- Turn the connected device On/Off manually or via Z-Wave remote control
- Remotely monitor with any mobile device*
- One Z-Wave remote controlled AC outlet (bottom outlet)
- · Remote ON/OFF control via the Z-Wave controller/network
- · Manual ON/OFF control with the front button
- · One Always-ON pass through AC outlet (top outlet)
- · Blue LED indicates ON/OFF status (supports advanced configuration for LED status)
- · Z-Wave Plus certified
- · White color

Z-Wave Plus Features

- Works with Z-Wave Classic and Z-Wave Plus Products
- · 50% more wireless range
- · 250% faster processor
- · 400% more memory
- \cdot 50% more energy efficient
- Supports wireless upgrades to future-proof your home

* Requires Z-Wave hub or controller, functions may vary depending on brand.



IDEVZ08W PRODUCT SPECIFICATIONS



Two Outlets

Contains one grounded Z-Wave AC outlet and one standard grounded AC outlet.



Tamper Resistant

Prevents objects being forcibly inserted into a single slot.

- Improves child safety
- Prevents injuries associated with electrical receptacles
- Meets National Electric Code (NEC) requirements
- UL approved

Device Configuration

Adding your device to a Z-Wave network

Once the hub is ready to add your smart dimmer, press and release the top or bottom button on the smart dimmer to add it in the network.

To remove and reset the device

Once the controller is ready to remove your device, press and release the top button on the smart dimmer to remove it from the network.

S2 + SmartStart install

The controller's app will indicate if it has discovered the device. If prompted by the controller to enter the S2 security code, refer to the QR code/security number on the side of the box, or the QR code label on the product. Enter the 5-digit code.



To return to factory defaults

Quickly press the ON button 3 times, then press the OFF button 3 times. The LED will flash ON/OFF 5 times when completed successfully.

Certifications & Compliances







Compliances, specifications and availability are subject to change without notice.

DISTRIBUTED BY WIRING DEVICES-KELLEMS HUBBELL INCORPORATED (DELAWARE) SHELTON, CT 06484

©Hubbell | IDEVZ08W | 2021 v1.1

Related Products - iDevices® Z-Wave Products



IDEVZ05DW In-Wall Smart Dimmer



IDEVZ01DW In-Wall Smart Switch



IDEVZ03DW Add-On Switch

