



WEEB-BNDJMP8.0, WEEB® Bonding Jumper, 6", M8 or 5/16" hardware NOT included

By WILEY

Catalog # [WEEB-BNDJMP8.0](#)

WEEB® Bonding Jumper.

Features

- UL 467 Listed, UL 2703 Listed
- Corrosion resistant, reliability for use throughout the lifetime of the PV system
- Equivalent to #6 AWG copper wire
- Available with or without WEEB washer technology, assembled or unassembled, with or without hardware
- In-stock standard lengths from 6" to 36", custom lengths available upon request

Application

WEEB Bond Jumpers are constructed of corrosion resistant, tin-plated braided copper. They offer an excellent solution to maintain electrical continuity over long spans or air gaps between metal structures. The WEEB washer's patented teeth pierce through most non-conductive coatings and imbed into the underlying metal component that it is installed on to and is both UL 467 and UL 270 listed. They are available with a variety of mounting hole sizes and in three standard lengths. Adding flexibility to both the installation process and application requirements, custom lengths and mounting configurations are available upon request.

General

Catalog Number	WEEB-BNDJMP8.0
Item Type	3B
UPC	781810537398
UPC 14 Digit GTIN	00781810537398

Dimensions

Bolt Size	5/16 in
-----------	---------



Dimension - Thread Size	-
-------------------------	---

Certifications And Compliance

Certification - CSA Approved	N
Certification - ETL	Y
Certification - UL Recognized	N
Certification - cULus	N
Certified Listed	UL2703
Industry Standard(s)	UL2703
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	400
Pallet Quantity	2000

Product Assets

[Brochures - WEEB Washer Guide and WEEB Washer Theory](#)
[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13](#)
[Certifications - Certificate of Compliance, UL 2703](#)
[Certifications - UL Certificate of Compliance, UL 2703](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50002064](#)
[Specifications - WEEBBNDJMP80 Specification Sheet English](#)
[Specifications - WEEB-BNDJMP8.0 Specification Sheet French](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WLY_CA-WEEBBNDJMP80-SPEC-EN | REV 4/2025