



## 5" Direct Ceiling Mount Cylinder

# 1102

One 75W BR30 or PAR30 Lamp  
120V

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

FIRM NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

## LiteForms™

For conversion to millimeters,  
multiply inches by 25.4  
Not to Scale

### APPLICATIONS:

The 1102 is a 5" ceiling mount cylinder that is properly scaled for use with PAR30/BR30 lamp source. The 1102 is suitable for a wide variety of commercial, retail and institutional applications.

### HOUSING:

.052" thick seamless extruded aluminum cylinder with durable powder coat paint finish. Specify: brushed aluminum, matte black, bronze, matte white or Prescolite's exclusive Zet, metallic silver.

### REFLECTOR:

Black interior, one-piece milligroove black baffle, black cone, or clear Alzak reflector.

### LAMP:

One (1) 75W PAR30 or BR30 lamp. Lamp furnished by others.

### SOCKET:


Porcelain socket with nickel plated screw shell.

### INSTALLATION:

Easy installation onto standard J-Box.

### LABELS:

UL, CSA listed for damp locations  
Meets insulated ceiling requirements  
Supply wiring: 60°C.



CATALOG NUMBER:

EXAMPLE: 1102-966BZ

HOUSINGS	FINISH OPTIONS	
<input type="checkbox"/> <b>1102</b> 5" Direct ceiling mount cylinder with painted black interior. One 75W PAR30 or BR30	<input type="checkbox"/> <b>BA</b> Brushed aluminum	<b>Special Reflector Finishes:</b> Refer to specification sheet LFO-INC-037 for reflector capabilities
<input type="checkbox"/> <b>1102-910</b> 5" Direct ceiling mount cylinder with black milligroove baffle. One 75W PAR30 or BR30	<input type="checkbox"/> <b>BL</b> Matte black	
<input type="checkbox"/> <b>1102-860</b> 5" Direct ceiling mount cylinder with black cone. One 75W PAR30 or BR30	<input type="checkbox"/> <b>BZ</b> Bronze	
<input type="checkbox"/> <b>1102-966</b> 5" Direct ceiling mount cylinder with clear Alzak reflector. One 75W PAR30 or BR30	<input type="checkbox"/> <b>WH</b> Matte White	
	<input type="checkbox"/> <b>Z</b> "Zet" metallic silver	

# PHOTOMETRIC DATA

---

## LiteForms™ - 5" Direct Ceiling Mount Cylinder 1102

### NOTES

Refer to [www.prescolite.com](http://www.prescolite.com) for additional photometric tests (IES Files).



Web: [www.prescolite.com](http://www.prescolite.com) • Tech Support: (888) 777-4832  
701 Millennium Blvd., • Greenville, SC 29607 U.S.A. • Phone (864) 678-1000

Prescolite is a division of Hubbell Lighting, Inc., with representatives' offices throughout North America

Copyright ©2008 Prescolite, All Rights Reserved • Specifications subject to change without notice. • Printed in U.S.A. • LFO-INC-003 • 9/10/08



Hubbell Lighting, Inc.