

SignosT

Architectural Elements

AKTSG

Gimbal Fixture Foundation
One 20-75W MR-16
Low Voltage Cover Glass Lamp

DATE: _____ TYPE: _____

FIRM NAME: _____

PROJECT: _____

ArchiTrak

For conversion to millimeters,
multiply inches by 25.4
Not to Scale

APPLICATIONS:

Prescolite's SignosT gimbal fixture foundation provides the perfect starting point to create your own unique style. Contemporary, colorful or highly shielded, the final design is up to you. Specify one or two SignosT architectural elements with one of three finishes to compliment your interior space.

TRACK FOUNDATION:

Diecast and extruded aluminum foundation with electronic 75W vertical mounted integral transformer. Rotates 180° both horizontally and vertically. Dimmable on solid state dimmers such as Lutron. Connector has solid copper contact bars, fixed for one or two circuit connection without modification. Baked enamel finish available in black, white, or Zet (metallic silver).

LAMP:

Use one (1) 20-75W MR-16 cover glass lamp only. Lamps furnished by others.

SOCKET:


Porcelain socket wired with 200°C wire in silicone insulator sleeve.

INSTALLATION:

Easy installation onto ArchiTrak one/two circuit trak.

LABELS:

CSA US/C Listed



CATALOG NUMBER:

EXAMPLE: AKTSGBL-SFC

TRAK FOUNDATION

ELEMENTS

AKTSG BL

AKTSG WH

AKTSG Z

Low voltage SignosT decorative gimbal fixture foundation, 20-75W MR-16 cover glass lamp



Frosted Glass Cone

- SFC** (frosted glass)
- SPFC** (pink frosted glass)
- SCFC** (cobalt blue frosted glass)
- SAFC** (amber frosted glass)

Stepped Frosted Glass Cone

- SSF** (stepped frosted glass)
- SSPF** (stepped pink frosted glass)
- SSCF** (stepped cobalt blue frosted glass)
- SSAF** (stepped amber frosted glass)

Perforated Shade

- SPS BL** (black perforated shade)
- SPS WH** (white perforated shade)
- SPS Z** (Zet metallic silver perf. shade)

Spun Metal Shade (Black & White Only)

- SMS BL** (black shade)
- SMS WH** (white shade)




A Division of Hubbell Lighting, Inc.

In a continuing effort to offer the best product possible we reserve the right to change, without notice, specifications or materials that in our opinion will not alter the function of the product.
Web: www.prescolite.com • Tech Support: (888) 777-4832

ATRK-001


Frosted Glass Cone



- SFC** (frosted glass)
- SPFC** (pink frosted glass)
- SCFC** (cobalt blue frosted glass)
- SAFC** (amber frosted glass)

Can be used alone or in combination with spun metal shade.


Stepped Frosted Glass Cone



- SSF** (stepped frosted glass)
- SSPF** (stepped pink glass)
- SSCF** (stepped cobalt blue glass)
- SSAF** (stepped amber frosted glass)


Can be specified alone or with the spun metal shade.

Perforated Shade



- SPS BL** (black perforated)
- SPS WH** (white perforated)
- SPS Z** (Zet metallic silver perforated)

Spun Metal Shade



- SMS BL** (black shade)
- SMS WH** (white shade)

Can be specified alone or with the frosted or stepped glass cone.