



# Remodel Construction

## RMN4QL-120

Line Voltage  
LED Downlight Housing  
Non-IC Rated  
120V

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

FIRM NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

**LiteBox** 4"

Aperture: 4"

Ceiling Cutout: 4½"

Maximum Ceiling Thickness: 1"

For conversion to millimeters,  
multiply inches by 25.4

Not to Scale

### APPLICATIONS

Designed for quick and easy installation into existing ceiling surfaces where insulation is not present or is spaced 3" away. The RMN4QL-120 is ideal for remodeling applications that require a small, concealed source to maintain a clean ceiling plane. Specify the RMN4QL-120 to accent items of interest in retail or hospitality spaces, and residentially in bedrooms, living rooms, foyers, and hallways.

### INSTALLATION

Integral housing flange aligns fixture flush with ceiling. Adjustable bars lock unit securely to ceiling. Does not require above ceiling access for installation.

### HOUSING

Aluminum housing accommodates ceilings ½" to 1" thick. One (1) cover provides easy access to splices.

### LABELS



CSA C/US approved for all ceiling types. Insulation, if present, must be spaced 3" away from housing. Listed for wet locations and through wiring (cable only). Facilitates California Title 24 compliance with LB4A Series LED downlights.

### LED MODULE INSTALLATION:

QuickLink LED housing easily connects to mating QuickLink connector on the LiteBox LB4A module without a screw base adapter preventing the use of low efficacy incandescent sources.

### J-BOX

Prewired galvanized steel junction box with preinstalled ground wire.



CATALOG NUMBER:

EXAMPLE: RMN4QL-120- LB4A6L30K9 WH

Order housing, reflector, and accessories separately

HOUSING	-	TRIMS	-	ACCESSORIES
<input type="checkbox"/> <b>RMN4QL-120</b> 4" Non-IC remodel housing		<input type="checkbox"/> <b>LB4A6L30K9 WH</b> 3000K, 90+ CRI		<input type="checkbox"/> <b>ICBOX</b> Recessed enclosure for IC applications. Refer to specification sheet FT-INC-005



In a continuing effort to offer the best product possible we reserve the right to change, without notice, specifications or materials that in our opinion will not alter the function of the product.  
Web: [www.prescolite.com](http://www.prescolite.com) • Tech Support: (888) 777-4832

LB-LED-008

Refer to [www.prescolite.com](http://www.prescolite.com) for photometrics.



Web: [www.prescolite.com](http://www.prescolite.com) • Tech Support: **(888) 777-4832**  
701 Millennium Boulevard • Greenville, SC 29607 U.S.A. • Phone (864) 678-1000  
Copyright ©2017 Prescolite, Inc., a division of Hubbell Lighting, Inc. All Rights Reserved  
Specifications subject to change without notice. • Printed in U.S.A. • LB-LED-008 • 07/19/17



**HUBBELL**  
Lighting, Inc.