

Weatherproof Boxes, Covers & Lighting





STANDARDS, 2020 NATIONAL ELECTRICAL CODE®

STANDARDS, 2020 NATIONAL ELECTRICAL CODE®

STANDARDS

BELL® UPC Vendor Number 050169.

Where applicable, BELL® products are engineered in accordance with the standards established by Underwriters Laboratories and the Canadian Standards Association. Dimensional data listed in this catalog is intended for general reference with broad tolerance limits.

2020 NEC®

When specifying BELL® Weatherproof boxes and covers, consult the requirements of the National Electrical Code®, Article 314.16 (B) and 406.9 (B). Article 314.16 (B) details the NEC® requirements for the maximum number of conductors allowed for a BELL® Weatherproof installation. Article 406.9 (B) provides details on the NEC® requirements for receptacles being used in wet locations.

For your convenience, we have reprinted the pertinent NEC® articles. In all cases, consult your local electrical code and inspector interpretation.

Wiring Capacity: BELL® Weatherproof Boxes and Extensions

Maximum Number of Conductors or Minimum Size Box (Article 314.16 (B)

The purpose of Section 314.16 (B) is to determine the maximum conductor count or the minimum box size required for the job. It also can be used to figure how many other conductors may be added without exceeding the Code-prescribed limit.

Most applications have determined the number of conductors. The rules of Section 314.16 (B) are used to determine the Code recognized limit, or smallest box that may be installed.

Selection of any BELL® Weatherproof box or extension for use in any electrical circuit work must take into consideration the maximum number of wires permitted in the box. Safe electrical practice demands that wires not be jammed into boxes because of the possibility of nicks, abrasions, or other damage to the insulating material, creating the potential for ground faults or short circuits.

314.16 Number of Conductors in Outlet, Device, and Junction Boxes, and Conduit Bodies. Boxes and conduit bodies shall be of an approved size to provide free space for all enclosed conductors. In no case shall the volume of the box, as calculated in 314.16(A), be less than the fill calculation as calculated in 314.16(B). The minimum volume for conduit bodies shall be as calculated in 314.16(C).

The provisions of this section shall not apply to terminal housings supplied with motors or generators.

Boxes and conduit bodies enclosing conductors 4

AWG or larger shall also comply with the provisions of 314.28. Outlet and device boxes shall also comply with 314.24.

- (A) Box Volume Calculations. The volume of a wiring enclosure (box) shall be the total volume of the assembled sections and, where used, the space provided by plaster rings, domed covers, extension rings, and so forth, that are marked with their volume or are made from boxes the dimensions of which are listed in Table 314.16(A). (1) Standard Boxes. The volumes of standard boxes that are not marked with their volume shall be as given in Table 314.16(A).
- (2) Other Boxes. Boxes 1650 cm3 (100 in.3) or less, other than those described in Table 314.16(A), and nonmetallic boxes shall be durably and legibly marked by the manufacturer with their volume. Boxes described in Table 314.16(A) that have a volume larger than is designated in the table shall be permitted to have their volume marked as required by this section.
- **(B) Box Fill Calculations.** The volumes in paragraphs 314.16(B)(1) through (B)(5), as applicable, shall be added together. No allowance shall be required for small fittings such as locknuts and bushings. Each space within a box installed with a barrier shall be calculated separately.
- (1) Conductor Fill. Each conductor that originates outside the box and terminates or is spliced within the box shall be counted once, and each conductor that passes through the box without splice or termination shall be counted once. Each loop or coil of unbroken conductor not less than twice the minimum length required for free conductors in 300.14 shall be counted twice. The conductor fill shall be calculated using Table 314.16(B). A conductor, no part of which leaves the box, shall not be counted.

Exception: An equipment grounding conductor or conductors or not over four fixture wires smaller than 14 AWG, or both, shall be permitted to be omitted from the calculations where they enter a box from a domed luminaire or similar canopy and terminate within that box.

- (2) Clamp Fill. Where one or more internal cable clamps, whether factory or field supplied, are present in the box, a single volume allowance in accordance with Table 314.16(B) shall be made based on the largest conductor present in the box. No allowance shall be required for a cable connector with its clamping mechanism outside the box.
- (3) Support Fittings Fill. Where one or more luminaire studs or hickeys are present in the box, a single volume allowance in accordance with Table

314.16(B) shall be made for each type of fitting based on the largest conductor present in the box.

- (4) Device or Equipment Fill. For each yoke or strap containing one or more devices or equipment, a double volume allowance in accordance with Table 314.16(B) shall be made for each yoke or strap based on the largest conductor connected to a device(s) or equipment supported by that yoke or strap. A device or utilization equipment wider than a single 50 mm (2 in.) device box as described in Table 314.16(A) shall have double volume allowances provided for each gang required for mounting.
- (5) Equipment Grounding Conductor Fill. Where up to four equipment grounding conductors or equipment bonding jumpers enter a box, a single volume allowance in accordance with Table 314.16(B) shall be made based on the largest equipment grounding conductor or equipment bonding jumper entering in the box. A 1/4 volume allowance shall be made for each additional equipment grounding conductor or equipment bonding jumper that enters the box, based on the largest equipment grounding conductor or equipment bonding conductor.

(C) Conduit Bodies.

- (1) General. Conduit bodies enclosing 6 AWG conductors or smaller, other than short-radius conduit bodies as described in 314.16(C)(3), shall have a cross-sectional area not less than twice the cross-sectional area of the largest conduit or tubing to which they can be attached. The maximum number of conductors permitted shall be the maximum number permitted by Table 1 of Chapter 9 for the conduit or tubing to which it is attached.
- (2) With Splices, Taps, or Devices. Only those conduit bodies that are durably and legibly marked by the manufacturer with their volume shall be permitted to contain splices, taps, or devices. The maximum number of conductors shall be calculated in accordance with 314.16(B). Conduit bodies shall be supported in a rigid and secure manner.
- (3) Short Radius Conduit Bodies. Conduit bodies such as capped elbows and service-entrance elbows that enclose conductors 6 AWG or smaller, and are only intended to enable the installation of the raceway and the contained conductors, shall not contain splices, taps, or devices and shall be of an approved size to provide free space for all conductors enclosed in the conduit body.

406.9 Receptacles in Damp or Wet Locations.

(A) Damp Locations. A receptacle installed outdoors in a location protected from the weather or in other damp locations shall have an enclosure for the receptacle that is weatherproof when the receptacle

is covered (attachment plug cap not inserted and receptacle covers closed).

An installation suitable for wet locations shall also be considered suitable for damp locations.

A receptacle shall be considered to be in a location protected from the weather where located under roofed open porches, canopies, marquees, and the like, and will not be subjected to a beating rain or water runoff. All 15- and 20-ampere, 125- and 250-volt nonlocking receptacles shall be a listed weather-resistant type.

Informational Note: The types of receptacles covered by this requirement are identified as 5-15, 5-20, 6-15, and 6-20 in ANSI/NEMA WD 6-2016, Wiring Devices — Dimensional Specifications.

(B) Wet Locations.

(1) Receptacles of 15 and 20 Amperes in a Wet Location. 15- and 20-ampere, 125- and 250-volt receptacles installed in a wet location shall have an enclosure that is weatherproof whether or not the attachment plug cap is inserted. An outlet box hood installed for this purpose shall be listed and shall be identified as "extra-duty." All 15- and 20- ampere, 125- and 250-volt nonlocking-type receptacles shall be listed weather-resistant type.

Informational Note No. 1: Requirements for extra-duty outlet box hoods are found in ANSI/UL 514D-2016, Cover Plates for Flush-Mounted Wiring Devices.

Informational Note No. 2: The types of receptacles covered by this requirement are identified as 5-15, 5-20, 6-15, and 6-20 in ANSI/NEMA WD 6-2016, Wiring Devices — Dimensional Specifications.

Exception: 15- and 20-ampere, 125- through 250volt receptacles installed in a wet location and subject to routine high-pressure spray washing shall be permitted to have an enclosure that is weatherproof when the attachment plug is removed.

(2) Other Receptacles. All other receptacles installed in a wet location shall comply with 406.9(B)(2)(a) or (B)(2)(b).

(a) A receptacle installed in a wet location, where the product intended to be plugged into it is not attended while in use, shall have an enclosure that is weatherproof with the attachment plug cap inserted or removed.

(b) A receptacle installed in a wet location where the product intended to be plugged into it will be attended while in use (e.g., portable tools) shall have an enclosure that is weatherproof when the attachment plug is removed.

(C) Bathtub and Shower Space. Receptacles shall not be installed within a zone measured 900 mm (3 ft) horizontally and 2.5 m (8 ft) vertically from the top of the bathtub rim or shower stall threshold. The identified zone is all-encompassing and shall include the space directly over the tub or shower stall.

(D) Protection for Floor Receptacles. Standpipes of floor receptacles shall allow floor-cleaning equipment to be operated without damage to receptacles.

(E) Flush Mounting with Faceplate. The enclosure for a receptacle installed in an outlet box flush-mounted in a finished surface shall be made weatherproof by

means of a weatherproof faceplate assembly that provides a watertight connection between the plate and the finished surface.

GENERAL FEATURES AND BENEFITS

BELL® Weatherproof products all offer these features and benefits:

- Rugged seamless die cast construction that will not allow entry of moisture
- Reinforced connector outlets to provide a secure mechanical installation
- State-of-the-art powder coat paint for maximum weatherability and scratch resistance
- Bilingual instructions provided with every product
- Installation hardware and ground screws included where applicable
- Shrink-wrap packaging that keeps all components together
- UPC-A barcoding to help lower transaction costs

Refer to the pages that follow for more specific information about BELL® products.

National Electric Code® and NEC® is a registered Trademark of the National Fire Protection Association.

Calculate The Minimum Size Box

Section 314-16(B) describes in detail the method of counting wires, as well as clamps, fittings, or devices (i.e., switches, receptacles, combination devices) — by establishing an equivalent conductor-value for each. These values are added together to get a total number of conductors. The minimum size box is the smallest one in cubic inch size that can accommodate that number of conductors.

Points to Remember:

- 1. No matter how many ground wires come into a box, they only count as one conductor within the box.
- 2. Any wire running unbroken through the box counts as one wire.
- 3. Each wire coming into a splice device (crimp or twist-on type) is counted as one wire.

Table 314.16(B) Volume Allowance Required per Conductor Size of Free Space Within Box

3126 01	Tiee Space	WILLIIII DUX				
Conductor	for Each Conducto					
(AWG)	<u>cm</u> ³	<u>in.</u> ³				
18	24.6	1.50				
16	28.7	1.75				
14	32.8	2.00				
12	36.9	2.25				
10	41.0	2.50				
8	49.2	3.00				
6	81.9	5.00				

- 4. Each wire coming into the box and connecting to a device counts as one wire of that size.
- Where devices are mounted in the box, the total conductor count must be increased by two for each mounting strap.

Example – BELL® Weatherproof

Supply power to a single switch with #14 conductors. Metal conduit will be used as the wire way. You must provide space for four conductors and one switch, totally a conductor count of 6. Read across the line in Table 314.16(B) for a #14 conductor. Multiply 6 times the free space within a box. For each conductor for a #14 conductor 2.00. This example requires a minimum box of 12.0 cubic inches.

HUBBELL



WEATHERPROOF BOXES, COVERS AND LIGHTING

DIE-CAST ALUMINUM EXTENSIONS AND ADAPTERS

• Use to provide additional capacity needed

• Adapters allow installer to add "take-offs"

Installation hardware, gasket, and ground

with NEMA requirements. Hubs accept all

• Closure plugs provided for two and six

Internal threads and hubs comply

for NEC box fill requirements

to new boxes/devices

PRODUCT FEATURES

screw provided

outlet styles

APPLICATIONS

APPLICATIONS

• For use in branch circuit wiring in wet, damp or dry locations

DIE-CAST ALUMINUM BOXES

 May be used as a weatherproof junction box, or as a housing for receptacles, switches and GFCI's

PRODUCT FEATURES

- Reinforced connector outlets
- Durable powder coat finish
- Eight box mounting options with detachable lugs provided
- Two closure plugs included
- Ground screw installed
- Multilingual instructions in each package
- Internal threads on hubs comply with NEMA requirements. Hubs accept all threaded fittings and threaded conduit

COMPLIANCES

- **(4)** File 195978
- NEMA 3R Rated

1-GANG







5320-0 to 5320-9 5324-0 to 5324-5

5320-1

5320-2





BELL WEATHERPROOF





5321-0 to 5321-6, 5330-0

5323-0, 5332-0 5322-0, 5331-0

5385-0 to 5387-0

CATALOG #	CUBIC IN. (CM3)	DESCR Color	IPTION OUTLETS	PKG. TYPE	STD. PKG.	BARCODE
2" Deep, w	vith Lugs – Th	ree Threade		4-1/2" X 2-3	/4"	
5320-0	18.3 (299.9)	Gray	(3) 1/2"	Shrink	20	IIIIIIII
5320-1	18.3 (299.9)	White	(3) 1/2"	Shrink	20	11111111
5320-2	18.3 (299.9)	Bronze	(3) 1/2"	Shrink	20	11111111
5320-5	18.3 (299.9)	Gray	(3) 1/2"	Carded	6	IIIIIIII
5320-6	18.3 (299.9)	White	(3) 1/2"	Carded	6	11111111
5320-7	18.3 (299.9)	Bronze	(3) 1/2"	Carded	6	IIIIIIII
5320-9	18.3 (299.9)	Gray	(3) 1/2"	Bulk	50	11111111
5324-0	18.3 (299.9)	Gray	(3) 3/4"	Shrink	20	11111111
5324-1	18.3 (299.9)	White	(3) 3/4"	Shrink	20	11111111
5324-5	18.3 (299.9)	Gray	(3) 3/4"	Carded	6	11111111
2" Deep, w	vith Lugs – Fo	our Threaded	l Outlets –	4-1/2" X 2-3/	/4"	
5321-0	18.3 (299.9)	Gray	(4) 1/2"	Shrink	20	IIIIIIII
5321-1	18.3 (299.9)	White	(4) 1/2"	Shrink	20	IIIIIIII
5321-2	18.3 (299.9)	Bronze	(4) 1/2"	Shrink	20	IIIIIIII
5321-5	18.3 (299.9)	Gray	(4) 1/2"	Carded	6	IIIIIIII
5321-6	18.3 (299.9)	White	(4) 1/2"	Carded	6	IIIIIIII
5330-0	18.3 (299.9)	Gray	(4) 3/4"	Shrink	20	IIIIIIII
	vith Lugs – Fi	ve Threaded		4-1/2" X 2-3/4		
5322-0	18.3 (299.9)	Gray	(5) 1/2"	Shrink	20	IIIIIIII
5331-0	18.3 (299.9)	Gray	(5) 3/4"	Shrink	20	IIIIIIII
5323-0	18.3 (299.9)	Gray	(5) 1/2"	Shrink	20	IIIIIIII
5332-0	18.3 (299.9)	Gray	(5) 3/4"	Shrink	20	11111111
				ets – 4-1/2" X		
5385-0	22.5 (368.7)	Gray	(3) 1/2"	Shrink	15	IIIIIIII
5386-0	22.5 (368.7)	Gray	(3) 3/4"	Shrink	15	IIIIIIII
5387-0	22.5 (368.7)	Gray	(3) 1"	Shrink	15	11111111

1-GANG



5406-0

(No ground screw provided)

1-Gang - Extension Adapte

1-Gang – Extension Adapte

CATALOG #

5406-0

5399-0

5403-0

5400-0

5400-5

5405-0

CUBIC IN.

(CM³)

9.5 (155.7)

9.5 (155.7)

11.0 (180.3)

9.5 (155.7)

9.5 (155.7)

11.0 (180.3)

1-Gang Extension - 4-1/2" X 2-3/4" X 1" Deep

Gray

Gray

Gray

- 5-1/4¹

Gray

Gray

Gray



COLOR | OUTLETS



5399-0, 5403-0 (Includes one closure plug)

- 5-1/4" X 3-1/2" X 1-1/2" Deep - Two tl

(2) 1/2"

(2) 3/4"

(6) 1/2"

(6) 1/2"

(6) 3/4"

3-1/2" X 1-1/2"

PKG. TYPE

Shrink

Shrink

Shrink

Shrink

Carded

Shrink

Deep - Six Th

5400-0 to 5400-5 5405-0

(Includes three closure plugs)

BARCODE

IIIIIIIII

11111111

11111111

IIIIIIII

IIIIIIII

STD. PKG.

25

20

20

20

6

20

readed outle

eaded outlets

threaded	fittings	and	threaded	conduit

COMPLIANCES

• **(4)** – File E195978

• NEMA 3R Rated





9,0	
P	
	9,6

5414-0, 5415-0 (Includes three closure plugs)

www.hubbell.com/bell/en

CATALOG #	CUBIC IN. (CM3)	DESCR Color	IPTION OUTLETS	PKG. TYPE	STD. PKG.	BARCODE
Swing-Arm -	- Extension Ac	lapters – 5-1/	4" X 3-1/2" X	1-1/2" Deep -	- Two Threade	d Outlets
5412-0	13.8 (226.1)	Gray	(2) 1/2"	Shrink	10	IIIIIIII
5413-0	13.8 (226.1)	Gray	(2) 3/4"	Shrink	10	IIIIIIII
Swing-Arm – Extension Adapters – 5-1/4" X 3-1/2" X 1-1/2" Deep – Six Threaded Outlets						
5414-0	12.8 (209.8)	Gray	(6) 1/2"	Shrink	10	IIIIIIII
5415-0	12.8 (209.8)	Gray	(6) 3/4"	Shrink	10	IIIIIIII

APPLICATIONS

- Used to provide additional capacity needed for NEC box fill requirements
- Allows installer to add "take-offs" to new boxes/devices

PRODUCT FEATURES

- Unique swing-arm design speeds installation. Allows the installer better visibility when lining up and threading fasteners
- Rugged die-cast construction
- Reinforced connector outlets
- Durable powder coat finish
- Installation hardware, ground screw and gasket provided
- Multilingual instructions in each package
- Internal threads and hubs comply with NEMA requirements. Hubs accept all threaded fittings and threaded conduit

COMPLIANCES

- (I) File E195978
- NEMA 3R Rated

SEE END OF SECTION (PG D36) FOR DETAILED DRAWINGS >> SEE END OF SECTION (PG D36) FOR DETAILED DRAWINGS >>





DIE-CAST ALUMINUM BOXES

DIE-CAST ALUMINUM BOX AND EXTENSION

APPLICATIONS

- For use in branch circuit wiring in wet, damp or dry locations
- May be used as a weatherproof junction box, or as a housing for receptacles, switches and GFCI's

PRODUCT FEATURES

- Reinforced connector outlets
- Durable powder coat finish
- Eight box mounting options with detachable lugs provided
- Closure plugs included
- Ground screw installed
- Multilingual instructions in each package
- Internal threads on hubs comply with NEMA requirements. Hubs accept all threaded fittings and threaded conduit

COMPLIANCES

- **(4)** File E195978
- NEMA 3R Rated

2-GANG





5333-0, 5341-0

5335-0, 5343-0





5337-1



5337-2



5337-0 to 5337-5, 5345-0

5334-0, 5342-0







5340-0, 5348-0

BELL WEATHERPROOF

5338-0, 5346-0

5388-0, 5389-0

CATALOG #	CUBIC IN. (CM3)	DESCR Color	PTION OUTLETS	PKG. TYPE	STD. PKG.	BARCODE
2" Deep, wi	th Lugs – Th	ree Threaded	d Outlets – 4	4-1/2" X 4-1/	2"	
5333-0	32.0 (524.4)	Gray	(3) 1/2"	Shrink	12	IIIIIIII
5341-0	32.0 (524.4)				12	11111111
2" Deep, wi	th Lugs – Fo	ur Threaded	Outlets – 4	-1/2" X 4-1/2	-	
5335-0	31.0 (508.0)	Gray	(4) 1/2"	Shrink	12	11111111
5343-0	31.0 (508.0)	Gray			12	11111111
2" Deep, w	ith Lugs – F	ive Threaded	Outlets - 4	-1/2" X 4-1/2	2"	
5337-0	31.0 (508.0)	Gray	(5) 1/2"	Shrink	12	11111111
5337-1	31.0 (508.0)	White	(5) 1/2"	Shrink	12	11111111
5337-5	31.0 (508.0)	Gray	(5) 1/2"	Carded	4	11111111
5345-0	31.0 (508.0)	Gray	(5) 3/4"	Shrink	12	11111111
5334-0	32.0 (524.4)	Gray	(5) 1/2"	Shrink	12	11111111
5342-0	32.0 (524.4)	Gray	(5) 3/4"		12	11111111
2" Deep, wi	th Lugs – Se	ven Threade	d Outlets –	4-1/2" X 4-1	/2"	
5340-0	30.2 (494.9)	Gray	(7) 1/2"	Shrink	12	11111111
5348-0	30.2 (494.9)	Gray	(7) 3/4"	Shrink	12	11111111
5338-0	31.0 (508.0)	Gray	(7) 1/2"	Shrink	12	11111111
5346-0	31.0 (508.0)	Gray	(7) 3/4"		12	11111111
2-5/8" Deep	o, with Lugs	Five Threa	ded Outlets	– 4-1/2" X 4	-1/2"	
5388-0	36.0 (589.9)	Gray	(5) 3/4"	Shrink	9	11111111
5389-0	36.0 (589.9)	Gray	(5) 1"	Shrink	9	IIIIIIII

2-GANG EXTENSION



5407-0

CATALOG #	CUBIC IN. (CM3)	COLOR OUTLETS		PKG. TYPE	STD. PKG.	BARCODE	
2-Gang Extension – 4-21/32" X 4-21/32" X 1-1/32" Deep							
5407-0	16.0 (262.2)	Gray	_	Shrink	10	HHHHH	

APPLICATION

• Used to provide additional capacity needed for NEC box fill requirements

PRODUCT FEATURES

- Rugged seamless construction
- Durable powder coat finish
- Installation hardware and gasket provided
- Multilingual instructions in each package

COMPLIANCES

- **(U)** File E195978
- NEMA 3R Rated

3-GANG

www.hubbell.com/bell/en

5390-0

CATALOG #	CUBIC IN. (CM3)		IPTION OUTLETS	PKG. TYPE	STD. PKG.	BARCODE
3-Gang Box – 2-5/8" Deep, with Lugs – Seven Threaded Outlets – 4-1/2" X 6-3/8"						
5390-0	55.0 (901.3)	Gray	(7) 3/4"	Boxed	1	

APPLICATIONS

- For use in branch circuit wiring in wet, damp or dry locations
- Can be used as a weatherproof junction box, or as a housing for receptacles, switches and GFCI's

PRODUCT FEATURES

- Seamless die-cast aluminum construction
- Reinforced connector outlets
- Durable powder coat finish
- Eight box mounting options with detachable lugs provided
- Four closure plugs included
- Ground screws installed
- Multilingual instructions in each package
- Internal threads and hubs comply with NEMA requirements. Hubs accept all threaded fittings and threaded conduit

COMPLIANCES

- **(4)** File E195978
- NEMA 3R Rated

SEE END OF SECTION (PG D37) FOR DETAILED DRAWINGS >> SEE END OF SECTION (PG D37) FOR DETAILED DRAWINGS >>



BELL

DIE-CAST ALUMINUM ROUND SPLICE BOXES AND EXTENSION ADAPTER

METAL 1-GANG DEVICE COVERS

APPLICATIONS

- For use in branch circuit wiring in wet, damp or dry locations
- Designed for use as a weatherproof junction box. May be used with BELL® round cluster covers and round lampholder combinations

PRODUCT FEATURES

- Rugged die-cast construction
- Reinforced connector outlets
- Durable powder coat finish
- Cast-in mounting lugs provide fast, secure installation
- Includes four closure plugs, installed ground screw and multilingual instructions

COMPLIANCES

- (4) File E195978
- NEMA 3R Rated

4" ROUND BOX



5361-0 to	5361-1
5361-7, 5372-0	

CATALOG #	CUBIC IN. (CM ³)	DESCRI Color	PTION OUTLETS	PKG. TYPE	STD. PKG.	BARCODE
4" Round S	plice Box - I	Five Threaded	d Outlets –	1-1/2" Deep		
5361-0	16.0 (262.2)	Gray	(5) 1/2"	Shrink	16	HHHHH
5361-1	16.0 (262.2)	White	(5) 1/2"	Shrink	16	IIIIIIII
5361-2	16.0 (262.2)	Bronze	(5) 1/2"	Shrink	16	IIIIIIII
5361-5	16.0 (262.2)	Gray	(5) 1/2"	Carded	6	IIIIIIII
5361-6	16.0 (262.2)	White	(5) 1/2"	Carded	6	IIIIIIII
5361-7	16.0 (262.2)	Bronze	(5) 1/2"	Carded	6	IIIIIIII
5372-0	16.0 (262.2)	Gray	(5) 3/4"	Shrink	16	IIIIIIII

5361-2

ROUND EXTENSION ADAPTERS

BELL WEATHERPROOF

APPLICATIONS

- For use with 4" round splice boxes
- Extension adapters are used to increase box capacity and allow the installer to add "take-offs" to new boxes/devices

PRODUCT FEATURES

- Rugged die-cast construction
- Reinforced connector outlets
- Durable powder coat finish
- Includes installation hardware, closure plugs, gasket and multilingual instructions

COMPLIANCES

- (UL) File E195978
- NEMA 3R Rated



5363-0

CATALOG #	CUBIC IN. (CM3)		IPTION OUTLETS	PKG. TYPE	STD. PKG.	BARCODE	
4" Round Extension Adapter – Four Threaded Outlets – 1-1/2" Deep							
5363-0	16.3 (267.1)	Grav	(4) 1/2"	Shrink	16	HHHH	

MULTICONFIGURATION COVERS



MX1050W

APPLICATIONS


 For use whenever weatherproof protection is required for an outdoor receptacle or switch

PRODUCT FEATURES

- Heavy duty die-cast metal construction
- Quick-fit keyhole mounting system allows cover installation in under a minute
- Includes gasket and mounting hardware
- Universal Fit Adapter System Technology (U-Fast) comes pre-configured for GFCI
- Durable powder coat finish
- Horizontal or vertical mount
- Lockable tab (fits up to 1/8" shackle)

COMPLIANCES


- c us File E212332
- Meets NEC® 406.9 (A) Requirements

















Horzizontal or Vertical Mount



CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
1-Gang Flip Covers					
MX1050S	Vertical/Horizontal	Gray	Shrink	20	IIIIIIII
MX1050W	Vertical/Horizontal	White	Shrink	20	IIIIIIII
MX1050Z	Vertical/Horizontal	Bronze	Shrink	20	IIIIIIII
MX1250S	Horizontal/Vertical	Gray	Shrink	20	IIIIIIII
MX1250W	Horizontal/Vertical	White	Shrink	20	IIIIIIII
MX1250Z	Horizontal/Vertical	Bronze	Shrink	20	IIIIIIII
MX1550S	Vertical/Horizontal Twist Lock Cover	Gray	Shrink	10	IIIIIIII

www.hubbell.com/bell/en

SEE END OF SECTION (PG D37) FOR DETAILED DRAWINGS >>

METAL 1-GANG DEVICE COVERS

METAL 1-GANG DEVICE COVERS

• For use whenever weatherproof protection

is required for an outdoor receptacle

• Durable powder coat finish provides

maximum weatherability and scratch-

DIF-CAST ALUMINUM RAYNTITE® COVERS

APPLICATION

 For use whenever weatherproof protection is required for an outdoor receptacle

PRODUCT FEATURES

- Rugged die-cast construction
- Durable powder coat finish provides maximum weatherability and scratch-
- Self-closing lids assure weatherproof protection when the receptacle is not in use
- Vertical mount covers are padlockable (fits up to 3/16" shackle)
- May be mounted to box or device
- Includes installation hardware, gasket and multilingual instruction

COMPLIANCES

- **(U)** File E195978
- Meets NEC® 406.9 (A) Requirements
- NEMA 3R rated



5027-0



5028-0 to 5028-6



5029-0, 5030-0



5031-0

5026-0

CATALOG # Rayntite® Ve	DESCRIPTION ertical Mount – Device Covers	COLOR	PKG. TYPE	STD. PKG.	BARCODE
5026-0	Single, 1.593" diameter	Gray	Shrink	24	IIIIIIII
5027-0	Duplex	Gray	Shrink	24	IIIIIIII
5028-0	GFCI	Gray	Shrink	24	IIIIIIII
5028-5	GFCI	Gray	Carded	6	IIIIIIII
5028-6	GFCI	White	Carded	6	IIIIIIII
5029-0	20A, 1.710" diameter	Gray	Shrink	12	IIIIIIII
5030-0	30-50A, 2.150" diameter	Gray	Shrink	12	IIIIIIII
5031-0	Single, 1.406" diameter	Gray	Shrink	12	IIIIIIII

VERTICAL FLIP COVERS



5146-0 to

5146-5



5103-0 to

5103-7

5155-0 to

5155-6



5103-1

5095-0



• Self-closing lids assure weatherproof 5103-2

protection when the receptacle is not in use

• Includes installation hardware, gasket and multilingual instructions

COMPLIANCES

APPLICATION

PRODUCT FEATURES

• Rugged metallic construction

- **(4)** File E195978
- Meets NEC® 406.9 (A) Requirements
- NEMA 3R rated



SEE END OF SECTION (PG D38) FOR DETAILED DRAWINGS >> SEE END OF SECTION (PG D38) FOR DETAILED DRAWINGS >>





METAL 1-GANG DEVICE COVERS

METAL 2-GANG DEVICE COVERS

• For use whenever weatherproof protection is required for an outdoor receptacle or switch

Heavy duty die-cast metal construction

• Includes gasket and mounting hardware

• Universal Fit Adapter System Technology

(U-Fast) comes pre-configured for GFCI

• Lockable tab (fits up to 1/8" shackle)

• Meets NEC® 406.9 (A) Requirements

• Quick-Fit keyhole mounting system allows cover installation in under a minute

APPLICATIONS

PRODUCT FEATURES

• Durable powdercoat finish

Horizontal or vertical mount

COMPLIANCES

NEMA 3R rated

• c(U) us — File E212332

APPLICATION

• For use whenever weatherproof protection is required for an outdoor receptacle

PRODUCT FEATURES

- Rugged metallic construction
- Durable powder coat finish provides maximum weatherability and scratchresistance
- Self-closing lids assure weatherproof protection when the receptacle is not in use
- Includes installation hardware, gasket and multilingual instructions

COMPLIANCES

- **(**) File E195978
- (Ū)
- Meets NEC® 406.9 (A) Requirements
- NEMA 3R rated

HORIZONTAL FLIP COVERS







5180-0 to 5180-7

7 5180-1

5180-2





5101-0 to 5101-7

5102-0







5152-0

5153-0

5712-5WRTR

CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
Device Mount					
5180-0	Duplex	Gray	Shrink	24	11111111
5180-1	Duplex	White	Shrink	24	11111111
5180-2	Duplex	Bronze	Shrink	24	11111111
5180-5	Duplex	Gray	Carded	6	11111111
5180-6	Duplex	White	Carded	6	11111111
5180-7	Duplex	Bronze	Carded	6	11111111
5101-0*	GFCI	Gray	Shrink	24	11111111
5101-1*	GFCI	White	Shrink	24	11111111
5101-2*	GFCI	Bronze	Shrink	24	11111111
5101-5*	GFCI	Gray	Carded	6	11111111
5101-6*	GFCI	White	Carded	6	11111111
5101-7*	GFCI	Bronze	Carded	6	11111111
5102-0	GFCI	Gray	Shrink	24	IIIIIIII
5152-0	Single, 1.406" diameter	Gray	Shrink	24	IIIIIIII
5153-0	Motor plug base, 1.600" diameter, 125V, 15A wiring device included	Gray	Shrink	12	IIIIIIII
5712-5WRTR*	125V, 15A WR/TR Duplex receptacle included	Gray	Carded	6	IIIIIIII

BELL WEATHERPROOF

HUBBELL

MULTICONFIGURATION COVERS







MX2050Z

MX2050WH



MX2150S

NFIGU	IKATIU	И2			
= (Included)	Duplex	GFCI			

CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
2-Gang Flip Covers					
MX2050S	2-Device 25-in-1	Gray	Shrink	6	IIIIIIII
MX2050WH	2-Device 25-in-1	White	Shrink	4	IIIIIIII
MX2050Z	2-Device 25-in-1	Bronze	Shrink	4	IIIIIIII
MX2150S	1-Device 3-in-1	Gray	Shrink	4	IIIIIIII

www.hubbell.com/bell/en

SEE END OF SECTION (PG D39) FOR DETAILED DRAWINGS >>

^{*} C/UL Listed



METAL LOCKING COVER

METAL 2-GANG DEVICE COVERS

HEAVY DUTY CAST FLUSH WEATHERPROOF

APPLICATIONS

- For use whenever weatherproof protection is required for an outdoor receptacle or switch
- Easily mounts to any 3-3/4" through 4-11/16" square box

PRODUCT FEATURES

- Heavy duty cast aluminum construction with durable enamel paint
- Cobra Cam lock, key removal in locked and unlocked positions
- 2 keys provided
- Universal Fit Adapter System Technology (U-Fast) for 4-in-1 custom device configurations, comes pre-configured for GFCI
- Irradiation crosslinked polyethylene foam gasket
- Mounting hardware included
- Adapters included for various devices

COMPLIANCES

- cUL us File E212332
- Meets NEC® 406.9 (A) Requirements
- NEMA 3R rated











CATALOG # 1-Gang Locking Cover	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
4600RAC	1-Device 4-in-1, Heavy duty, weatherproof	Gray	Boxed	1	11111111

BELL WEATHERPROOF

DIE-CAST ALUMINUM RAYNTITE® COVERS









5043-0 5045-0

• For use whenever weatherproof protection is required for an outdoor receptacle

PRODUCT FEATURES

- Rugged die-cast construction
- Durable powder coat finish provides maximum weatherability and scratch resistance
- Self-closing lids assure weatherproof protection when the receptacle is not in use
- Covers are padlockable (fits up to 3/16" shackle)
- May be mounted to box or device
- Includes installation hardware, gasket and multilingual instructions

COMPLIANCES

- (4) File E195978
- Meets NEC® 406.9 (A) Requirements
- NEMA 3R rated

CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
Rayntite® V	ertical Mount – Device Covers				
5033-0	(1) Duplex & (1) GFCI	Gray	Shrink	6	IIIIIIII
5034-0	(1) 30-50A Receptacle 2.625" diameter	Gray	Shrink	6	IIIIIIII
5036-0	(1) 30-50A Receptacle 2.156" diameter	Gray	Shrink	6	IIIIIIII
5043-0	(1) Toggle & (1) GFCI	Gray	Shrink	6	IIIIIIII
5045-0	(2) GFCI	Gray	Shrink	6	IIIIIIII

www.hubbell.com/bell/en

SEE END OF SECTION (PG D40) FOR DETAILED DRAWINGS >>> SEE END OF SECTION (PG D40) FOR DETAILED DRAWINGS >>







METAL 2-GANG DEVICE COVERS

METAL 3-GANG DEVICE COVERS

APPLICATION

 For use whenever weatherproof protection is required for an outdoor receptacle

PRODUCT FEATURES

- Rugged metallic construction
- Durable powder coat finish provides maximum weatherability and scratch resistance
- Self-closing lids assure weatherproof protection when the receptacle is not in use
- Includes installation hardware, gasket and multilingual instructions

COMPLIANCES

- c(UL) us File E195978
- **(4)** File E195978
- Meets NEC® 406.9 (A) Requirements
- NEMA 3R rated

5145-0



2-GANG FLIPCOVERS

5148-0 to 5148-5



5145-0

IIIIIIIII

5157-0

Gray

Shrink

10

CATALOG # DESCRIPTION COLOR PKG. TYPE STD. PKG. BARCODE **Device Mount** 5148-0 (2) Duplex Shrink HIIIIIII Gray 18 5148-5 HIIIIII (2) Duplex Gray Carded 5157-0 (2) Single, 1.406" dia. Gray Shrink 18 IIIIIIII **Box Mount**

BELL WEATHERPROOF

(2) GFCI

MULTICONFIGURATION COVER





DESCRIPTION


3-Device 125-in-1

CATALOG #

MX3050S

3-Gang Flip Covers







MX3050S

APPLICATIONS

• For use whenever weatherproof protection is required for an outdoor receptacle or switch

PRODUCT FEATURES

- Heavy duty die-cast metal construction
- Quick-Fit keyhole mounting system allows cover installation in under a minute
- Includes gasket and mounting hardware
- Universal Fit Adapter System Technology (U-Fast) for 125-in-1 custom device configurations, comes pre-configured for GFCI
- Durable powder coat finish
- Horizontal or vertical mount
- Lockable tab (fits up to 3/16" shackle)

COMPLIANCES

- c(UL) us File E212332
- Meets NEC® 406.9 (A) Requirements
- NEMA 3R rated

BOX MOUNT FLIP COVER

www.hubbell.com/bell/en

COLOR PKG. TYPE STD. PKG. BARCODE



5093-0

CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
3-Gang Flip	Covers				
5093-0	(3) Single, 1.406" dia.	Gray	Boxed	1	HHHH

APPLICATIONS

 For use whenever weatherproof protection is required for an outdoor receptacle

PRODUCT FEATURES

- Rugged metallic construction
- Durable powder coat finish provides maximum weatherability and scratch resistance
- Self-closing lids assure weatherproof protection when the receptacle is not in use
- Includes installation hardware, gasket and multilingual instructions

COMPLIANCES

- cUL us File E195978
- Meets NEC® 406.9 (A) Requirements
- NEMA 3R Rated

SEE END OF SECTION (PG D40) FOR DETAILED DRAWINGS >> SEE END OF SECTION (PG D40 - D41) FOR DETAILED DRAWINGS >>

METAL DEVICE COVER COMBOS AND KITS

METAL COVERS

FLIP COVER COMBOS AND COMPLETE KITS

MD1050S

APPLICATION

• Receptacle and metal cover combos for use whenever weatherproof protection is required in wet, damp, or dry location

PRODUCT FEATURES

- High quality Hubbell WRTR device included
- Heavy duty die-cast metal construction
- Includes gasket and mounting hardware
- Durable powder coat finish
- Lockable tab (see cover listings for shackle dia.)
- Includes receptacle and cover
- Each kit is a convenient, complete weatherproof installation — no need to purchase separate components

COMPLIANCES

- **(II)** File E212332 (MD/MG series)
- (U) File E313240 (5839 series)
- c(U) us File E346152 (5874/MK series)
- Meets NEC® 406.9 (A) Requirements
- NEMA 3R rated









5839-5WRTR to

	5839-7WRTR				
CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
Receptacle / FI	ip Cover Combos				
MD1050S	Hubbell WR/TR 15A GFCI Duplex/ Vertical/Horizontal Flip Cover Combo	Gray	Shrink	8	11111111
MG1050S	Hubbell WR/TR 15A Self Test GFCI / Vertical/Horizontal Flip Cover Combo	Gray	Shrink	6	
MD1250S	Hubbell WR/TR 15A GFCI Duplex / Horizontal/Vertical Flip Cover Combo	Gray	Shrink	8	
MG1250S	Hubbell WR/TR 15A Self Test GFCI / Horizontal/Vertical Flip Cover Combo	Gray	Shrink	6	IIIIIIII
Complete Flip	Cover Kits				
5839-5WRTR	Flip Cover, WR/TR Duplex, GFCI	Gray	Box	4	IIIIIIII
5839-6WRTR	Flip Cover, WR/TR Duplex, GFCI	White	Box	4	
5839-7WRTR	Flip Cover, WR/TR Duplex, GFCI	Bronze	Box	4	IIIIIIII
5874-5S	Self Test GFCI	Gray	Box	4	11111111
5874-6S	Self Test GFCI	White	Box	4	IIIIIIII
MK1250S	GFCI Duplex	Gray	Clamshell	4	IIIIIIII
MK1250WH	Duplex	White	Clamshell	4	IIIIIIII

BELL WEATHERPROOF

METAL BOX COVERS



5175-0 to 5175-5



5177-0

CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
1-Gang Blan	k Covers - Device Mount				
5173-0	Blank Cover	Gray	Shrink	50	11111111
5173-1	Blank Cover	White	Shrink	50	11111111
5173-2	Blank Cover	Bronze	Shrink	50	11111111
5173-5	Blank Cover	Gray	Carded	12	IIIIIIII
5173-6	Blank Cover	White	Carded	12	
5173-7	Blank Cover	Bronze	Carded	12	IIIIIIII
1-Gang Blan	k Covers - Box Mount				
5174-0	Blank Cover	Gray	Shrink	50	IIIIIIII
2-Gang Blan	k Covers - Device Mount				
5175-0	Blank Cover	Gray	Shrink	25	IIIIIIII
5175-1	Blank Cover	White	Shrink	25	
5175-2	Blank Cover	Bronze	Shrink	25	IIIIIIII
5175-5	Blank Cover	Gray	Carded	6	IIIIIIII
3-Gang Blan	k Covers - Box Mount				
5177-0	Blank Cover	Gray	Boxed	10	11111111

APPLICATION

• For use whenever weatherproof protection is required for a weatherproof box

PRODUCT FEATURES

- Rugged metallic construction
- Durable powder coat finish provides maximum weatherability and scratchresistance

COMPLIANCES

- c(UL) us File E195978
- NEC® Compliant
- NEMA 3R Rated

ROUND BOX COVERS

www.hubbell.com/bell/en



CATALOG # 4" Round Cover	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
5374-0	Round, Blank Cover	Gray	Shrink	30	11111111
5374-1	Round, Blank Cover	White	Shrink	20	IIIIIIII
5374-2	Round, Blank Cover	Bronze	Shrink	20	HHHH

APPLICATION

• For use with 4" round splice boxes

PRODUCT FEATURES

- Rugged metallic construction
- Durable powder coat finish
- Includes installation hardware, gasket and multilingual instructions

COMPLIANCES

- (U) File E195978
- NEC® Compliant
- NEMA 3R Rated

SEE END OF SECTION (PG D42) FOR DETAILED DRAWINGS >>> SEE END OF SECTION (PG D41) FOR DETAILED DRAWINGS >>

HUBBELL



METAL ROCKER SWITCH COVERS

METAL TOGGLE SWITCH COVERS

METAL DECORATOR SWITCH COVERS

APPLICATION

 A convenient and stylish switch for BBQ island, patio, deck, exterior walls, pool and spa and more

PRODUCT FEATURES

- Convenient on/off rocker switch
- Internal elastomer membrane
- Compatible with single pole or 3-way decorator switches

COMPLIANCES

- c(UL) us File E116141
- NEC® Compliant
- NEMA 3R Rated







5123-0

5127-0

Enhance Your Outdoor Space!
















5122-0*

5123-2

5127-2

9	9	
	9	,



BELL WEATHERPROOF

* 15A 120/277 VAC single pole decorator switch included.



5121-0 to 5121-5 5141-0 to 5141-5 5128-0, 5137-0

5166-0WRTR to 5166-5WRTR



5124-0, 5124-5







5167-0







5126-0

APPLICATION

• For use whenever weatherproof protection is required for an "on-off" type switch

PRODUCT FEATURES

- Rugged metallic construction
- Durable powder coat finish provides maximum weatherability and scratch resistance.
- Includes installation hardware and multilingual instructions
- Most units supplied with switch(es) no need to purchase separate components
- Switch/cover units are supplied with the switch unassembled to the cover

COMPLIANCES

- **(J)** File E195978
- NEC® Compliant
- NEMA 3R Rated

CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
1-Gang Switch	Covers – Vertical – Device Mounted				
5121-0	SP 125V, 15A	Gray	Shrink	24	IIIIIIII
5121-1	SP 125V, 15A	White	Shrink	24	IIIIIIII
5121-2	SP 125V, 15A	Bronze	Shrink	24	IIIIIIII
5121-5	SP 125V, 15A	Gray	Carded	6	IIIIIIII
5141-0	3-Way 125V, 6A or 250V, 3A	Gray	Shrink	8	11111111
5141-5	3-Way 125V, 6A or 250V, 3A	Gray	Carded	6	11111111
5128-0	SP 120-277VAC, 20A	Gray	Shrink	20	11111111
5137-0	DP 120-277VAC, 20A	Gray	Shrink	20	11111111
2-Gang Switch	Covers – Device Mounted				
5124-0	(2) SP 125V, 15A	Gray	Shrink	8	11111111
5124-5	(1) SP & (1) 3-Way 125V, 15A Toggle switch	Gray	Carded	4	HHHHH
5125-0	Cover only	Gray	Shrink	8	11111111
5166-OWRTR	(1) SP 125V, 15A & (1) WR/TR Duplex Receptacle	Gray	Shrink	8	HHHHH
5166-5WRTR	(1) SP 125V, 15A & (1) WR/TR Duplex Receptacle	Gray	Carded	4	HHHH
5167-0	2-Gang, Switch/GFCI Cover	Gray	Shrink	8	HHHH
3-Gang Switch	Cover – Device Mount				
5126-0	(3) SP 125V, 15A	Gray	Boxed	1	11111111
Toggle Switch					
5201-0	SP 125V, 15A Toggle switch	_	Polybag	10	

www.hubbell.com/bell/en

SEE END OF SECTION (PG D42) FOR DETAILED DRAWINGS >> SEE END OF SECTION (PG D43) FOR DETAILED DRAWINGS >>





DIE-CAST LAMPHOLDER/CLUSTER COVERS

DIE-CAST LAMPHOLDERS

APPLICATIONS

- For use with BELL® 1-Gang rectangular or round weather-proof boxes
- Cluster covers provide an easy means of mounting BELL® lampholders and other accessories

PRODUCT FEATURES

- Rugged die-cast construction
- Durable powder coat finish provides maximum weatherability and scratchresistance
- Includes installation hardware, gasket and multilingual instructions
- Three-hole covers are supplied with two closure plugs

COMPLIANCES

- **\$** Standard 514A
- NEC® Compliant
- NEMA 3R Rated









5186-0 to 5189-0 to 5193-0 to 5186-7 5189-7 5193-7

5197-0 to 5197-7

CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
Rectangular	Cluster Covers				
5186-0	(1) 1/2" Outlet	Gray	Shrink	20	IIIIIIII
5186-1	(1) 1/2" Outlet	White	Shrink	20	IIIIIIII
5186-2	(1) 1/2" Outlet	Bronze	Shrink	20	IIIIIIII
5186-5	(1) 1/2" Outlet	Gray	Carded	6	IIIIIIII
5186-6	(1) 1/2" Outlet	White	Carded	6	IIIIIIII
5186-7	(1) 1/2" Outlet	Bronze	Carded	6	HIIIIII
5189-0	(3) 1/2" Outlets	Gray	Shrink	20	IIIIIIII
5189-1	(3) 1/2" Outlets	White	Shrink	20	HIIIIII
5189-2	(3) 1/2" Outlets	Bronze	Shrink	20	11111111
5189-5	(3) 1/2" Outlets	Gray	Carded	6	HIIIIII
5189-6	(3) 1/2" Outlets	White	Carded	6	IIIIIIII
5189-7	(3) 1/2" Outlets	Bronze	Carded	6	HIIIIII
4" Round C	luster Covers				
5193-0	(1) 1/2" Outlet	Gray	Shrink	20	11111111
5193-1	(1) 1/2" Outlet	White	Shrink	20	IIIIIIII
5193-2	(1) 1/2" Outlet	Bronze	Shrink	20	IIIIIIII
5193-5	(1) 1/2" Outlet	Gray	Carded	6	11111111
5193-6	(1) 1/2" Outlet	White	Carded	6	IIIIIIII
5193-7	(1) 1/2" Outlet	Bronze	Carded	6	HIIIIII
5197-0	(3) 1/2" Outlets	Gray	Shrink	20	HIIIIII
5197-1	(3) 1/2" Outlets	White	Shrink	20	HIIIIII
5197-2	(3) 1/2" Outlets	Bronze	Shrink	20	HIIIIII
5197-5	(3) 1/2" Outlets	Gray	Carded	6	HIIIIII
5197-6	(3) 1/2" Outlets	White	Carded	6	HIIIIII
5197-7	(3) 1/2" Outlets	Bronze	Carded	6	IIIIIIII



CATALOG #		COLOR	PKG. TYPE	STD. PKG.	BARCODE
Lampholde	ers and Accessories for 75-150 Wa	att Par 38	3 Lamps		
5606-0	Lampholder	Gray	Shrink	30	IIIIIIII
5606-1	Lampholder	White	Shrink	30	IIIIIIII
5606-2	Lampholder	Bronze	Shrink	30	
5606-5	Lampholder	Gray	Carded	6	IIIIIIII
5606-6	Lampholder	White	Carded	6	
5606-7	Lampholder	Bronze	Carded	6	IIIIIIII
5612-0	Lampholder w/gasket	Gray	Shrink	30	IIIIIIII
5611-0	Outer gasket only, replacement gasket for 5612-0	_	Polybag	15	IIIIIIII
Architectu	ral Lampholders for 75-150 Watt	Par 38 La	amps		
5613-0	Lampholder	Gray	Shrink	4	IIIIIIII
5613-1	Lampholder	White	Shrink	4	
5613-2	Lampholder	Bronze	Shrink	4	HIIIIII

APPLICATIONS

- For outdoor or indoor lighting use
- For use with BELL® cluster covers and boxes

PRODUCT FEATURES

- Rugged metallic construction
- Durable powder coat finish provides maximum weatherability and scratchresistance
- Locking swivel knuckle assures positive lamp positioning and provides pinpoint directional aiming
- Extra long wire leads for easy hook-up
- Each lampholder supplied with a porcelain socket, inside gasket, 1/2" locknut and multilingual instructions

COMPLIANCES

- (U) Standard 1598
- NEC® Compliant
- NEMA 3R Rated

SWIVEL JOINT LAMPHOLDERS

www.hubbell.com/bell/en



CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
120V Halo	gen Swivel Lampholder				
LHS100S	75W Halogen Bulb Included (GY 8.6 TYPE 4)	Gray	Shrink	6	IIIIIIII
LHS100W	75W Halogen Bulb Included (GY 8.6 TYPE 4)	White	Shrink	6	IIIIIIII
LHS100Z	75W Halogen Bulb Included (GY 8.6 TYPE 4)	Bronze	Shrink	6	IIIIIIII
Traditional	or CFL Swivel Lampholder				
LTS100S	Uses Par 38 Bulb (150W Maximum, Not Included)	Gray	Shrink	10	
LTS100WH	Uses Par 38 Bulb (150W Maximum, Not Included)	White	Shrink	10	IIIIIIII
LTS100Z	Uses Par 38 Bulb (150W Maximum, Not Included)	Bronze	Shrink	10	IIIIIIII

APPLICATION

• For general outdoor lighting use in wet, damp or dry locations

PRODUCT FEATURES

- Superior commercial quality die-cast metal construction
- Premium powder coat finish
- LTS100 include porcelain sockets and external weatherproof gaskets. CFL compatible
- LHS uses halogen bulb which last up to 3 times longer and produce almost 50% more light as incandescent bulbs
- No-tool easy-mount feature
- Swivel joint for easy directional lighting

COMPLIANCES

- (L) File E310337
- NEC® Compliant
- NEMA 3R Rated

HUBBELL

HUBBELL

LED SWIVEL FLOODLIGHTS

LL800S

LL800Z

METAL BULLET LAMPHOLDER AND PORTABLE LAMPHOLDERS

APPLICATION

• Use to light outdoor hard-to-see areas for added convenience

DIE-CAST LED FLOODLIGHTS

PRODUCT FEATURES

- 85% less energy consumption (8W)
- 800 lumens (LL800 series) equal to a 60W incandescent
- Die-cast aluminum heads
- Swivel joint for easy light adjustment
- 120VAC 60Hz
- Long life up to 50,000 hours

COMPLIANCES

• c(VL)us — NEC and NEMA 3R

APPLICATION

• Use to light outdoor hard-to-see areas for added convenience

PRODUCT FEATURES

- Commercial Grade
- 85% less energy consumption (13W)
- 1200 lumens (equal to 75W Incandescent)
- Die-cast aluminum heads
- Unique locking swivel joint for easy light adjustment
- 120/277VAC 50/60Hz
- Long life up to 50.000 hours
- 6" lead wires

COMPLIANCES

- c(VL) us NEC and NEMA 3R
- DI.C4.0 CERTIFIED

APPLICATION

Warm White 3000K

CAT.#	DESCRIPTION	COLOR	PKG. Type	STD. PKG.	BAR- Code
LED Swivel Floodlight for Outdoor Use in Wet Locations					
LL800S	Weatherproof LED Floodlight 8W/800 Lumen Warm White	Gray	Box	4	IIIIIIII
LL800W	Weatherproof LED Floodlight 8W/800 Lumen Warm White	White	Вох	4	IIIIIIII
118007	Weathernroof LED Floodlight 8W/800 Lumen Warm White	Bronze	Box	4	HHHH

LL800W



CAT. #	DESCRIPTION	COLOR	TYPE	PKG.	CODE
LED Sw	ivel Floodlight for Outdoor Use in Wet Locations				
LL1200S	Weatherproof LED Floodlight 13W/1200 Lumen Warm White	Gray	Box	4	IIIIIIII
LL1200W	Weatherproof LED Floodlight 13W/1200 Lumen Warm White	White	Box	4	IIIIIIII
LL1200Z	Weatherproof LED Floodlight 13W/1200 Lumen Warm White	Bronze	Box	4	IIIIIIII

LED KIT WITH MOTION SENSOR SWITCH

BELL WEATHERPROOF

• Use to light outdoor hard-to-see areas for added convenience

PRODUCT FEATURES

- Warm white LED flood lights (3000K) 2000 lumens 26W
- Die-cast aluminum heads and cover
- Multidirectional swivel joint for easy light adjustment
- 180° motion sensor with duration. sensitivity and photocell controls (See part number 5639-5 pg. D29)
- 2 additional 1/2" threaded openings with closure plug
- 120VAC
- Product Warranty: 5 years

COMPLIANCES

HUBBELL

• c(VL)us — NEC and NEMA 3R



CATALOG #	DESCRIPTION	COLOR	PKG. Type	STD. PKG.	BARCODE
Round Co	over, Light and Motion Sensor Kit				
5882-5	Weatherproof LED Flood Light Kit with Motion Sensor	Gray	Box	4	IIIIIIII
5882-6	Weatherproof LED Flood Light Kit with Motion Sensor	White	Box	4	IIIIIIII
5882-7	Weatherproof LED Flood Light Kit with Motion Sensor	Bronze	Box	4	IIIIIIII

CATALOG # Bullet Lamp	DESCRIPTION Pholders - for 75-150 Watt Pa		PKG. TYPE R-40 Lamps		BARCODE
5820-8	Lampholder	Green	Boxed	2	IIIIIII

5820-8

APPLICATION

- For general outdoor lighting use
- Use with BELL® cluster covers and boxes

PRODUCT FEATURES

- · Rugged die-cast
- Locking swivel knuckle
- Assure positive lamp positioning and provides pinpoint directional aming
- Includes installation hardware and multilingual instructions

COMPLIANCES

- NEC® Compliant
- NEMA 3R rated

PORTABLE LAMPHOLDERS



APPLICATION

• For general outdoor lighting use in wet, damp or dry locations

PRODUCT FEATURES

- · Rugged die-cast construction
- Durable powder coat finish provides maximum weatherability and scratch-resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional
- SPLED2Z Long lasting energy efficient 6.5 Watts/350 Lumens
- SPLED500Z Multidirectional swivel joint/long life: 50,000 hours - energy efficient 9 Watts/540 Lumens

COMPLIANCES

- (\$\mathbb{U}\mathbb{L}\mathbb{D}\mathbb{D}\mathbb{File E310318 (\$\mathbb{L}101\mathbb{B}/\mathbb{S}PLED500Z)
- NEC® Compliant
- NEMA 3R rated

CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
Portable Spike L	_ights				
SPLED2Z	6.5 Watts Warm White LED 350 Lumens	Bronze	Box	4	IIIIIIII
SPLED500Z	9 Watts Warm White LED 540 Lumens	Bronze	Box	4	
SL101B	Uses Par 38 Bulb (150W Maximum, Not Included)	Bronze	Clamshell	10	HHHHH
5792-0	Spike, 6 ft. cord & plug	Gray	Polybag	12	11111111

www.hubbell.com/bell/en

SEE END OF SECTION (PG D44) FOR DETAILED DRAWINGS >> SEE END OF SECTION (PG D45) FOR DETAILED DRAWINGS >>





DIE-CAST LAMPHOLDER COMBINATIONS

LIGHT KITS

APPLICATION

• For use with BELL® 1-Gang rectangular or round weatherproof boxes

PRODUCT FEATURES

- Rugged metallic construction
- Durable powder coat finish provides maximum weatherability and scratchresistance
- Each combination kit is a complete weatherproof installation – no need to purchase separate components
- Includes installation hardware, gasket and multilingual instructions

COMPLIANCES

- **(4)** File E225082
- NEC® Compliant
- NEMA 3R Rated



CATALOG #	DESCRIPTION Cover – Combinations for 7	COLOR 5 150 West	PKG. TYPE		BARCODE
				•	
5620-0	(1) Lampholder	Gray	Shrink	8	
5620-5	(1) Lampholder	Gray	Carded	4	IIIIIIII
5621-0	(2) Lampholders	Gray	Shrink	8	
5621-5	(2) Lampholders	Gray	Carded	4	11111111
5621-6	(2) Lampholders	White	Carded	4	IIIIIII
5621-7	(2) Lampholders	Bronze	Carded	4	IIIIIIII
4" Round Co	over – Combinations for 75-	150 Watt Pa	ar 38 Lamps		
5624-0	(1) Lampholder	Gray	Shrink	8	HHHH
5624-1	(1) Lampholder	White	Shrink	8	11111111
5624-2	(1) Lampholder	Bronze	Shrink	8	HHHH
5624-5	(1) Lampholder	Gray	Carded	4	HHHH
5624-6	(1) Lampholder	White	Carded	4	HHHH
5625-0	(2) Lampholders	Gray	Shrink	8	11111111
5625-1	(2) Lampholders	White	Shrink	8	HHHH
5625-2	(2) Lampholders	Bronze	Shrink	8	1111111
5625-5	(2) Lampholders	Gray	Carded	4	HHHH
5625-6	(2) Lampholders	White	Carded	4	11111111
5625-7	(2) Lampholders	Bronze	Carded	4	HHHH



5883-5 to 5883-6



5818-5 to 5818-6

APPLICATION

 For general lighting use in wet, damp or dry locations

PRODUCT FEATURES

- Each kit is a complete weatherproof installation - no need to purchase separate components
- Each kit includes easy-to-follow multilingual instructions
- All kit components are described in the preceding pages

COMPLIANCES

- (l)
- NEC® Compliant
- NEMA 3R Rated



5841-5 to 5841-6



5829-5 to 5829-6



5876-5 to 5876-7

CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
Rectangular Light	Kits for 75-150 Watt Par 38 Lamps				
5883-5	Box, cover, photocell & (2) lampholders	Gray	Boxed	4	IIIIIIII
5883-6	Box, cover, photocell & (2) lampholders	White	Boxed	4	IIIIIIII
5818-5	Box, cover & (2) lampholders	Gray	Boxed	4	IIIIIIII
5818-6	Box, cover & (2) lampholders	White	Boxed	4	IIIIIIII
I" Round Light Ki	ts for 75-150 Watt Par 38 Lamps				
5829-5	Box, cover & (2) lampholders	Gray	Boxed	4	IIIIIII
5829-6	Box, cover & (2) lampholders	White	Boxed	4	IIIIIIII
5841-5	Box, cover, photocell & (2) lampholders	Gray	Boxed	4	IIIIIIII
5841-6	Box, cover, photocell & (2) lampholders	White	Boxed	4	IIIIIIII
5876-5	Box, cover & (2) architectural lampholders	Gray	Boxed	4	IIIIIII
5876-6	Box, cover & (2) architectural lampholders	White	Boxed	4	IIIIIIII
5876-7	Box, cover & (2) architectural lampholders	Bronze	Boxed	4	IIIIIII

HUBBELL





METALLIC GARDEN LIGHTS ACCESSORIES

APPLICATION

• For accent lighting along walkways, driveways, terraces, porches and garden areas

PRODUCT FEATURES

- Rugged die-cast construction
- Durable powder coat finish provides maximum weatherability and scratch-
- Includes screw-in clear glass globe, wire connectors, gasket, and multilingual instructions
- Three-tier lights accept 40W maximum lamps
- Four-tier lights accept 60W maximum lamps

COMPLIANCE

• cUL)us



CATALOG # Incandescent T	DESCRIPTION ype Threaded 1/2" Npt		PKG. TYPE	STD. PKG.	BARCODE
5884-8	3-Tier	Green	Box	2	11111111
5893-8	4-Tier	Green	Box	2	IIIIIIII
Replacement G	lobes for Garden				
5694-0	For 3-tier	Clear	Carton	4	HHHH
5695-0	For 4-tier	Clear	Carton	4	11111111

MOTION SENSOR SWITCH



CATALOG # | Motion Sensor Switch

5639-5

5639-6

5639-7







5639-7

|||||||

DESCRIPTION OUTER CTN. QTY. STD. PKG. BARCODE 10 ||||||| Weatherproof motion sensor switch, Gray Weatherproof motion sensor switch, White

10

APPLICATION

• For use whenever outdoor motion detection is needed in unlit areas

PRODUCT FEATURES

- Swivel joint for easy aiming
- 180° motion sensor with duration, sensitivity and photocell controls
- Standard 1/2" threaded mount
- 120VAC

COMPLIANCES

• culus — NEC & NEMA 3R

PHOTOCELL



Weatherproof motion sensor switch, Bronze



PE100

CATALOG # Photoelectric	DESCRIPTION Eye Switch	COLOR	PKG. TYPE	STD. PKG.	BARCODE
5638-5	Swivel Switch, locknut 2000W Tungsten 1800VA Ballast 120V 50-60HZ	Gray	Carded	6	IIIIIIII
PE100	Outdoor Photoelectric Switch Rated 1000 Watts, Fits 1/2" Hole	Black	Poly Bag	10	IIIIIIII

APPLICATION

- Use for darkness activated automatic control of night lighting from dusk to dawn
- Control porch lights, garden lights, post lanterns, barn lights, loading dock lights, outdoor signs etc.

PRODUCT FEATURES

- Durable weatherproof construction
- Built-in time delay prevents operation temporary light flashes

METAL CLOSURE PLUGS



5269-0 to 5269-10, 5270-0 to 5270-9, 5271-0

	0203 0 10 02	05 10, 0	2700 10 3270	J, JL/ I J	
CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
Closure Plugs	5				
5269-0	1/2" NPT	Gray	75 Polybags of 4	75 bags*	IIIIIIII
5269-1	1/2" NPT	White	75 Polybags of 4	75 bags*	IIIIIIII
5269-2	1/2" NPT	Bronze	75 Polybags of 4	75 bags*	IIIIIIII
5269-5	1/2" NPT	Gray	12 Cards of 3	12 cards**	IIIIIIII
5269-6	1/2" NPT	White	12 Cards of 3	12 cards**	IIIIIIII
5269-7	1/2" NPT	Bronze	12 Cards of 3	12 cards**	IIIIIIII
5269-9	1/2" NPT	Gray	Bulk	1000	_
5269-10	1/2" NPT	Bronze	Bulk	4500	_
5270-0	3/4" NPT	Gray	75 Polybags of 4	75 bags*	IIIIIIII
5270-1	3/4" NPT	White	75 Polybags of 4	75 bags*	IIIIIIII
5270-5	3/4" NPT	Gray	12 Cards of 3	12 cards**	IIIIIIII
5270-9	3/4" NPT	Gray	Bulk	1000	_
5271-0	1" NPT	Gray	75 Polybags of 4	75 bags*	IIIIIIII

^{*}Order in standard package bag quantities only - not per piece

- triggered by auto headlamps or other

APPLICATION

• For use with BELL® weatherproof boxes, extension adapters, cluster covers and round splice boxes to seal off unused outlets

PRODUCT FEATURES

- Gray closure plugs are die-cast zinc
- White and bronze closure plugs are nonmetallic

COMPLIANCE

• **(4)** – File E195973

SEE END OF SECTION (PG D46) FOR DETAILED DRAWINGS >>





SEE END OF SECTION (PG D46) FOR DETAILED DRAWINGS >>

^{**}Order in standard package card quantities only — not per piece



PRCF57550GY

ACCESSORIES

NONMETALLIC CEILING FAN/LUMINAIRE BOXES

BOX MOUNTING LUGS

	DESCRIPTION Lugs & Screws		PKG. TYPE	STD. PKG.	BAR CODE
5302-0	_	_	100 Polybags of 2	100	IIIIIIII



5302-0

ROUND CLOSURE PLATES

APPLICATION

 Use in dry locations for closure of unused ceiling outlets

PRODUCT FEATURES

- Rugged metallic construction
- Durable powder coat paint finish provides a scratch-resistant surface

COMPLIANCE

• **(4)** – File E195978



CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BAR CODE
5" Round Clos	sure Plates – Steel				
5652-1	Screw & universal mount strap	Off White	Shrink	10	IIIIIIII
5653-1	(2) 8 - 32 screws, direct mount to fixture outlet box	Off White	Shrink	10	IIIIIIII
5654-1	Fixture stud & universal mount strap	Off White	Shrink	10	IIIIIIII

REPLACEMENT GASKETS

BELL WEATHERPROOF

APPLICATION

CATALOG #

5019-0

5017-0

5020-0

 Replacement gaskets for BELL® weatherproof covers and lampholders

PRODUCT FEATURES

- Each gasket has cut outs for a toggle switch, duplex (5020-0 only) receptacle and 1.406" dia. round receptacle
- Remove cut outs for the duplex (5020-0 only) and round receptacles for a GFCI receptacle opening

Rectangular Box/Cover Gaskets

DESCRIPTION

1-Gang

2-Gang





PKG. TYPE STD. PKG. BARCODE COLOR Black 20 Cello bags of 2 20 1-Gang cover gasket, 4 Lampholder gaskets, 1 Round cover gasket 20 Black 20 Cello bags Black 20 Cello bags of 2 20 |||||||

OUTDOOR CEILING FAN & LUMINAIRE BOXES







PRCF57550BZ

APPLICATIONS

- Provides a safe and secure mounting and weatherproof wiring junction for outdoor fans, chandeliers or pendant lights
- Designed to enhance outdoor living spaces with the same convenience and comfort as
- Perfect for porches, covered patios, pergolas

PRODUCT FEATURES

- Support fans up to 70lbs or heavy luminaires up to 150lbs
- Constructed of heavy duty PVC with integrated galvanized steel support bracket
- Five 3/4i" threaded entries for conduit or fittings with four closure plugs
- Includes three reducer bushings (3/4" to 1/2")
- Box mounts parallel, perpendicular or 45° from a joist

COMPLIANCES

- U Listed
- NEC and NEMA 3R Compliant



CATALOG # DESCRIPTION		CU. IN. CAPACITY		RECOMMENDE		STD.	BARCODE
GAIALUU #	DESCRIPTION	(when used w/collar)	ENTRIES	CEILING FAN (Dynamic) LBS.	FIXTURE (STATIC) LBS.	PKG.	DARGODE
4" Nonmetallic	Outdoor Round Box, 1-1/2" Deep	- Heavy Duty PVC	w/Integrated C	Salvanized Steel	Support Bracke	et	
PRCF57550GY	Ceiling Fan Luminaire Box, Gray	16.0"	(5) 3/4" or 1/2"	70	150	4	IIIIIIII
PRCF57550WH	Ceiling Fan Luminaire Box, White	16.0"	(5) 3/4" or 1/2"	70	150	4	IIIIIIII
PRCF57550BZ	Ceiling Fan Luminaire Box, Bronze	16.0"	(5) 3/4" or 1/2"	70	150	4	IIIIIIII

www.hubbell.com/bell/en

SEE END OF SECTION (PG D46) FOR DETAILED DRAWINGS >> SEE END OF SECTION (PG D47) FOR DETAILED DRAWINGS >>





NONMETALLIC BOXES **NONMETALLIC COVERS**

APPLICATION

• For general use whenever weatherproof protection is required

PRODUCT FEATURES

- Durable high impact PVC construction
- Can be used for 1/2" and 3/4" conduit
- Includes 3/4" closure plugs and reducer bushings

COMPLIANCES

- (UL) us LISTED UL Marine Listed
- Meets NEC® 406.9 (A) Requirements
- NEMA 3R Rated

HUBBELL

OUTLET BOXES



PSB37550GY



PSB37550WH







PDB77550GY



PDB77550WH



PRB57550GY



PRB57550WH







CATALOG #	DESCRIPTION oxes, Three Threaded Outlets	CU. IN. (CM³)	COLOR	PKG. TYPE	STD. PKG.	BARCODE
PSB37550GY	Three 1/2" or 3/4" Holes 2.0" Depth	16.5 (270.4)	Gray	Shrink	8	IIIIIIII
PSB37550WH	Three 1/2" or 3/4" Holes 2.0" Depth	16.5 (270.4)	White	Shrink	5	IIIIIIII
2-Gang Outlet Bo	oxes, Seven Threaded Outlets					
PDB77550GY	Seven 1/2" or 3/4" Holes 2.0" Depth	26.5 (434.3)	Gray	Shrink	6	IIIIIIII
PDB77550WH	Seven 1/2" or 3/4" Holes 2.0" Depth	26.5 (434.3)	White	Shrink	6	IIIIIIII
Round Outlet Bo	x, Five Threaded Outlets					
PRB57550GY	Five 1/2" / 3/4" Holes 1.5" Depth	13.5 (221.2)	Gray	Shrink	8	IIIIIIII
PRB57550WH	Five 1/2" / 3/4" Holes 1.5" Depth	13.5 (221.2)	White	Shrink	8	IIIIIIII

BLANK COVERS



PBC100GY PBC100WH PBC200GY PBC200WH



PBC300GY PBC300WH

APPLICATION

• For general use whenever weatherproof protection is required

PRODUCT FEATURES

- Durable high impact polycarbonate construction
- Includes attached gasket and mounting hardware

COMPLIANCES

- cUL)us
- NEC® Compliant
- NEMA 3R Rated

CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
Blank Covers					
PBC100GY	Blank	Gray	Shrink	12	IIIIIIII
PBC100WH	Blank	White	Shrink	12	IIIIIIII
PBC200GY	Blank 2-Gang	Gray	Shrink	10	IIIIIIII
PBC200WH	Blank 2-Gang	White	Shrink	10	IIIIIIII
PBC300GY	Blank Round	Gray	Shrink	10	IIIIIIII
PBC300WH	Blank Round	White	Shrink	10	IIIIIIII

TOGGLE / DEVICE COVERS

Horseshoe Adapter Ensures a Snug Fit for Small and Large Head Switches









PTC521GY



PTC100GY PTC100WH









CATALOG # 1-Gang Device Covers	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
PTC100GY	Toggle	Gray	Shrink	5	11111111
PTC100WH	Toggle	White	Shrink	3	IIIIIIII
2-Gang Device Covers					
PTC200GY	Toggle/Toggle	Gray	Shrink	3	IIIIIIII
PTC521GY	Toggle/GFCI	Gray	Shrink	3	IIIIIII
PTC521WH	Toggle/GFCI	White	Shrink	4	IIIIIIII

SEE END OF SECTION (PG D44-D47) FOR DETAILED DRAWINGS >>

HUBBELL

NONMETALLIC LIGHTING

NONMETALLIC ACCESSORIES

APPLICATION

• For general outdoor lighting use in wet, damp or dry locations


PRODUCT FEATURES

- Durable high impact PBT construction
- Includes attached gasket and mounting


COMPLIANCES

- cUL us
- NEC® Compliant
- NEMA 3R Rated

HUBBELL



LAMPHOLDER COVERS



_	110	~~	~~
o.	.V3	211	1 - V
ГL	_v .⊃	Ju	u

PLV330WH

CATALOG # Lampholders	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BARCODE
PLTS100GY	Swivel Lampholder	Gray	Shrink	12	11111111
PLTS100WH	Swivel Lampholder	White	Shrink	12	11111111
Lampholder Covers					
PLV330GY	Three 1/2" Holes	Gray	Shrink	8	HHHH
PLV330WH	Three 1/2" Holes	White	Shrink	8	HHHH

BELL WEATHERPROOF

NONMETALLIC CLOSURE PLUGS





PCP47550GY

PCP47550WH

CATALOG #	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BAR CODE
Closure Plug A	Assortment (Pack of 4)				
PCP47550GY	Two 1/2", Two 3/4"	Gray	Poly Bag	30	IIIIIII
PCP47550WH	Two 1/2", Two 3/4"	White	Poly Bag	30	IIIIIIII





HB75W

GK240

CATALOG # Gaskets	DESCRIPTION	COLOR	PKG. TYPE	STD. PKG.	BAR CODE
GK240	Bag of 2 Lampholder Gaskets	Black	Poly Bag	15	HHHH
Halogen Replacement Bulbs	5				
HB75W	75W Halogen Bulb (GY 8.6 Type 4)	Clear	Poly Bag	100	HHHH

www.hubbell.com/bell/en

SEE END OF SECTION (PG D49) FOR DETAILED DRAWINGS >> SEE END OF SECTION (PG D49) FOR DETAILED DRAWINGS >>






DETAILED DRAWINGS


DETAILED DRAWINGS

DIE-CAST ALUMINUM BOXES AND EXTENSION RINGS


1-GANG BOXES (General Dimensions)




EXTENSIONS: 5406-0




2-GANG BOXES WITH 7 OUTLETS CAT. NOs. 5340-0, 5348-0




CAT. NOs. 5338-0, 5346-0




EXTENSIONS: 5399-0, 5403-0




2-GANG BOXES WITH 5 OUTLETS CAT. NOs. 5388-0, 5389-0






2-GANG EXTENSION




EXTENSIONS: 5400-0 SERIES




2-GANG BOXES (General Dimensions)


SWING ARM EXTENSION ADAPTERS: 5412-0 TO 5415-0





3-GANG BOX





4" ROUND SPLICE BOXES












END VIEW FOR STYLES WITH TWO OUTLETS ON ONE END

4" ROUND EXTENSION ADAPTERS










METALLIC 1-GANG DEVICE COVERS

MX1050




MX1250







MX1550




RAYNTITE® 1-GANG DEVICE COVERS – VERTICAL




RAYNTITE® 1-GANG DEVICE COVERS -HORIZONTAL




GFCI STYLE COVERS




DUPLEX STYLE COVER




SINGLE RECEPTACLE STYLE COVERS




CAT. NOs. 5180-0 SERIES




CAT. NO. 5101-0 series







CAT. NO. 5102-0




CAT. NO. 5152-0







CAT. NO. 5153-0




CAT. NO. 5712-5WRTR







METALLIC 2-GANG DEVICE COVERS


MX2050





MX2150










METALLIC 1-GANG LOCKING COVER

4600RAC









METALLIC 2-GANG DEVICE COVERS


RAYNTITE®









5145-0










METAL 3-GANG DEVICE COVERS

MX3050









BOX MOUNT FLIP COVER

5093-0




FLIP COVER COMBOS AND KITS


MD1050S




MG1050S




MD1250S










MG1250S








MK1250, 5874-5, 5874-6










METAL COVERS


2-GANG 3-GANG 1-GANG BLANK COVERS 6 13/32 2-25/32" -1-13/16-5 5/8 DEVICE MOUNT BOX MOUNT


METALLIC ROUND BOX COVER




METAL ROCKER SWITCH COVERS


DECORATOR COVER SERIES
















METALLIC TOGGLE SWITCH COVERS


1-GANG **5121 SERIES, 5141 SERIES** CAT. NOs. 5128-0, 5137-0




2-GANG CAT. NO. 5124-0, 5125 SERIES




2-GANG 5167 SERIES




2-GANG 5166 SERIES



3-GANG




TOGGLE SWITCH CATALOG NOS. 5201-0




METALLIC LAMPHOLDER COVERS


RECTANGULAR CLUSTER COVERS 5186 SERIES, 5189 SERIES




ROUND CLUSTER COVERS 5193 SERIES, 5197 SERIES









METALLIC PORTABLE LAMPHOLDERS







METALLIC LAMPHOLDER COMBINATIONS AND GARDEN LIGHT



5625 SERIES




5884-8, 5893-8




CATALOG #	DIA.	HEIGHT
5884-8	6"	7"
5893-8	6"	8-3/4"

REPLACEMENT GLOBE: 5694-0, 5695-0




CATALOG #	DIA.	HEIGHT
5694-0	3-1/4"	5"
5695-0	3-1/4"	6-3/4"


ACCESSORIES




PHOTOSCELL 5638




PE100




BOX MOUNTING LUG CATALOG NO. 5302-0





ROUND CLOSURE PLATES CATALOG NO. 5652-1














GASKET: **CATALOG NO. 5019-0**




GASKET: **CATALOG NO. 5020-0**




GASKETS: CATALOG NO. 5017-0




NONMETALLIC BOXES






PRB57550









NONMETALLIC COVERS

PBC100












DETAILED DRAWINGS


NONMETALLIC COVERS

PBC300













PTC200










PTC521








NONMETALLIC LIGHTING



NONMETALLIC ACCESSORIES

PCP47550





WEATHERPROOF BOXES, COVERS AND LIGHTING

NOTES