



SECTION W

Table of Contents



TrukTrak® and TredTrak® Systems



AccessTrak® Systems



ProTrak™ Systems




| Product | Page |
|-----------------------|------|
| Products at a Glance | W-2 |
| Features and Benefits | W-3 |
| TrukTrak® Systems | W-4 |
| TredTrak® Systems | W-5 |

| Product | Page |
|------------------------------|------|
| AccessTrak® Systems | W-6 |
| ProTrak™ Systems | W-7 |
| FloorTrak® Floor Cable Cover | W-8 |


Hose and Cable Protection Systems

Products at a Glance



TrukTrak® Systems

- High density polyurethane construction supports heavy loads and is weather resistant
- Modular interlocking design for easy installation, breakdown and storage
- Safety surface pattern reduces slipping and skidding
- High visibility safety blue and yellow colors



TredTrak® Systems

- High density polyurethane construction supports heavy loads and is weather resistant
- Modular interlocking design for easy installation, breakdown and storage
- Safety surface pattern reduces slipping and skidding
- High visibility safety blue and yellow colors



AccessTrak® Systems

- This interlocking system provides a safe, flexible means of protecting cables and hoses in areas requiring ADA compliance
- High density polyurethane construction is weather resistant
- AccessTrak is an expandable five channel system that expands by length or width
- High visibility safety symbols on blue and gray colors



ProTrak™ Systems

- High density polyurethane construction supports heavy loads and is weather resistant
- Modular interlocking design for easy installation, breakdown and storage
- Safety surface pattern reduces slipping and skidding
- High visibility safety yellow and black
- Anti-slip pad kits available



FloorTrak® Floor Cable Cover

- Flexible and rigid PVC material
- Protects and reduces trip hazards
- Available in four different sizes and five PVC colors to blend with the various decors
- Withstands temperatures of 0°F to +120°F (-18°C to +49°C)

Hose and Cable Protection Systems

Features and Benefits



Hubbell TrukTrak® non-metallic cable protectors are designed to safeguard electrical cables and cords from vehicle and pedestrian traffic. The TrukTrak interlocking system comes in two, three and five channel sizes and will protect cables up to 3.25 inches (82.6mm) in diameter. It is ideal for the industrial environment where it is necessary to support heavy trucks and fork lifts.




TredTrak® non-metallic cable protectors can also be interlocked to protect cables and cords of any length. The TredTrak system is a five channel modular cable protection system that will protect cable diameters up to 1.28 inches (32.5mm). It is designed to support pedestrian and light vehicle traffic in public, institutional and commercial applications. The Hubbell modular cable protection line also permits compliance with NEC® requirements (Article 525) for insulating electrical cables and cord at carnivals, amusement parks, convention centers and similar public areas.



The AccessTrak® ramping system is a modular cable protection product that enables users to be ADAAG (American Disabilities Act Accessibility Guidelines) compliant and limits the exposure of cables and hoses to people and light vehicles passing over those cables and hoses. AccessTrak is an expandable five channel system that will protect cable and hose diameters up to 1.31 inches (33.0mm). For applications requiring more than five channels, AccessTrak can be expanded by width. In addition, AccessTrak is interlocking expandable by length to protect cables and hoses of any length. The AccessTrak ramping system provides a safe, flexible means of protecting cables and hoses in areas requiring ADA compliance.



ProTrak™ non-metallic single channel cable protectors are suitable for lightweight vehicle and pedestrian traffic. Available in both black and yellow. The drop over PROTRK115 series can accommodate up to 0.75 inches (19.0mm), while the PROTRK140 can handle up to 1.50 inches (38.1mm). The hinged covered PROTRK1225 series can accommodate up to 0.75 inches (19.0mm). A unique tread surface provides maximum traction. ProTrak™ cable protectors can be interlocked as a single color run or as a yellow and black run.



FloorTrak® is a flexible, non-metallic cover for cables that run over the floor when portable cords and cables cannot be concealed or routed away from traffic patterns. FloorTrak protects, organizes and reduces trip hazards. Four different sizes mean it will handle cables of up to 1.25 inches (31.8mm) in diameter. FT2, FT3 and FT4 are available in five PVC colors to blend with the various decors. FT10 is available in black and yellow colors only. The F10 Heavy Duty FloorTrak is ideal for applications such as industrial work areas, food processing plants and abusive areas where cable management is necessary.


NEC® is a registered trademark of the The National Electrical Code.

Hose and Cable Protection Systems


TrukTrak® Systems

Ideal for Heavy Vehicle Traffic in Industrial, Commercial or Public Applications

- High density polyurethane construction supports heavy loads and is weather resistant
- Modular interlocking design for easy installation, breakdown and storage
- Safety surface pattern reduces slipping and skidding
- High visibility safety blue and yellow colors



| TrukTrak® Systems | Trak | | | Channel | | | Catalog Number |
|---|--------------------|-------------------|--------------------|-------------------|--------------------|---------------------|----------------------------------|
| | Length in. (mm) | Width in. (mm) | Height in. (mm) | Width in. (mm) | Height in. (mm) | Weight lbs. (kg) | |
| 5 Channel TrukTrak®, blue and yellow. | 36.0" (914) | 20" (508) | 2.31" (58.7) | 1.25" (31.8) | 1.25" (31.8) | 30.60 (13.9) | HBLTT5B |
| 5 Channel TrukTrak® end caps (pair only), yellow. | 7.50" (190) | 20" (508) | 2.31" (58.7) | 1.25" (31.8) | 1.25" (31.8) | 8.55 (3.9) | HBLTT5ECB (Female end) |
| | 5.25" (133) | 20" (508) | 2.31" (58.7) | 1.25" (31.8) | 1.25" (31.8) | 8.55 (3.9) | (Male end) |
| 5 Channel 45° right turn TrukTrak®, blue and yellow. | 25.0" (635) | 20" (508) | 2.31" (58.7) | 1.25" (31.8) | 1.25" (31.8) | 15.35 (7.0) | HBLTT545RB |
| 5 Channel 45° left turn TrukTrak®, blue and yellow. | 25.0" (635) | 20" (508) | 2.31" (58.7) | 1.25" (31.8) | 1.25" (31.8) | 14.45 (6.6) | HBLTT545LB |
| 3 Channel TrukTrak®, blue and yellow. | 36.0" (914) | 20" (508) | 3.05" (77.5) | 2.25" (57.2) | 2.25" (57.2) | 30.85 (14.0) | HBLTT3B |
| 3 Channel TrukTrak® end caps (pair only), yellow. | 8.25" (209) | 20" (508) | 3.05" (77.5) | 2.25" (57.2) | 2.25" (57.2) | 10.25 (4.6) | HBLTT3ECB (Female end) |
| | 6.38" (162) | 20" (508) | 3.05" (77.5) | 2.25" (57.2) | 2.25" (57.2) | 10.25 (4.6) | (Male end) |
| 2 Channel TrukTrak®, blue and yellow. | 36.0" (914) | 22" (559) | 4.13" (104.9) | 3.25" (82.6) | 3.25" (82.6) | 41.00 (18.6) | HBLTT2B |



Specifications

| | |
|-----------------------|-----------------------------------|
| Material | Polyurethane. |
| Operating Temperature | -40°F to +120°F (-40°C to +49°C). |
| Hinge Material | Reinforced fiberglass. |
| Safety Symbols | Per ANSI Z535.3. |

Load Capacity

| No. of Channels | Test Fixture Footprint Inches (mm) | Tire Load lbs. +/- 20% | | Axle Load lbs. +/- 20% | |
|--------------------|---------------------------------------|------------------------|--------------|------------------------|--------------|
| | | 70°F (21°C) | 120°F (49°C) | 70°F (21°C) | 120°F (49°C) |
| 5 | 6.9" x 17.3" (175 X 439) | 20,150 | 9,200 | 40,300 | 18,400 |
| 3 | 6.9" x 17.3" (175 X 439) | 14,210 | 4,653 | 18,420 | 9,306 |
| 2 | 6.9" x 17.3" (175 X 439) | 10,880 | 2,095 | 21,760 | 4,190 |


Dimensions in Inches (mm)

Hose and Cable Protection Systems


TredTrak® Systems

Improves Pedestrian Safety by Decreasing Risk of Tripping

- High density polyurethane construction supports heavy loads and is weather resistant
- Modular interlocking design for easy installation, breakdown and storage
- Safety surface pattern reduces slipping and skidding
- High visibility safety blue and yellow colors



| TredTrak® Systems | Trak | | | Channel | | | Catalog Number |
|--|-----------------|----------------|-----------------|----------------|-----------------|-------------|------------------------------------|
| | A | B | C | D | E | Weight | |
| Description | Length in. (mm) | Width in. (mm) | Height in. (mm) | Width in. (mm) | Height in. (mm) | lbs. (kg) | |
| 5 Channel TredTrak®, blue and yellow. | 36.0" (914) | 17.5" (445) | 1.95" (50) | 1.30" (33) | 1.30" (33) | 21.15 (9.6) | HBLTRED5B |
| 5 Channel TredTrak® end caps (pair only), yellow. | 5.75" (146) | 17.5" (445) | 1.95" (50) | 1.30" (33) | 1.30" (33) | 6.40 (2.9) | HBLTRED5ECB (Female end) |
| | 5.75" (146) | 17.5" (445) | 1.95" (50) | 1.30" (33) | 1.30" (33) | 6.40 (2.9) | (Male end) |
| 5 Channel TredTrak® female end caps (2 females), yellow. | 5.75" (146) | 17.5" (445) | 1.95" (50) | 1.30" (33) | 1.30" (33) | 6.40 (2.9) | HBLTRED5ECFB |
| 5 Channel "X" fitting, blue and yellow. | 17.5" (445) | 17.5" (445) | 1.95" (50) | 1.30" (33) | 1.30" (33) | 14.25 (6.5) | HBLTRED5XB |
| 5 Channel "Y" fitting, blue and yellow. | 17.5" (445) | 17.5" (445) | 1.95" (50) | 1.30" (33) | 1.30" (33) | 13.95 (6.3) | HBLTRED5YB |



Specifications

| | |
|-----------------------|-----------------------------------|
| Material | Polyurethane. |
| Operating Temperature | -40°F to +120°F (-40°C to +49°C). |
| Hinge Material | Reinforced fiberglass. |
| Safety Symbols | Per ANSI Z535.3. |

Load Capacity

| Product | Test Fixture Footprint Inches (mm) | Tire Load lbs. +/- 20% | | Axle Load lbs. +/- 20% | |
|-------------|---------------------------------------|------------------------|--------------|------------------------|--------------|
| | | 70°F (21°C) | 120°F (49°C) | 70°F (21°C) | 120°F (49°C) |
| TredTrak | 6.9" x 17.3" (175 X 439) | 10,500 | 6,500 | 21,000 | 13,000 |
| "X" Fitting | 6.9" x 17.3" (175 X 439) | 2,900 | 2,300 | 5,800 | 5,600 |
| "Y" Fitting | 6.9" x 17.3" (175 X 439) | 2,900 | 2,300 | 5,800 | 5,600 |


Dimensions in Inches (mm)

Hose and Cable Protection Systems

AccessTrak® Systems

ADA Compliant Limits Exposure of Cables and Hoses to Pedestrians

- This interlocking system provides a safe, flexible means of protecting cables and hoses in areas requiring ADA compliance
- High density polyurethane construction is weather resistant
- AccessTrak is an expandable five channel system that expands by length or width
- High visibility safety symbols on blue and gray colors




AccessTrak Expanded by Length

| AccessTrak® System | Trak | | | Channel | | | Catalog Number |
|--|-----------------|-----------------|-----------------|----------------|-----------------|------------------|----------------------|
| | A | B | C | D | E | | |
| Description | Length in. (mm) | Width in. (mm) | Height in. (mm) | Width in. (mm) | Height in. (mm) | Weight lbs. (kg) | |
| 5 Channel AccessTrak® kit*, blue and gray. | 41.06" (1043.0) | 42.90" (1090.0) | 4.00" (102.0) | 1.34" (34.0) | 1.31" (33.0) | 73.65 (33.41) | HBLAT5KITA |
| 5 Channel AccessTrak® trough, blue and gray. | 36.00" (914.0) | 13.34" (339.0) | 1.94" (49.0) | 1.34" (34.0) | 1.31" (33.0) | 22.35 (10.14) | HBLAT5A |
| AccessTrak® trough end rails (set), gray. | 2.50" (63.0) | 13.28" (337.0) | 4.00" (102.0) | — | — | 6.95 (3.15) | HBLAT5ERA |
| AccessTrak® ramps (set), blue. | 36.00" (914.0) | 14.50" (368.0) | 1.94" (49.0) | — | — | 29.90 (13.56) | HBLAT5RAMPA |
| AccessTrak® ramp end rails (set), gray. | 2.50" (63.5) | 14.75" (375.0) | 4.00" (102.0) | — | — | 8.05 (3.65) | HBLAT5RAMPERA |


Note: *Consists of (1) HBLAT5A; (1 set) HBLAT5ERA; (1 set) HBLAT5RAMPA; (2 sets) HBLAT5RAMPERA.

Assembled Kit

Accessibility label, blue symbol, white background




Trough (top view)




Trough (side view)




Ramp (top view)




Trough End Rails (side view)




Ramp End Rails (top view)



Ramp End Rails (side view)



Ramp (side view)



Specifications

| | |
|-----------------------|--------------------------------------|
| Material | Polyurethane. |
| Operating Temperature | -40°F to +120°F (-40°C to +49°C). |
| Hinge Material | Reinforced fiberglass. |
| Safety Symbols | Per ANSI Z535.3-1991. |
| ADA Symbols | Per ADAAG "Symbols of Accessibility" |

Load Capacity

| Product | Test Fixture Footprint Inches (mm) | Measured Load lbs. (N) +/- 20% | |
|------------|------------------------------------|--------------------------------|----------------|
| | | 70°F (21°C) | 120°F (49°C) |
| AccessTrak | 7" x 7" (178 x 178) | 10,000 (44,480) | 8,000 (35,584) |


Dimensions in Inches (mm)

Hose and Cable Protection Systems


ProTrak™ Systems

For Pedestrian and Light Vehicle Traffic

- High density polyurethane construction supports heavy loads and is weather resistant
- Modular interlocking design for easy installation, breakdown and storage
- Safety surface pattern reduces slipping and skidding
- High visibility safety yellow and black
- Anti-slip pad kits available



| ProTrak™ Systems | Trak | | | Channel | | | Catalog Number |
|---------------------------------|--------------------|-------------------|--------------------|-------------------|--------------------|---------------------|---------------------|
| | Length in. (mm) | Width in. (mm) | Height in. (mm) | Width in. (mm) | Height in. (mm) | Weight lbs. (kg) | |
| 1 Channel, drop over, yellow | 36.0" (914) | 5.25" (133) | .75" (19.0) | 1.50" (38.1) | .50" (12.7) | 3.00 (1.40) | PROTRK115Y |
| 1 Channel, drop over, black | 36.0" (914) | 5.25" (133) | .75" (19.0) | 1.50" (38.1) | .50" (12.7) | 3.00 (1.40) | PROTRK115BK |
| 1 Channel, drop over, yellow | 36.0" (914) | 10.75" (273) | 1.50" (38.1) | 4.00" (101.6) | 1.00" (25.4) | 8.00 (3.60) | PROTRK140Y |
| 1 Channel, drop over, black | 36.0" (914) | 10.75" (273) | 1.50" (38.1) | 4.00" (101.6) | 1.00" (25.4) | 8.00 (3.60) | PROTRK140BK |
| 1 Channel, hinged cover, yellow | 36.0" (914) | 10.81" (274) | 1.25" (31.8) | 2.25" (57.2) | .75" (19.0) | 7.80 (3.54) | PROTRK1225Y |
| 1 Channel, hinged cover, black | 36.0" (914) | 10.81" (274) | 1.25" (31.8) | 2.25" (57.2) | .75" (19.0) | 7.80 (3.54) | PROTRK1225BK |



Accessories

| ProTrak Series | Anti-Slip Pad Kits* |
|----------------|---------------------|
| PROTRK115 | PROTRK1ASPK |
| PROTRK140 | PROTRK2ASPK |
| PROTRK1225 | PROTRK3ASPK |

*One kit per section



Load Capacity

| Product | Test Fixture Footprint Inches (mm) | Tire Load lbs. +/- 20% | Axle Load lbs. +/- 20% |
|------------|---------------------------------------|------------------------|------------------------|
| | | 70°F (21°C) | 70°F (21°C) |
| PROTRK115 | 6.9" x 17.3" (175 X 439) | 10,500 | 21,000 |
| PROTRK140 | 6.9" x 17.3" (175 X 439) | 10,500 | 21,000 |
| PROTRK1225 | 6.9" x 17.3" (175 X 439) | 13,000 | 26,000 |

Dimensions in Inches (mm)



Hose and Cable Protection Systems

FloorTrak® Floor Cable Cover

For Pedestrian Traffic in Office and Public Areas

- Flexible and rigid PVC material
- Protects and reduces trip hazards
- Available in four different sizes and five PVC colors to blend with the various decors
- Withstands temperatures of 0°F to +120°F (-18°C to +49°C)

FT2BK10

FT3BK5

FT4BK5

FT10BK5

FloorTrak® 2*

| Color | Length Feet (meters) | Catalog Number |
|--------|-------------------------|-------------------|
| Black | 10.0' (3.05) | FT2BK10 |
| Brown | 10.0' (3.05) | FT2BR10 |
| Beige | 10.0' (3.05) | FT2BG10 |
| Gray | 10.0' (3.05) | FT2GY10 |
| Yellow | 10.0' (3.05) | FT2Y10 |

FloorTrak® 3*

| Color | Length Feet (meters) | Catalog Number |
|--------|-------------------------|-------------------|
| Black | 5.0' (1.52) | FT3BK5 |
| Black | 25.0' (7.62) | FT3BK25 |
| Brown | 5.0' (1.52) | FT3BR5 |
| Brown | 25.0' (7.62) | FT3BR25 |
| Beige | 5.0' (1.52) | FT3BG5 |
| Beige | 25.0' (7.62) | FT3BG25 |
| Gray | 5.0' (1.52) | FT3GY5 |
| Gray | 25.0' (7.62) | FT3GY25 |
| Yellow | 5.0' (1.52) | FT3Y5 |
| Yellow | 25.0' (7.62) | FT3Y25 |

Note: *ADA Compliant Section 4.5.2.

FloorTrak® 4

| Color | Length Feet (meters) | Catalog Number |
|--------|-------------------------|-------------------|
| Black | 5.0' (1.52) | FT4BK5 |
| Black | 25.0' (7.62) | FT4BK25 |
| Gray | 25.0' (7.62) | FT4GY25 |
| Yellow | 5.0' (1.52) | FT4Y5 |
| Yellow | 25.0' (7.62) | FT4Y25 |

FloorTrak® 10 (Heavy Duty)


| Color | Length Feet (meters) | Catalog Number |
|--------|-------------------------|-------------------|
| Black | 3.0' (.914) | FT10BK3 |
| Black | 5.0' (1.52) | FT10BK5 |
| Yellow | 3.0' (.914) | FT10Y3 |
| Yellow | 5.0' (1.52) | FT10Y5 |

Accessories

| Description | Catalog Number |
|---|----------------|
| 1" Wide, 75' Roll Double-Sided Adhesive Tape. | FTT1 |
| 2" Wide, 75' Roll Double-Sided Adhesive Tape. | FTT2 |

Dimensions

| FloorTrak® | FT2 in. (mm) | FT3 in. (mm) | FT4 in. (mm) | FT10 (Heavy Duty) in. (mm) |
|---------------------|-------------------------------|--------------------------------|---------------------------------|----------------------------------|
| Width (A) | 2.75" (69.9) | 3.00" (76.2) | 3.25" (82.6) | 5.6" (142.24) |
| Height (B) | .53" (13.5) | .75" (19.1) | 1.10" (27.9) | 1.7" (43.18) |
| Center Hole (Cx Dx) | .60" x .31" (15.2) x (7.9) | .75" x .50" (19.1) x (12.7) | 1.21" x .75" (30.7) x (19.1) | 1.81" x 1.25" (45.98 x 31.75) |



Specifications

| | |
|-----------------------|---------------------------------|
| Material | Rigid PVC. |
| Operating Temperature | 0°F to +120°F (-18°C to +49°C). |

Dimensions in Inches (mm)