



HBL – LED High Bay Series*

Heavy industrial, cast aluminum LED high bay with high ambient temperature up to 55°C.



10-Day Quick Ship Ordering Guide
Order Limit Per Fixture Selection: 50

HBL	-		-	U	-	A	-	2	-		-		-	070	-	ND	-		-	
-----	---	--	---	---	---	---	---	---	---	--	---	--	---	-----	---	----	---	--	---	--

SERIES	MOUNT	HUB	COLOR TEMP	DISTRIBUTION	DRIVE CURRENT	DIMMING	COLORS
HBL LED High Bay	A Pendant	2 ¾" Hub	3K 3000K 4K 4000K 5K 5000K	N Narrow W Wide	070 700 MA	ND Non Dimming	GR Gray WH White

NUMBER OF LEDS	VOLTAGE
60L 60 High brightness LEDs 72L 72 High brightness LEDs	U 120 - 277V

Notes: Voltage must be specified for Fusing and Occupancy Sensor compatibility. Refer to product spec sheet for 480V specification requirements.

Accessories - Order Separately

Catalog Number	Description
HOOK/LOOP	Fixture Mounting Hook
BLA-C4HLPX	Cord and Plug Set
LG2S	DUAL-LITE 250 VA LiteGear Emergency Lighting Inverter

Note: One (1) LED Highbay per LG2S

OPTIONS	
Fx	Fusing (Replace "x" with voltage - Refer to spec sheet for more info.)
ENCA	Frosted Acrylic Protective Lens
ENCG	Glass Protective Lens
OCS(X)	Occupancy Sensor
WG	Zinc Plated Wire Gaurd

Notes:
1. OCS unavailable with ENCA or ENCG options

*DLC® (DesignLights Consortium) Qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org.