

### 3L-S-D\*

The MOD™ 3L LED Surface Direct (3L-S-D) is part of the MODx family, which is an affordably-priced, full-featured offering with best-in-class attention to detail.



Click RDC/QS Guide for full details.



#### 10-Day Quick Ship Ordering Guide Order Limit Per Fixture Selection: 150




SERIES	MOUNTING	FIXTURE DISTRIBUTION	ROW LENGTH	MAX LENGTH IN ROW	DIRECT OPTICAL DISTRIBUTION	FINISH/COLOR <sup>2</sup>
3L MOD	S Surface	D Direct AD Asymmetric Direct	—' Enter in foot increments	<b>02</b> 2', 609mm <b>03</b> 3', 914mm <b>04</b> 4', 1219mm <b>05</b> 5', 1524mm <b>06</b> 6', 1829mm <b>08</b> 8', 2438mm	<b>SOF</b> Soft Diffuse Lens, Lambertian <b>REG</b> Regressed Diffuse Lens <b>BWO</b> Blade Baffle with Overlay <b>ASYM</b> Asymmetric Diffuse Lens <sup>3,4</sup> <b>BAT</b> Batwing Lens <b>DRP</b> Drop Lens	<b>C1</b> Matte White (Default) <b>C2</b> Textured Matte White <b>C3</b> Light Silver <b>C4</b> Machined Aluminum <b>C5</b> Carbon Black <b>C6</b> Textured Camera Black



COLOR TEMPERATURE	DIRECT OUTPUT/FT <sup>6</sup>	DRIVER	CIRCUITING	VOLTAGE
<b>27K</b> 2700K <sup>1</sup> <b>30K</b> 3000K <b>35K</b> 3500K <b>40K</b> 4000K <b>50K</b> 5000K <sup>1</sup> <b>27K9</b> 2700K, 90 CRI <sup>1</sup> <b>30K9</b> 3000K, 90 CRI <b>35K9</b> 3500K, 90 CRI <b>40K9</b> 4000K, 90 CRI <b>50K9</b> 5000K, 90 CRI <sup>1</sup> <b>2230TD</b> 2200K-3000K SpectraSync™ Dim-to-Warm <sup>5</sup> <b>2750T</b> 2700K-5000K SpectraSync™ Tunable White <sup>5</sup> <b>2765T</b> 2700K-6500K SpectraSync™ Tunable White <sup>5</sup>	<b>D030</b> 300 (min) to <b>D125</b> 1250 (max)	<b>D01</b> 1% Dimming, 0-10V <b>D00</b> 1% Dim-to-Off, 0-10V <b>D05</b> SpectraSync 5% Dimming, 0-10V <sup>9</sup> <b>DS1</b> 1% Dimming w/ Soft Start, 0-10V <b>DS0</b> 1% Dim-to-Off w/ Soft Start, 0-10V <b>LEC</b> Hi-lume 1% Ecosystem LED Driver <b>DALI</b> DALI <sup>1</sup> <b>DALIP</b> Powered by DALI (2.0) <sup>1</sup> <b>NDM</b> Non-Dimming	<b>1C</b> 1 Circuit	<b>UNV</b> Universal Voltage (120V-277V) <b>347</b> 347 Volt <sup>1,7</sup>

#### OPTIONAL



NIGHTLIGHT	EMERGENCY	THRU-WIRING
<b>NL</b> Nightlight Circuit Required. Enter quantity. 2NL = 2 nightlight circuits/row	<b>EF</b> 10W Emergency Battery Pack. Enter quantity. 2EF = 2 emergency batteries/row. <sup>8</sup>	<b>W1</b> No Thru Wire <b>W2</b> Provide Normal and Emergency/Nightlight Thru Wiring <sup>10</sup> <b>W3</b> Provide Normal Thru Wiring Only

Notes:

- 1 Additional lead time may be applicable. Contact factory.
- 2 Visit [www.litecontrol.com/finishes](http://www.litecontrol.com/finishes) for details.
- 3 Not Available with Patterns.
- 4 Must be ordered with AD.
- 5 Must be ordered with D05 Driver option; excludes 2' lengths and patterns.
- 6 Specifiable in 50 lumen increments. Reference the Performance Data Table for full performance offering and exceptions.
- 7 Excludes Emergency Battery Pack 'EF' Option. Excludes DALI, DALIP and Lutron (LEC) Dimming Drivers
- 8 EF - 10W battery powered driver. Provides a minimum of 90 minutes of emergency lighting. Inverter-Compatible. Provided by others.
- 9 Must be ordered with 2230TD, 2750T or 2765T Option
- 10 Only applicable when specified with Emergency/Nightlight.
- 11 Contact Factory for pattern configurations. Approval drawings required.