



## 3L-W-ID\*

The MOD™ 3L LED Wall Indirect/Direct (3L-W-ID) is part of the MODx family, which is an affordably-priced, full-featured offering with best-in-class attention to detail.



Click RDC/QS Guide  
for full details.



### 10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 150

<b>3L</b>	-	<b>W</b>	-		-		-		-		-	
<b>SERIES</b>	<b>MOUNTING</b>	<b>FIXTURE DISTRIBUTION</b>	<b>INDIRECT OPTICAL DISTRIBUTION</b>	<b>ROW LENGTH</b>	<b>MAX LENGTH IN ROW</b>	<b>DIRECT OPTICAL DISTRIBUTION</b>						
<b>3L</b> MOD	<b>W</b> Wall	<b>ID</b> Indirect/Direct <b>IAD</b> Indirect/Asymmetric Direct	<b>LPA</b> Low Peak Angle <b>LPAD</b> Low Peak Angle with Diffuser	—' Enter in foot increments	<b>02</b> 2', 609mm <b>03</b> 3', 914mm <b>04</b> 4', 1219mm <b>05</b> 5', 1524mm <b>06</b> 6', 1829mm <b>08</b> 8', 2438mm	<b>SOF</b> Soft Diffuse Lens, Lambertian <b>REG</b> Regressed Diffuse Lens <b>BWO</b> Blade Baffle with Overlay <b>ASYM</b> Asymmetric Diffuse Lens <sup>3,4</sup> <b>DRP</b> Drop Lens						

	-		-		-		-		-		-		-		-	
FINISH/COLOR <sup>2</sup>	COLOR TEMPERATURE	INDIRECT OUTPUT/FT <sup>6</sup>	DIRECT OUTPUT/FT <sup>6</sup>	DRIVER	CIRCUITING											
C1 Matte White (Default)	27K 2700K <sup>1</sup>	I030 300 (min)	D030 300 (min)	D01 1% Dimming, 0-10V	1C 1 Circuit											
C2 Textured Matte White	30K 3000K	to	to	D00 1% Dim-to-Off, 0-10V	2C 2 Circuit - Uplighting / Downlight											
C3 Light Silver	35K 3500K	I135 1350 (max)	D125 1250 (max)	D05 SpectraSync 5% Dimming, 0-10V <sup>9</sup>												
C4 Machined Aluminum	40K 4000K			DS1 1% Dimming w/ Soft Start, 0-10V												
C5 Carbon Black	50K 5000K <sup>1</sup>			DS0 1% Dim-to-Off w/ Soft Start, 0-10V												
C6 Textured Camera Black	27K9 2700K, 90 CRI <sup>1</sup>			LEC Hi-Lume 1% Ecosystem LED Driver												
	30K9 3000K, 90 CRI			DALI DALI <sup>1</sup>												
	35K9 3500K, 90 CRI			DALIP Powered by DALI (2.0) <sup>1</sup>												
	40K9 4000K, 90 CRI			NDM Non-Dimming												
	50K9 5000K, 90 CRI <sup>1</sup>															
	2230TD 2200K-3000K SpectraSync™ Dim-to-Warm <sup>5</sup>															
	2750T 2700K-5000K SpectraSync™ Tunable White <sup>5</sup>															
	2765T 2700K-6500K SpectraSync™ Tunable White <sup>5</sup>															

### OPTIONAL

	-		-		-		-		-		-		-		-	
VOLTAGE	NIGHTLIGHT	EMERGENCY	THRU-WIRING	DUST COVER												
UNV Universal Voltage (120V-277V)	NL Nightlight Circuit Required. Enter quantity. 2NL = 2 nightlight circuits/row	EF 10W Emergency Battery Pack. Enter quantity. 2EF = 2 emergency batteries/row. <sup>8</sup>	W1 No Thru Wire W2 Provide Normal and Emergency/ Nightlight Thru Wiring <sup>10</sup> W3 Provide Normal Thru Wiring Only	L1 Clear Acrylic Dust Cover Lens												
347 347 Volt <sup>1,7</sup>																

#### Notes:

- Additional lead time may be applicable. Contact factory.
- Visit [www.litecontrol.com/finishes](http://www.litecontrol.com/finishes) for details.
- Not Available with Patterns.
- Must be ordered with AD.
- Must be ordered with D05 Driver option; excludes 2' lengths and patterns.
- Specifiable in 50 lumen increments. Reference the Performance Data Table for full performance offering and exceptions.
- Excludes Emergency Battery Pack 'EF' Option. Excludes DALI, DALIP and Lutron (LEC) Dimming Drivers
- EF - 10W battery powered driver. Provides a minimum of 90 minutes of emergency lighting. Inverter-Compatible. Provided by others.
- Must be ordered with 2230TD, 2750T or 2765T Option
- Only applicable when specified with Emergency/Nightlight.
- Contact Factory for pattern configurations. Approval drawings required.