



## 4L-W-ID\*

The MOD™ 4L LED Wall Indirect/Direct (4L-W-ID) is part of the MODx family, which is an affordably-priced, full-featured offering with best-in-class attention to detail.



Click RDC/QS Guide for full details.



**10-Day Quick Ship Ordering Guide**  
Order Limit Per Fixture Selection: 150

| <b>4L</b> | <b>W</b> |  |   |                            |  |   |
|-----------|----------|--|---|----------------------------|--|---|
| SERIES    | MOUNTING | FIXTURE DISTRIBUTION   | INDIRECT OPTICAL DISTRIBUTION   | ROW LENGTH                 | MAX LENGTH IN ROW  | DIRECT OPTICAL DISTRIBUTION   |
| 4L MOD    | W Wall   | <b>ID</b> Indirect/Direct<br><b>IAD</b> Indirect/Asymmetric Direct | <b>LPA</b> Low Peak Angle<br><b>LPAD</b> Low Peak Angle with Diffuser | ' Enter in foot increments | <b>02</b> 2', 609mm<br><b>03</b> 3', 914mm<br><b>04</b> 4', 1219mm<br><b>05</b> 5', 1524mm<br><b>06</b> 6', 1829mm<br><b>08</b> 8', 2438mm | <b>SOF</b> Soft Diffuse Lens, Lambertian<br><b>REG</b> Regressed Diffuse Lens<br><b>BWO</b> Blade Baffle with Overlay<br><b>ASYM</b> Asymmetric Diffuse Lens <sup>3,4</sup><br><b>DRP</b> Drop Lens |

| FINISH/COLOR <sup>2</sup>       | COLOR TEMPERATURE  | INDIRECT OUTPUT/FT <sup>6</sup> | DIRECT OUTPUT/FT <sup>6</sup> | DRIVER  | CIRCUITING                                   |
|---------------------------------|--|---------------------------------|-------------------------------|---|--|
| <b>C1</b> Matte White (Default) | <b>27K</b> 2700K <sup>1</sup>                                    | <b>I030</b> 300 (min)           | <b>D030</b> 300 (min)         | <b>D01</b> 1% Dimming, 0-10V                          | <b>1C</b> 1 Circuit                          |
| <b>C2</b> Textured Matte White  | <b>30K</b> 3000K   | to                              | to                            | <b>D00</b> 1% Dim-to-Off, 0-10V                       | <b>2C</b> 2 Circuit - Uplighting / Downlight |
| <b>C3</b> Light Silver          | <b>35K</b> 3500K   | <b>I135</b> 1350 (max)          | <b>D125</b> 1250 (max)        | <b>D05</b> SpectraSync 5% Dimming, 0-10V <sup>9</sup> |  |
| <b>C4</b> Machined Aluminum     | <b>40K</b> 4000K   |                                 |                               | <b>DS1</b> 1% Dimming w/ Soft Start, 0-10V            |  |
| <b>C5</b> Carbon Black          | <b>50K</b> 5000K <sup>1</sup>                                    |                                 |                               | <b>DS0</b> 1% Dim-to-Off w/ Soft Start, 0-10V         |  |
| <b>C6</b> Textured Camera Black | <b>27K9</b> 2700K, 90 CRI <sup>1</sup>                           |                                 |                               | <b>LEC</b> Hi-lume 1% Ecosystem LED Driver            |  |
|                                 | <b>30K9</b> 3000K, 90 CRI  |                                 |                               | <b>DALI</b> DALI <sup>1</sup>                         |  |
|                                 | <b>35K9</b> 3500K, 90 CRI  |                                 |                               | <b>DALIP</b> Powered by DALI (2.0) <sup>1</sup>       |  |
|                                 | <b>40K9</b> 4000K, 90 CRI  |                                 |                               | <b>NDM</b> Non-Dimming                                |  |
|                                 | <b>50K9</b> 5000K, 90 CRI <sup>1</sup>                           |                                 |                               |   |  |
|                                 | <b>2230TD</b> 2200K-3000K SpectraSync™ Dim-to-Warm <sup>5</sup>  |                                 |                               |   |  |
|                                 | <b>2750T</b> 2700K-5000K SpectraSync™ Tunable White <sup>5</sup> |                                 |                               |   |  |
|                                 | <b>2765T</b> 2700K-6500K SpectraSync™ Tunable White <sup>5</sup> |                                 |                               |   |  |

### OPTIONAL

| VOLTAGE  | NIGHTLIGHT  | EMERGENCY   | THRU-WIRING   | DUST COVER                              |
|--|---|---|---|---|
| <b>UNV</b> Universal Voltage (120V-277V)<br><b>347</b> 347 Volt <sup>1,7</sup> | <b>NL</b> Nightlight Circuit Required. Enter quantity.<br>2NL = 2 nightlight circuits/row | <b>EF</b> 10W Emergency Battery Pack. Enter quantity. 2EF = 2 emergency batteries/row. <sup>8</sup> | <b>W1</b> No Thru Wire<br><b>W2</b> Provide Normal and Emergency/ Nightlight Thru Wiring <sup>10</sup><br><b>W3</b> Provide Normal Thru Wiring Only | <b>L1</b> Clear Acrylic Dust Cover Lens |

Notes:

- 1 Additional lead time may be applicable. Contact factory.
- 2 Visit [www.litecontrol.com/finishes](http://www.litecontrol.com/finishes) for details.
- 3 Not Available with Patterns.
- 4 Must be ordered with AD.
- 5 Must be ordered with D05 Driver option; excludes 2' lengths and patterns.
- 6 Specifiable in 50 lumen increments. Reference the Performance Data Table for full performance offering and exceptions.
- 7 Excludes Emergency Battery Pack 'EF' Option. Excludes DALI, DALIP and Lutron (LEC) Dimming Drivers
- 8 EF - 10W battery powered driver. Provides a minimum of 90 minutes of emergency lighting. Inverter-Compatible. Provided by others.
- 9 Must be ordered with 2230TD, 2750T or 2765T Option
- 10 Only applicable when specified with Emergency/Nightlight.
- 11 Contact Factory for pattern configurations. Approval drawings required.