



CVL- Curv Louvered

QS
10

10-Day Quick Ship Ordering Guide

Order Limit 1000' Linear Feet (See Alera Express Brochure for Limitations and Details.)

MODEL	DISTRIBUTION	SHIELDING	VOLTAGE	FINISH	OPTIONS
CVL Cürv Louvered	Blank 60% Uplight, 40% Downlight 0/100 0% Uplight, 100% Downlight ¹ 20/80 20% Uplight, 80% Downlight ¹ 40/60 40% Uplight, 60% Downlight ¹ 85/15 85% Uplight, 15% Downlight ¹ CLC Center Lamp Cover A/V Mode ¹	LD Low Iridescent Semi-Specular Louver (Std.) LS Low Iridescent Specular Louver	U 120V-277V	MW Matte White	DC Dust Cover (T8 and T5 with standard distribution only) ¹ SCE Sculpted End Cap (5 5/8" each) LR Left/Right Switching (2-Lamp only) IBOB Inboard/Outboard Switching (3-Lamp only) EL One T8 Emergency Battery Pack ^{2,4} EL5 One T5(HO) Battery Pack ^{2,4} EL5H One High Lumen Emergency Battery Pack ^{2,4} FO841 With T8 4100K Lamp Installed F5841 With T5/T5HO 4100K Lamp Installed FO835 With T8 3500K Lamp Installed F5835 With T5/T5HO 3500K Lamp Installed EMC Emergency Circuit ³ NLC Night Light Circuit ³ TBAR T-Bar Mounting B50LP One/Two T8 Emergency Battery Pack LP600 Emergency Battery Pack 600-1325 Lumens T5, T5HO, T8
ROW LENGTH	LAMP TYPE & PROFILE	MOUNTING METHOD	ADJUSTABLE CABLE LENGTH	BALLAST	
4 4' Single 8 8' Single — Indicate row length over 8' in 4' increments Note: Rows over 8' will be configured by Alera. Example: 16' will be (2) 8'. Alternate configurations: contact factory.	1T5 1 T5 Lamp 2T5 2 T5 Lamps 3T5 3 T5 Lamps 1T5HO 1 T5HO Lamp 2T5HO 2 T5HO Lamps 3T5HO 3 T5HO Lamps 1T8 1 T8 Lamp 2T8 2 T8 Lamps 3T8 3 T8 Lamps	CM Adj. Aircraft Cable Mount	48 48" 96 96"	E Electronic, Instant Start (Std. for T8) EP Electronic, Programmed Start (Std. for T5 & T5HO, optional for T8) ELW Electronic T8, 0.77BF, Low Watt, Instant Start EPLW Electronic T8, 0.77BF, Low Watt, Programmed Start ED_ADVVMK10 Electronic Dimming, Must Specify Voltage, Advance, Mark10 Powerline, 2T8 only EDUADVVMK7 Universal Voltage, Electronic Dimming, Advance Mark7(0-10v) 2T8 only	

Specifications apply. Please see Alera Express Program Rules page.

¹ Dust cover not available when using these optical distribution covers. Distribution varies with lamp and/or shielding.

² Specify voltage.

³ EMC/NLC is installed in right-hand side of 8' unit. Consists of 1 lamp ballast and one power drop.

⁴ EMC/NLC is not available for dimming on Alera Express.

⁵ See Alera Express Program Rules page for emergency battery pack information.

General Note: Not all options are available in every possible configuration.