



**Protects from**


-  high temperature cleaning
-  high pressure cleaning
-  chemicals
-  weather



## **IP69 Wash-Down Enclosures for Hygienic Applications**

For tough environments, get tougher than NEMA 4X

# Hygienic electrical enclosures for maximum safety



Built for the challenging demands of the food & beverage production environment, our wall-mount electrical enclosures stand up to rigorous washdown requirements. Go beyond the demands of NEMA 4X and even exceed the requirements for IP69!

Constructed of 304 stainless steel, the design features sloped surfaces to shed water, with no catch points to minimize bacterial growth. It allows for faster cleaning and easily handles high temperature/high pressure spray, and harsh cleaning chemicals.

For easier installation, the mounting points remain accessible even when an internal panel is installed. The reversible door features mounting points on both sides, making it easy to remove the door and convert from left to right hinging.



Replaceable silicone gasket

## Features

- IP69 compliant for high temperature and high pressure washdown
- Food-safe, high contrast blue nonporous external silicone gasketing
- Sloped design sheds water away from the enclosure
- Secondary gasketing for ultimate protection
- Internal, reversible hinges eliminate contamination points
- Internal, reversible hinges for access convenience
- Hygienic door latch design sheds water and includes silicone gaskets
- Pre-drilled mounting holes for standoffs
- Assembled in USA



Sloped design

# HYG-SS HYGIENIC Series


## Enclosures

Catalog Number	Size H X W X D
<b>HYG161608SS</b>	16 x 16 x 8 (406 x 406 x 203)
<b>HYG202008SS</b>	20 x 20 x 8 (508 x 508 x 203)
<b>HYG202010SS</b>	20 x 20 x 10 (508 x 508 x 254)
<b>HYG242408SS</b>	24 x 24 x 8 (610 x 610 x 203)
<b>HYG242410SS</b>	24 x 24 x 10 (610 x 610 x 254)
<b>HYG242412SS</b>	24 x 24 x 12 (610 x 610 x 305)
<b>HYG362408SS</b>	36 x 24 x 8 (914 x 610 x 203)
<b>HYG362410SS</b>	36 x 24 x 10 (914 x 610 x 254)
<b>HYG362412SS</b>	36 x 24 x 12 (914 x 610 x 305)
<b>HYG363010SS</b>	36 x 30 x 10 (914 x 762 x 254)
<b>HYG363012SS</b>	36 x 30 x 12 (914 x 762 x 305)
<b>HYG363016SS</b>	36 x 30 x 16 (914 x 762 x 406)

## Back Panels

Catalog Number		Size H X W X D
Painted	Stainless Steel	
<b>HP1616</b>	<b>HP1616SS</b>	11.00 x 11.00 (279 x 279)
<b>HP2020</b>	<b>HP2020SS</b>	15.00 x 15.00 (381 x 381)
<b>HP2424</b>	<b>HP2424SS</b>	19.00 x 19.00 (483 x 483)
<b>HP3624</b>	<b>HP3624SS</b>	31.00 x 19.00 (787 x 483)
<b>HP3630</b>	<b>HP3630SS</b>	31.00 x 25.00 (787 x 635)

Because this high-performance design is from Wiegmann, it's also available in custom sizes. Perfect for food & beverage, pharmaceutical, medical, or water treatment applications.



## Certifications/Standards

- UL508A Listed: Types 1, 3R, 4, 4X, 12
- cUL Listed per CSA C22.2 No. 14: Types 1, 3R, 4, 4X, 12
- NEMA/EEMAC Type 1, 3R, 4, 4X, 12
- EC 60529: IP69

# Get protection beyond NEMA 4X!

Contact your sales rep to find out more.



Proud members of the Hubbell family.

©2023 Wiegmann\*. All rights reserved.  
Hubbell and the Hubbell logo are registered trademarks or trademarks of Hubbell Incorporated.  
All other trademarks are the property of their respective owners.  
[hubbell.com/wiegmann/en](http://hubbell.com/wiegmann/en)  
USA 618-539-3193 | Canada 905-839-1138 | Mexico 52-55-9151-9999

EP-WIEG-MULT-BR-EN-01045

