




LAL Series

Linear LED Technology

for Harsh and Hazardous Environments





LAL/LALXE/LALC SERIES

KILLARK

LOW PROFILE LINEAR ALUMINUM LED • EXCLUSIVE DESIGN FEATURES

High temperature rated silicone gasketing provides Type 4X & IP66 sealing.



Diffused



Clear

2 Lens Choices:

- Clear for maximum lumens
- Diffused for glare control

Looping Terminal Blocks under Wiring Access Plate(s).

Optional Through Wiring

2 Access Plates for feed through wiring

Battery

E5, E13 and E26 models include internal Emergency battery systems to 50°C suitability

Surge

Standard with internal 20kA/10kA Supplemental Surge Protection

Endcaps standard with 1 x 3/4" hub. 1/2" NPT and M20 available.

End Caps include feet for direct **ceiling** mounting and safety cable connection



Shown with LAL-SB Height adjustable Swivel Brackets

Mounting **Slots** on back and at 45°

Earth

External Earth Ground for IECEx requirement



LINEAR LED TECHNOLOGY



LINEAR^{ITE}® *

* marca registrada MEXICO

FEATURES-SPECIFICATIONS

Applications

ABS (American Bureau of Shipping) type approval for use on decks, vessels, platforms, barges, ships and boats. Also suitable for docks and marinas.

Compliances

- UL-8750 for LED lighting
- ANSI/UL 1598(A)
- UL-844 Standard for lighting fixtures for hazardous locations, Class I, Division 2; Class II, Divisions 1 and 2; Class III
- CSA C22.2 no. 137-M1981 electric luminaires for use in hazardous locations
- IEC suffix Zone 2/21 to IEC 60079-0, 60079-15, 60079-31 Standards
- Enclosed and gasketed
- Type 3, 4X
- IP66

Materials

- Housing – one piece natural finish < .1% copper-free aluminum extrusion
- Endcaps & wiring – Access covers are copper-free (< .4%) aluminum with gray baked powder epoxy-polyester finish, electrostatically applied for complete uniform corrosion resistance.
- External screws are 316 stainless steel
- Lens – Impact resistant polycarbonate lens available in diffuse or clear

Supplemental **20KA/10KV Surge Protection** is **standard** (for 120-277 VAC models)
10KA/10KV Surge Protection (for 347-480 VAC)

LAL & LALxE Product Features

- LALxE models have “built-in” battery backup for 90 or 180 minute emergency exit
- Shallow design minimizes profile in work areas with low ceiling heights
- Diffuse Lens Standard to minimize glare; Clear Lens available
- Polycarbonate Single Lens 18W to 60W; Double Lens model 80W & 120W
- Slot Back Design allows multiple mounting access points across length – slots can also be used with 5/16” or 8mm bolts & nuts, 3 housing slots, 1 center back and 2 at 45°.
- Variety of mounting options including swivel brackets, wall, ceiling brackets, or beam clamps
- End Caps each have 2 mounting feet built-in plus a safety strap attachment point
- Standard unit End Caps each have single a 3/4” NPT hub, and fixture is furnished with one 3/4” close-up plug and two 3/4” to 1/2” reducers – provides out of the box 1/2” dead-end to 3/4” feed-through flexibility. Metric openings are available.
- Standard LALs have one wiring Access Plate for easy access to driver leads.

Class I, Div. 2, Groups A, B, C, D
Class I, Zone 2, Groups IIC, IIB, IIA
Class II, Div. 1 & 2, Groups E, F, G
AEx nAII, Ex nAII
Wet Locations
Type 4X
IP66
Marine Rated (US only)



Certified - File LR11713

IECEx Rated
Zone 2 and Zone 21 areas
Ex nA IIC T6 to T3, Gc
Ex tb IIC T95°C Db
Tamb -50°C < Tz < +65°C, IP66

IECEx Certificate
QPS 15.0010

ATEX Certificate
CML 15ATEX4081X (nA)
&
CML15ATEX3082X (tb)

LED Features and Standards


- Many Midpower LEDs blend light to simulate fluorescent tubes
- Chromaticity outputs:
standard – 5000K 70 CRI
3590 option – 3500K 90 CRI
3070 option – 3000K 70 CRI
- 3590 option is not available on the LALC
- 3070 option is only available on the LALC 15-45 watt.
- Energy Savings – High lumens per watt
- LED Array Life – 100,000+ hours with 70% initial lumens
- Long Fixture Life – 50,000 - 55,000 maintenance free hours
- Ambient suitability -40°C to 65°C (see tables). **-20°C to 50°C Ambient suitability for Emergency models.**
- Instant On – Including after power interruption
- World Voltage 120 - 277VAC 50/60Hz
- Solder-LESS LED Board Connections – Vibration Resistant



LAL/LALXE/LALC SERIES

KILLARK

CATALOG LOGIC




Energy Savings

LED VS FLUORESCENT WATTAGE & DELIVERED LUMENS					
CATALOG NUMBER	LUMENS	L/W	FLUORESCENT		LUMENS
LAL1830C	2479	138	40W	1x40W BX	2471
LAL2830C	3624	129	55W	1x55W BX	3766
LAL4530C	5515	122	56W	2x28T5	4676
			64W	2x32T8	4772
LAL6030C	7709	128	108W	2x54T5HO	8088
			120W	2x60T12HO	6965
LAL8030C	11032	138	162W	3x54T5HO	11619

ORDERING INFORMATION

ORDERING INFORMATION AND AMBIENT SUITABILITY							C1D2 ABCD/ ZONE 2 IIC, IIB, IIA			C1D2 GRPS. EFG SIMULTANEOUS			C2D1 GRPS. EFG			IEC ZONE 2			IEC ZONE 21		
CATALOG NUMBER W/ DIFFUSE LENS	WEIGHT LBS./KG	WATTS STD. POWER	LENGTH STYLE - INCHES (MM)	VOLTAGE	AMPS	DELIVERED LUMENS Diffuse/ Clear	40°C	55°C	65°C	40°C	55°C	65°C	40°C	55°C	65°C	40°C	55°C	65°C	40°C	55°C	65°C
LAL1830D	17.9 / 8.1	18	B-32.6 (828)	120-277VAC	0.15 - 0.06	2272 / 2479	T6	T6	T5	T4A	T4A	T4A	T4A	T4A	T4A	T6	T6	T5	T4	T4	T4
LAL1830D-L4-2AP	21.9 / 9.9		C-51 (1295)																		
LAL18E1330D-L4-2AP	31.9 / 14.5		C-51 (1295)																		
LAL2830D	17.9 / 8.1	28	B-32.6 (828)		0.23 - 0.10	3321 / 3624	T6	T6	T5	T4A	T4A	T4A	T4A	T4A	T4A	T6	T6	T5	T4	T4	T4
LAL2830D-L4-2AP	21.9 / 9.9		C-51 (1295)																		
LAL28E1330D-L4-2AP	31.9 / 14.5		C-51 (1295)																		
LAL4530D	17.9 / 8.1	45	B-32.6 (828)		0.38 - 0.16	5054 / 5515	T6	T5	-	T4A	T4A	T4A	T4A	T4A	T4A	T6	T5	T5	T4	T4	T4
LAL4530D-L4-2AP	21.9 / 9.9		C-51 (1295)																		
LAL45E1330D-L4-2AP	31.9 / 14.5		C-51 (1295)																		
LAL6030D	18.9 / 8.6	60	B-32.6 (828)		0.50 - 0.22	7064 / 7709	T6	T5	-	T4A	T4A	-	T4A	T4A	-	T6	T5	-	T4	T4	-
LAL6030D-L4-2AP	22.9 / 10.4		C-51 (1295)																		
LAL60E1330D-L4-2AP	32.9 / 14.9		C-51 (1295)																		
LAL8030D	34.5 / 15.6	80	D-57.9 (1471)		0.67 - 0.29	10110 / 11032	T6	T5	-	T4A	T4A	-	T4A	T4A	-	T6	T5	-	T4	T4	-
LAL80E1330D	44.5 / 20.2		D-57.9 (1471)																		
LAL80E2630D	54.5 / 24.7		D-57.9 (1471)																		
LAL12030D	36.5 / 16.6	120	D-57.9 (1471)		1.00 - 0.43	15090 / 16467	T6	T5	-	T4A	T4A	-	T4A	T4A	-	T6	T5	-	T4	T4	-
LAL120E1330D	46.5 / 21.1		D-57.9 (1471)																		
LAL120E2630D	56.5 / 25.6		D-57.9 (1471)																		
LALC1527D	12.03 / 4.49	15	A-18.73 (476)	12-24VDC	1.3-0.6	1503 / 1640															
LALC1530D				120-277VAC	0.15-0.06		T5	T4A	-	T4A	T4A	-	T4A	T4A	-	T5	T4	-	T4	T4	-
LALC1534D				120-250VDC	0.2-0.1																
LALC2027D		20	A-18.73 (476)	12-24VDC	1.7-0.8	2337 / 2550															
LALC2030D				120-277VAC	0.17-0.08		T5	T5	-	T4A	T4A	-	T4A	T4A	-	T5	T5	-	T4	T4	-
LALC2034D				120-250VDC	0.2-0.1																
LALC2527D		25	A-18.73 (476)	12-24VDC	2.1-1.0	3019 / 3294															
LALC2530D				120-277VAC	0.18-0.08		T5	T4A	-	T4A	T4A	-	T4A	T4A	-	T5	T4	-	T4	T4	-
LALC2534D				120-250VDC	0.2-0.1																
LALC3030D		30	A-18.73 (476)	120-277VAC	0.26-0.11	2726 / 2974	T5	T4A	-	T4A	T4A	-	T4A	T4A	-	T5	T4	-	T4	T4	-
LALC3530D		35	A-18.73 (476)		0.30-0.13	3261 / 3558	T5	T4A	-	T4A	T4A	-	T4A	T4A	-	T5	T4	-	T4	T4	-
LALC4030D		40	A-18.73 (476)		0.34-0.15	4152 / 4530	T5	T5	-	T4A	T4A	-	T4A	T4A	-	T5	T5	-	T4	T4	-
LALC4530D		45	A-18.73 (476)		0.38-0.17	5136 / 5604	T5	T5	-	T4A	T4A	-	T4A	T4A	-	T5	T5	-	T4	T4	-
LALC5030D		50	A-18.73 (476)		0.42-0.18	6039 / 6590	T5	-	-	T4A	-	-	T4A	-	-	T5	-	-	T4	-	-

CABLE GLAND ORDERING OPTIONS




CATALOG NUMBER	ENTRY THREAD SIZE (NPT)	CABLE ACCEPTANCE DETAILS	
		DIAMETER 'C'	
		MIN.	MAX.
MCX1B	1/2"	0.51" (13.0)	0.63" (16.0)
MCX1C	1/2"	0.60" (15.2)	0.82" (20.8)
MCX2	3/4"	0.73" (18.5)	1.03" (26.2)


For entire series, please see www.hubbell-killark.com.




DIMENSIONS AND ACCESSORIES




A: Dimensions
for LALC




B: Dimension
for Single Lens




C: Dimension
Single Lens
with approx.
4 foot length
and 2 access
covers



D: Dimension
Double Lens




End Views




ACCESSORIES AND REPLACEMENT PARTS

ACCESSORIES AND REPLACEMENT PARTS	
LAL-SB	Swivel Bracket Set w/ Adjustable Height; includes 5/16" bolts/nuts/lock-washers for attachment to LAL(C) "slots"; can also be attached to end cap mounting feet with FBO bolts.
LZCB	Ceiling Bracket Set with Stainless Steel Bolts to attach to LAL(C) "slots"
LZWB	Wall Bracket Set with Stainless Steel Bolts to attach to LAL(C) "slots"
LAL-BC	Steel/malleable Iron with Zinc electroplate for corrosion resistance; includes Stainless Steel Bolts to attach to LAL(C) "slots"
LAL-EB	Eyebolt Set with Stainless Steel Bolts to attach to LAL(C) "slots"
VMSC10	10' Stainless Steel Safety Cable with loop grip
LALG	Stainless Guard for 1 LAL Lens, order two for 2 lens models
LALCG	LALC Stainless Guard
LAL-LENSCLR	Single Clear Lens with Gasket for LAL Series
LAL-LENSDIF	Single Diffuse Lens with Gasket for LAL Series
LALC-LENSCLR	Single Clear Lens with Gasket for LALC Series
LALC-LENSDIF	Single Diffuse Lens with Gasket for LALC Series
LAL-RIG-CB	Rig Mounting Style Ceiling Bracket
LAL-RIG-WB	Rig Mounting Style Wall Bracket
RIG-LALC	Rig End Caps for LALC





LAL-SB on Center Slot



LAL-SB on 45° Slot




LAL-SB Dimensions – extended shown




Wall Bracket Set
Part Number LZWB
Stainless Steel (natural finish)




Ceiling Bracket Set
Part Number LZCB
Stainless Steel (natural finish)



VMSC10 Safety Cable



LAL-BC Beam Clamp





CERTI*LITE*® DESIGN

LIGHTING DESIGN SOFTWARE

Copyright ©2014 All Rights Reserved

- **Modern “Ribbon” Windows Interface with “Real Time” Calculations**
- **Easily import/export of CAD files (DWG/DXF/PDF)**
- **Enhanced photometric database with luminaire images and wireframes**
- **Ability to draw round or complex rooms and grids**
- **False Colors to indicate “Relative Brightness”**

See “Lighting Software link” at www.hubbell-killark.com to download

HKSB-LAL 03-19 © Killark, 2019

KILLARK®

Hubbell Killark
2112 Fenton Logistics Park Blvd. • Fenton, MO 63026
Phone: (314) 531-0460 • Fax: (314) 531-7164
www.hubbell-killark.com



Harsh & Hazardous