

ORDERING INFORMATION



ORDERING EXAMPLE: LNC2-P25-4K-FT-U-DB-SCP-8F

LNC2	-	-	-	-	-	-	-	-	-
SERIES	OUTPUT SELECTION	CCT/CRI	DISTRIBUTION	VOLTAGE	FINISH/COLOR	CONTROL OPTIONS	OPTIONS		
LNC2 Small LitePak LNC2	P15 15w Prismatic Refractor	3K 3000K, 70 CRI	FT Forward Throw	U 120-277V	DB Dark bronze textured	SCP ^{2,3} Occupancy Sensor Programmable (Dim)	EH ¹ Battery Backup Unit with Heater (-30°C)		
	P25 25w Prismatic Refractor	4K 4000K, 70 CRI		1 120V	BL Black textured		E ² Battery Backup Unit (0°C)		
	P35 35w Prismatic Refractor	5K 5000K, 70 CRI		2 208V	GYS Gray Smooth	PCU Universal Button Protocol	F ³ Fuse & Fuse-holder (not available with Battery Backup)		
				3 240V	PS Platinum smooth		CH Surface Conduit Hubs		
				4 277V	WH White textured				
					CC Custom Color				


1 Must specify voltage (120 or 277 only for E & EH)
 2 Must order minimum of one remote control to program dimming settings, 0-10V fully adjustable dimming with automatic daylight calibration and different time delay settings, 120-277V only
 3 PCU option not applicable, included in sensor

SPECIFY SCP/SWPM HEIGHT
 8F Up to 8ft mount height
 20F Up to 20ft mount height


DIMENSIONS



Standard Unit



With Sensor Options



With Battery Backup

A	B	C	D	E	WEIGHT STD.	WEIGHT SENSOR	WEIGHT WITH BBU
5.54"	10.16"	6.33"	7.64"	9.10"	7.0 lbs.	7.5 lbs.	9.5 lbs.
40.7mm	258 mm	160.7mm	194mm	231mm	3.2 kg	3.4 kg	4.3 kg

LITEPAK

Family



FOR MORE INFORMATION ABOUT LNC2 PRISMATIC:



- ALERA LIGHTING
- HUBBELL INDUSTRIAL LIGHTING
- ARCHITECTURAL AREA LIGHTING
- HUBBELL OUTDOOR LIGHTING
- BEACON PRODUCTS
- KIM LIGHTING
- COLUMBIA LIGHTING
- KURT VERSEN
- COMPASS
- LITECONTROL
- DUAL-LITE
- PRESCOLITE
- HUBBELL CONTROL SOLUTIONS
- WHITEWAY

Due to our continued efforts to improve our products, product specifications are subject to change without notice.

LITEPAK

PRISMATIC




The award winning Litepak LNC2 luminaire now features an industry leading prismatic refractor option for the ultimate combination of performance and visually appealing perimeter illumination. Additionally, the LNC2 can be specified with energy saving controls and/ or egress options. The Litepak LNC2 luminaire is available in multiple lumen packages providing safety, security and identity.

- Prismatic refractor lens for optimal visual comfort and performance
- Optional photocell, occupancy sensor and battery backup
- Optional Four - 1/2" threaded surface conduit entries
- IP65 rated
- DLC qualified*



Prismatic Lens
Specially design prismatic refractor lens provides improved visual comfort and superior light output and performance.




Quick Mounting
Quick-mount – easy mounting without opening fixture. Attach adapter plate to wall, connect wires, hang fixture and tighten set screws.



Photo Control
Optional factory installed top mounted button photocontrol.



PERFORMANCE



CONTROLS

SCP programmable sensor offers greater control and energy savings including adjustable delay and dimming levels.



EGRESS/BATTERY BACK UP

Battery backup unit features Spectron self diagnostic push-to-test status indicator and delivers Life Safety Code average illumination of 1.0 FC. EH option includes heater for ambient temperatures as low as -30°C.



* DesignLights Consortium (DLC) qualified, consult DLC website for more details: <http://www.designlights.org/OPL>