

Options

Price List 6300AM * November 2002 * Repl. Nov. 1998 * Discount Schedule E11

Optional items for models:

LXi 1100, 1200, 1300, 1400, 1700, 1800, 1900

LXi 2100, 2200, 2300, 2400, 2700, 2800, 2900

Option Symbol	Description	List Price
Miscellaneous		
A	Test timer with drain solenoid and test pushbutton	\$540
A1	Same as A without test pushbutton	\$500
B	Load shed contacts with pump start delay (without transfer switch)	\$185
B1	Same as B when with transfer switch	\$550
	Digital amps and volts display	Standard
	Digital pressure display	Standard
	Sequence start, adjustable time delay (field selectable)	Standard
	Remote/Deluge valve start	Standard
F1	Series pumping	
F2	Low zone controller	\$44
F3	Mid zone controller	\$448
	High zone controller	\$404
	Space heaters - price includes line circuit breaker. Must be connected to separate power source.	
	120 Volt	
G1	Space heater only	\$200
G2	Space heater with thermostat	\$320
G3	Space heater with humidistat	\$320
	Space heaters (with transfer switch)	
G4	Space heater with circuit breaker	\$400
G5	Space heater with thermostat	\$640
G6	Space heater with humidistat	\$640
	240 Volt	
G7	Space heater only	\$200
G8	Space heater with thermostat	\$320
G9	Space heater with humidistat	\$320
	Space heaters (with transfer switch)	
G10	Space heater with circuit breaker	\$400
G11	Space heater with thermostat	\$640
G12	Space heater with humidistat	\$640
	Manual stop (omit run period timer, field selectable)	Standard
	Increased short circuit ratings	
J1	150,000 amps RMS symmetrical	\$1,350
J2	200,000 amps RMS symmetrical	\$2,550
K	Tropicalization	\$400
	Special packaging	
L1	Export Crating (without transfer switch)	\$750
L2	Export Crating (with transfer switch)	\$900
Enclosures		
M1a	Type 3R	\$100
M1b	Type 3R (with transfer switch)	\$200
M2a	Type 12	\$100
M2b	Type 12 (with transfer switch)	\$200
M3a	Type 4	\$1,200
M3b	Type 4 (with transfer switch)	\$2,400
M4a	Type 4X stainless steel	\$3,000
		LXi 1100, 1300, 1400
		LXi 1200, 1700, 1800, 1900
M4b	Type 4X stainless steel (with transfer switch)	\$6,000
		LXi 2100, 2300, 2400
		LXi 2200, 2700, 2800, 2900
M5a	Type 4X painted steel	\$1,350
M5b	Type 4X painted steel (with transfer switch)	\$2,530
Pressure Transducers		
N1	25-600 psi, fresh water	No charge
N2	10-300 psi, stainless steel, sea water / foam	\$280
N3	25-600 psi, stainless steel, sea water / foam	\$480

Option Symbol	Description	List Price
Pressure Recorders		
	LXi controllers inherently record pressure as part of the event data logging feature. The pressure history can be downloaded to a lap top computer or printer.	Standard
Local Alarms and Contacts for remote Indication All contacts include one normally open and closed form "C" contact		
R1	Pump room temperature alarm with thermostat, light and contact Pump run light	\$290 Standard
R3	Pump run contacts (2 sets of form "C" contacts are standard)	\$90
R5	Phase/power failure contacts (2 sets of form "C" contacts are standard)	\$90
R6	Low system pressure contacts Low system pressure light	\$90 Standard
R8	Pump fail to start contacts Pump fail to start light	\$120 Standard
R10	Phase reversal contacts (2 sets of form "C" contacts are standard) Phase reversal light	\$90 Standard
R12	Pump overload contacts	\$190
R14	Reservoir low contacts (initiating switch not included)	\$90
R15	Reservoir low light (initiating switch not included)	\$120
R16	Low suction pressure contact (initiating switch not included) Low suction pressure light (initiating switch not included)	\$90 Standard
	Common trouble contacts	Standard
R19	Common trouble light	\$120
R20	Common trouble audible alarm	\$120
R21	Transfer switch contacts, 1-N.O. contact on Normal and Emergency	\$90
R22	Power failure light (Requires separate 120V supply)	\$290
	Annunciator group - provides visible indication of the following conditions Low pressure, local start, remote start, emergency manual start lockout on, pump run, & run timer on.	Standard
RC	Chicago code - provides built in audible alarm for phase / control power failure, phase reversal, pump run, with alarm silence switch.	\$195
Miscellaneous		
V	Lamp test pushbutton	Standard
W	Printer	No Charge
Y	Audible alarm	\$190
X	Low Suction Pressure switch, installed and wired for low suction shutdown	\$250
	Special option	Consult factory
Special Labeling		
S1	ULC / CSA labels	N/C
S2	New York City MEA label	N/C
S3	Foam service - pressure switch not included, requires N/C contact to start pump	N/C
S4	Foam service - pressure switch included	N/C

Prices subject to change without notice.