

MODTM X

2L 3L 4L 6L

LITECONTROL
making light work™



HUBBELL
Lighting

MOD™x

Featuring **four aperture widths**, a selection of **mounting types**, **output distributions**, **lumen output**, **diffuser types**, along with dozens of features and options, the **MOD™x family** is the perfect solution to any space or environment.

HISTORY OF QUALITY

Litecontrol developed its original architectural slot more than five decades ago. The first MOD™ delivered a cost-sensitive, full-family solution to ambient lighting.

The MOD™x family represents a modernization of this timeless form with the same original value proposition: affordably-priced, full feature offering and best-in-class attention to detail.

A COMPREHENSIVE FAMILY

Full-featured offering with **four widths** & **five mounting types**

PERFORMANCE

Outputs up to **1350 lm/ft** and efficacies up to **118 lm/w Direct** and **148 lm/w Indirect**

ATTENTION TO DETAIL

Industry-best **diffuser uniformity**, **simple & consistent fixture alignment**, **elimination of light leak** and a **focus on fit/finish**

VI TECHNOLOGY & TWO SDCM COLOR VARIATION

Accommodate a wide **variety of applications** to your exact specifications














PRODUCT
FEATURES

MODTM X



PENDANT MOUNT



2
3
4
6

2
3
4
5
6
8

Direct
Indirect/direct

Standard
Low Peak Angle
Low Peak Angle w/ Diffuser

Lambertian
Asymmetric
Batwing

Soft Diffuse
Regressed
Blade Baffle with Overlay
Drop
Asymmetric
Batwing

Matte White
Textured Matte White
Light Silver
Machined Aluminum
Carbon Black
Textured Camera Black
Custom Color

27K
30K
35K
40K
50K
80CRI
90CRI
SpectraSync™

Indirect
2L: 300-1250
3/4/6L: 300-1350

Direct
2L: 300-1000
3/4/6L: 300-1250

0-10V
Lutron
Dali

NX Distributed Intelligence™
Daylight
Occupancy

347V
Emergency
Dust Cover

Lambertian
SOE/REG/
BWO/DRP


Asymmetric
ASYM

Batwing
BAT


Standard
STD

Low Peak Angle
LPA/LPAD

WALL
MOUNT



Aperture Widths




- 2
- 3
- 4
- 6

Fixture Lengths



- 2
- 3
- 4
- 5
- 6
- 8

Fixture Distribution



- Direct
- Indirect/direct

Uplight Distribution



- Low Peak Angle
(only on room side)
- Low Peak Angle with
Diffuser (only on room side)

Downlight Distribution



- Lambertian
- Asymmetric

Downlight Diffuser



- Soft Diffuse
- Regressed
- Blade Baffle with Overlay
- Drop
- Asymmetric

Finish




- Matte White
- Textured Matte White
- Light Silver
- Machined Aluminum
- Carbon Black
- Textured Camera Black
- Custom Color

Color Temperature



- 27K
- 30K
- 35K
- 40K
- 50K
- 80CRI
- 90CRI
- SpectraSyncTM

Outputs



- Indirect
- 2L: 300-1250
- 3/4/6L: 300-1350
- Direct
- 2L: 300-1000
- 3/4/6L: 300-1250

Driver

- 0-10V
- Lutron
- Dali

Controls

- NX Distributed IntelligenceTM
- Daylight
- Occupancy

Additional Options

- 347V
- Emergency
- Dust Cover

Direct



Lambertian
SOF/REG/
BWO/DRP



Asymmetric
ASYM


Indirect/Direct




Low Peak Angle
LPA/LPAD



SURFACE MOUNT



Aperture Widths



2
3
4
6

Fixture Lengths



2
3
4
5
6
8

Fixture Distribution



Direct

Downlight Distribution



Lambertian
Asymmetric
Batwing

Downlight Diffuser



Soft Diffuse
Regressed
Blade Baffle w/ Overlay
Drop
Asymmetric
Batwing

Finish



Matte White
Textured Matte White
Light Silver
Machined Aluminum
Carbon Black
Textured Camera Black
Custom Color

Color Temperature



27K
30K
35K
40K
50K
80CRI
90CRI
SpectraSyncTM

Outputs



Direct
2L: 300-1000
3/4/6L: 300-1250

Driver

0-10V
Lutron
Dali

Controls

NX Distributed IntelligenceTM
Daylight
Occupancy

Additional Options

347V
Emergency

Direct




Lambertian
SOF/REG/
BWO/DRP



Asymmetric
ASYM



Batwing
BAT





90
120
135

Non-Illuminated (2L-P)




C (90° corner)
T
X
V (120° corner)
Y (120°)




CORNERS & PATTERNS

PENDANT, WALL & SURFACE FEATURES




UPLIGHT OPTIONS

The Standard (STD) uplight distribution creates a lambertian output above the fixture. The Low Peak Angle (LPA) uplight distribution allows for a batwing shaped output, perfect for closer to ceiling applications. The LPA option allows for less fixtures in your space, changing the recommended fixture to fixture spacing from 12' to 16'.




DIFFUSER UNIFORMITY


Calculated lens-to-LED source distance creates a uniform diffuser appearance regardless of fixture width.




DIFFUSER OPTIONS




SOF - Standard




REG - Regressed




BWO - Baffle



DRP - Drop




ASYM - Asymmetric




BAT - Batwing

PATENTED END CAP DESIGN



HOUSING X-BRACKET

- Captures suspension cable gripper
- Blocks light leaks, provides row mounting alignment
- Row joining & end cap plate attachment
- LED reflector mounting




NON-ILLUMINATED BOXES










Available in a 90° square version to create a 90° corner (C), T and X shapes along with a 120° triangle version to create a 120° corner (V) and Y shapes. Available on 2L-P only.

SIMPLE ROW JOINING








Center X-bracket design allows for Male/Female connection to straighten out row joined fixtures and block light leak at fixture seams.

Extruded aluminum housing





RECESSED MOUNT



2L 3L 4L 6L

Flush 2" Regressed 3" Regressed 4" Regressed

Finish

Color Temperature

Outputs

Driver

Controls

Additional Options

Matte White
Textured Matte White
Light Silver
Machined Aluminum
Carbon Black
Textured Camera Black
Custom Color


27K
30K
35K
40K
50K
80CRI
90CRI
SpectraSyncTM

Direct
2L: 300-1000
3/4/6L: 300-1250

0-10V
Lutron
Dali

NX Distributed IntelligenceTM
Zigbee
Daylight
Occupancy



347V
Emergency
Chicago Plenum Rated
IC rated



PERIMETER
WALL/SLOT
MOUNT




CORNERS
& PATTERNS





90
120
135




90



Inside field cut corner (85-160°)
Outside field cut corner (70-160°)





FORMED STEEL RECESSED DESIGN


- Extruded snap in lens is simple to pop in and out
- Vertical magnetic end cap design allows for easy diffuser removal from below the ceiling
- Each fixture has a unique flange welded on for a perfect fit in any ceiling




Drywall




Plaster Trim



Grid Ceiling
15/16" LG




Grid Ceiling
9/16" NG



Grid Ceiling
9/16" Screw Slot


RECESSED CEILING TYPE OPTIONS

Available in five ceiling type options: three grid types, a drywall installation and the trimless finish of the plaster trim



WALL WASH

Our ASYM option can be utilized to wall wash in your space



SIMPLE AND CLEAN WIRING WITH CUSTOM DESIGN LED BOARDS

Breakable-board technology allows for 3" increment specification in recessed & Wall/Slot® products



SpectraSync™ is an easy and intuitive white tuning solution offered in two modes to accommodate a variety of applications.



Tunable White

Tunable White offers users the ability to tailor CCT to their personal preference, enhancing task visibility, material and colors, or the aesthetics of the space. (Available with 2700K-5000K or 2700K-6500K)



Dim to Warm

Dim to Warm mimics the familiar warming effect that occurs with traditional incandescent sources as they are dimmed. (Available with 2200K-3000K)



Variable Intensity Technology

Vi Story

Variable Intensity Technology is a simple method for specification of luminaire lumens and wattage to meet the exacting demands of each project. Vi Technology provides verifiable wattage for compliance with programs, agencies and state and local codes.



OVER 50 YEARS OF DEVELOPMENT

Early 1960s**Original MOD Family Introduced**

The MOD family was designed to be an affordably-priced, full-featured offering with best-in-class attention to detail.

2016**Next Generation of MODx Family**

Improved design, upgraded linear LED board technology, driver enhancements, addition of the 3/4/6L in pendant, wall, surface, recessed and 90° corners.

2019**Perimeter Mount & Expansion**

Additional perimeter mount option with 4 ceiling regression depths and a narrow distribution. New illuminated angled corners, non-illuminated 2L joiners for unique pattern configurations, batwing downlight distribution and a ½" drop lens diffuser.

2009**Introduction of LED MOD**

The introduction of LED boards allows for greater efficiency, versatility and housing options.

Early 2018**2" Aperture Design Introduced**

A slim 2" profile, in a comprehensive pendant, wall, surface, and recessed product offering, joins the MODx family.



ALERA LIGHTING

ARCHITECTURAL AREA LIGHTING

BEACON PRODUCTS

COLUMBIA LIGHTING

COMPASS

DUAL-LITE

HUBBELL CONTROL SOLUTIONS

HUBBELL INDUSTRIAL LIGHTING

HUBBELL OUTDOOR LIGHTING

KIM LIGHTING

KURT VERSEN

LITECONTROL

PRESCOLITE

LITECONTROL
making light work™

701 Millennium Blvd. Greenville, SC 29607
Tel 864.678.1000
www.litecontrol.com

HL18000051 1/19

Copyright © 2019 *Litecontrol*, a division of Hubbell Lighting, Inc. All rights reserved. Please refer to online specifications for most up-to-date content as specifications are subject to change without notice.