



*L*Parkway
SQUARE® architectural
arealighting

ARCHITECTURAL AREA LIGHTING



The
ultimate in
style and
technological
sophistication

ENERGY EFFICIENCY

The light sources employed in the Parkway Square family of fixtures are the most efficient sources commercially available today, including energy efficient LED, metal halide and compact fluorescent. The result is more light with less energy consumption.

LONGEVITY

AAL manufactures its products to have a life span as long as the buildings and spaces they illuminate. The primary material used for all our products is aluminum to resist corrosion and the need for maintenance. Aluminum will not need the periodic refinishing required of steel products that will eventually rust and corrode. All our internal parts and fasteners are made of aluminum or stainless steel. Lamp enclosures are kept dust free and dry to prevent light degradation and maintain a high level of energy efficiency.

SUSTAINABILITY

AAL develops our products with recycling and resource management in mind. We recycle all incoming packaging materials. Our state-of-the-art finishing system uses eco-friendly cleansing and preparation chemicals that are harmless enough to send to the drain without further processing. Finally, AAL makes the Parkway Square, like all AAL products, with renewable materials such as aluminum and stainless steel.

US Patents D728,143 S, D715,475 S, D707,882 S, D705,476 S, D689, 646 S, US D676,588 S, D662, 647 S, D647,235 S





WALL SCONCE



ACCENT (SMALL) SCALE



PEDESTRIAN (MEDIUM) SCALE



BOLLARD

TABLE OF Contents

Design Excellence.....	6
Optical Systems	8
Configured by You.....	14
Elevated Scale.....	18
Pedestrian Scale	20
Accent Scale	22
Mounting Options.....	24
Sconce	28
Bollard.....	30



PKWS-ANG-GLA-18LED-DB-DSOF-SSP-PR4



PKWM-ANG-Y5VD-32LED-MDB-PR4



Excellence refined

The appointed styling
of Parkway Square is
more on parallel with
a fine piece of art than
an outdoor luminaire.

Design Excellence

Beneath its refined and tastefully styled exterior, **Parkway Square** holds true the promise of high performance and long life for which AAL is known.






Quality

Craftsmanship



The attention to detail and quality craftsmanship that goes into every AAL fixture ensures the luminaires will last as long as the buildings and spaces they illuminate.

Optical Systems



Parkway Square offers a wide variety of optical systems designed to meet the lighting requirements of any project. Parkway Square employs the most energy efficient sources on the market, including HID, LED, and compact fluorescent.

- LED Optical System
- Horizontal Optical System
- Vertical Optical System
- Indirect Optical System

HORIZONTAL OPTICAL SYSTEM

Parkway Square features AAL's exclusive horizontal reflector system


Available in four IES distribution patterns, Parkway Square's horizontal optical system provides maximum efficiency and flexibility to precisely illuminate pedestrian areas, streets and complete project site lighting. Certain configurations of the horizontal reflector models meet IES standards for full cutoff, addressing requirements for glare control, light trespass, and light pollution.

- Optics rotate on 90° centers
- Full cutoff options available
- Wide variety of efficient lamp sources
- Four IES distribution patterns



Parkway Square offers a variety of dark sky friendly options

DISTRIBUTION PATTERNS AVAILABLE



TYPE 2

TYPE 3

TYPE 4



TYPE 5

Optical Systems

Parkway Square Indirect has a **concealed light source** for comfortable, glare free illumination. The enclosed optical module eliminates the problem of light deterioration common on open lens indirect fixtures. Parkway Square's indirect optical system is perfect when even, uniform illumination, with minimal glare, is required.

INDIRECT OPTICAL SYSTEM

DISTRIBUTION PATTERNS AVAILABLE




INDIRECT

VERTICAL OPTICAL SYSTEM



GLASS REFRACTOR




DIFFUSER

Glass Refractor and Diffuser


Parkway Square's glass refractor lens is available in IES Type 3 and Type 5 distribution patterns and is a perfect solution for general lighting. The glass diffuser provides a decorative touch and effectively conceals the light source.

DISTRIBUTION PATTERNS AVAILABLE

GLASS REFRACTOR



TYPE 3



TYPE 5

Optical Systems



Parkway
SQUARE®

LED

OPTICAL SYSTEM

MEDIUM SCALE
P K W M
SMALL SCALE
P K W S

BOLLARD
P K W B
SCONCE
P K S A / P K S P

Optimal Performance and Energy Efficiency

Precision engineering harnesses the power of today's brilliant, high-efficiency LED's to deliver maximum performance and reduce energy consumption.

Parkway Square presents a versatile approach to light delivery, emphasizing high performance, uniform illumination and flexibility in design with four distribution patterns available in a variety of standard color temperatures.

- Long lasting highly efficient LEDs
- Up to 5300 delivered lumens
- Up to 69 lumens per watt
- Three standard color temperatures: 5100K, 4200K or 3000K
- Standard IES distributions - Type 2, 3, 4, 5

Quality Engineering


The Parkway Square stands above other traditional lanterns available on the market today. The quality tested AAL design provides a lifetime of energy efficient, trouble free operation and a long lasting LED optical system.

- IP66 optical system
- Internal surge protection
- 120-277 AC input voltage at 50/60Hz
- Upgrade Kit available for existing installations
- Integral thermal protection




Configured by You


The unique design of **Parkway Square** allows you to mix-and-match between four optical systems, three hood styles, and five decorative screen options to truly customize your luminaire.



1 *ANGLED HOOD - ANG*



2 *STRAIGHT HOOD - STR / INDIRECT - IND*
(underside of Indirect hood in high reflectance white)



3 *DOUBLE HOOD - DBL*

Hoods

1 | **SELECT** DESIRED HOOD

Parkway Square features three designer hoods, each with a distinct design statement, available in painted aluminum to match the fixture, or natural copper and stainless steel.



*STAINLESS STEEL
Hood - STS*



*COPPER
Hood - COP*

Specify hoods in either painted aluminum, natural copper, or stainless steel to complement other design elements on the project.

To customize the look of the luminaire, add a decorative screen in either a contemporary style such as Wheat or Infinity, or a more traditional style with Offset, Trio or Shutter. Submit your own design or logo to truly customize the luminaire. Each screen is created with a water laser to ensure smooth lines and consistency with each luminaire.

Optics

2 | SELECT OPTICAL SYSTEM

Choose the optical system that **best suits** your project needs.

Vertical/ Horizontal
LED/NON-LED/Indirect



Configured by You



Screens

3

SELECT

DECORATIVE SCREEN
OPTION



1 TRIO - DSTR



2 WHEAT - DSWH



3 INFINITY - DSIN




4 OFFSET - DSOF



5 CUSTOM - DSCS



STAINLESS STEEL
Screen - SSP



COPPER
Screen - CPR

Specify screens
in either painted
aluminum,
natural copper, or
stainless steel.

To customize the look of the luminaire, add a decorative screen in either a contemporary style such as Wheat or Infinity, or a more traditional style with Offset or Trio. Submit your own design or logo to truly customize the luminaire. Each screen is created with a water laser to ensure smooth lines and consistency with each luminaire.

Parkway
S Q U A R E™


Contemporary Styling

Select the double hood and Wheat decorative screen in stainless steel with medium grey finish for a contemporary luminaire ensemble.


Traditional Styling

Specify the angled hood and Offset screen in copper with dark bronze finish for more traditional appeal.

Elevated Scale



LUMINAIRE	PKSP-UBDS/ PKSA-DB (Large/Small Sconce)	PKWM (Pedestrian)	PKWS (Accent)	PKWM(2) (Pedestrian)
HOOD	—	ANG	STR	ANG
OPTICS	30LED-BW/15LED-BW	Y3VC-32LED-5K	GLA 18LED-BW	Y5HC-32LED-5K
OPTIONS	DSTR	—	—	—
ARM	—	PSA-BU	—	PSA-BU(2)
POLE	—	PR4-4R12/BC5-4	PS3-3S8	PS4-4S16/ACBCS



PKWS (Accent)

PKWM(2) (Pedestrian)

PKWB (Bollard)

PKWM/PKWS (Pedestrian/Small)

DBL

STR

—

DBL/ANG

GLA 18LED-BW

Y5VC-5K

GLA 12LED-BW

Y5VC-32LED-5K/GLA 18LED-BW

DSIN

—

DSOF

DSWH

—

PSA-TU(2)

—

PSWM-BD/PSWM-TD

PS3-3S10


PS4-4S12/ACBCS

—

—


Pedestrian Scale

Medium Housing



PKWM


HOOD



ANG – Angled Hood



STR – Straight Hood



DBL – Double Hood

ORDERING EXAMPLE – PEDESTRIAN (MEDIUM) SCALE

1. LUMINAIRE & HOOD PKWM-DBL	2. OPTICS Y3VC	3. LIGHT ENGINE 32LED-3K	4. COLOR MDB	5. OPTIONS DSIN-COP-CPR	6 MOUNTING PSA-TU
---------------------------------	-------------------	-----------------------------	-----------------	----------------------------	----------------------

ORDERING INFORMATION

1. LUMINAIRE AND HOOD

PKWM-ANG Angled Hood	PKWM-DBL Double Hood	PKWM-STR Straight Hood	PKWM-IND Indirect Hood (HID -3 or -5 only)
-----------------------------	-----------------------------	-------------------------------	---

2. LED OPTICS – choice of distribution and lensing

DISTRIBUTION

Y2 IES Type II distribution	Y3 IES Type III distribution
Y4 IES Type IV distribution	Y5 IES Type V distribution

LENSING

HC Clear flat lens	VC Clear vertical lens
HD Diffused flat lens	VD Diffused vertical lens

3. LED LIGHT ENGINE – choice of CCT and lumen package

COLOR TEMPERATURE

32LED-3K 3000K CCT	32LED-4K 4000K CCT	32LED-5K 5000K CCT
---------------------------	---------------------------	---------------------------

LUMEN PACKAGE

700 388mA, 73 watts ²	525 525mA, 58 watts ¹
500 500mA, 53 watts ²	350 350mA, 38 watts ¹

¹ - Requires selection of vertical lens optics

² - Requires selection of flat lens optics

³ - HID only

2. HID OPTICS

CLEAR VERTICAL LENSING

GLA Internal frosted glass diffuser, symmetric distribution
GR3 Internal glass refractor, asymmetric distribution
GR5 Internal glass refractor, symmetric distribution

-3 Indirect hood and optics, asymmetric distribution
-5 Indirect hood and optics, symmetric distribution

3. HID LAMP / BALLAST

METAL HALIDE

70MH 70 watt ballast	150PSMH 150 watt pulse start ballast
70MHEB 70 watt electronic ballast	150MHEB 150 watt electronic ballast
70MHT6 70 watt ballast, G12 base	150PSMHT6 150 watt pulse start ballast, G12 base
70MHT6EB 70 watt electronic ballast, G12 base	150MHT6EB 150 watt electronic ballast, G12 base
100MH 100 watt ballast	
100MHEB 100 watt electronic ballast	

HIGH PRESSURE SODIUM

70HPS 70 watt ballast
100HPS 100 watt ballast
150HPS 150 watt ballast

OTHER

CF 26,32 or 42 watt compact fluorescent
140CO 140 watt CosmoPolis ballast

4. COLOR

WT Arctic White	BL Black	BLT Matte Black	DGN Dark Green	DB Dark Bronze
WDB Weathered Bronze	MDB Bronze Metallic	VBU Verde Blue	CRT Corten	MAL Matte Aluminum
MG Medium Grey	AGN Antique Green	LG Light Grey	RAL Premium Color	CUSTOM Custom Color

5. OPTIONS

DECORATIVE SCREEN

DSIN Infinity pattern ¹	DSTR Trio pattern ¹	DSOF Offset pattern ¹	DSSH Shutter pattern ¹	DSWH Wheat pattern ¹	DSCS Custom pattern ¹
---	---------------------------------------	---	--	--	---

HOOD FINISH

COP Hood in natural copper, brushed horizontal grain	STS Hood in natural Stainless Steel, brushed horizontal grain
---	--

SCREEN FINISH

SSP Decorative screen in natural Stainless Steel, brushed horizontal grain ¹	CPR Decorative screen in natural Copper, brushed horizontal grain ¹
--	---

CONTROLS

SCP Sensor Control Programmable pole accessory is available to provide occupancy detection for outdoor applications meeting California Title 24. For complete spec sheet and ordering information, visit www.aal.net/products/sensor_control_programmable/
--

OTHER

FS1 Single fuse holder	ULS Upper lens shield ¹	HSS House side shield ¹	LDL Lightly diffused lens ³
-------------------------------	---	---	---

6. MOUNTING - Standard mounting slips over a 4"/100mm open top square pole or tenon or may choose one-

TENON MOUNT

TA23 Tenon adapter slips over 2 3/8" O.D x 4" long tenon. Required for poles by others or used in conjunction with TEN pole option by AAL.

POLE MOUNTED ARM

PSA-TU Fixture on top of bracket, upward swept arm
PSA-TD Fixture on top of bracket, downward swept arm
PSA-BU Fixture hangs below bracket, upward swept arm
PSA-BD Fixture hangs below bracket, downward swept arm

WALL MOUNTED ARM

PSWM-TU Fixture on top of bracket, upward swept arm
PSWM-TD Fixture on top of bracket, downward swept arm
PSWM-BU Fixture hangs below bracket, upward swept arm
PSWM-BD Fixture hangs below bracket, downward swept arm


Accent Scale

Small Housing



PKWS


HOOD



ANG – Angled Hood



STR – Straight Hood



DBL – Double Hood

ORDERING EXAMPLE – ACCENT (SMALL) SCALE

1. LUMINAIRE AND HOOD
PKWS-STR

2. OPTICS
GLA-18LED

3. LIGHT ENGINE
WW

4. COLOR
BLT

5. OPTIONS
DSOF-STS-SSR

6. MOUNTING
PSWM-BU

ORDERING INFORMATION

1. LUMINAIRE AND HOOD

PKWS-ANG Angled Hood

PKWS-DBL Double Hood

PKWS-STR Straight Hood

PKWS-IND Indirect Hood (HID -3 or -5 only)

2. LED OPTICS – choice of lensing, distribution, and wattage

T1-36LED	Flat lens, Type I, 3000K CCT, 38 watts
T3-36LED	Flat lens, Type III, 3000K CCT, 38 watts
T5-36LED	Flat lens, Type V, 3000K CCT, 38 watts
GLA-9LED	Vertical lens, Type III, 3000K CCT, 13 watts
GLA-18LED	Vertical lens, Type V, 3000K CCT, 21 watts

2. HID OPTICS

GLA	Vertical lens, internal frosted glass diffuser, symmetric distribution
GR3	Vertical lens, Internal glass refractor, asymmetric distribution
GR5	Vertical lens, Internal glass refractor, symmetric distribution
-3	Vertical lens, Indirect hood and optics, asymmetric distribution
-5	Vertical lens, Indirect hood and optics, symmetric distribution
H2	Horizontal lens, Type II distribution
H3	Horizontal lens, Type III distribution
H4	Horizontal lens, Type IV distribution
H5	Horizontal lens, Type V distribution

3. LED LIGHT ENGINE – choice of color temperature

WW	3000K CCT
NW	4000K CCT
BW	5000K CCT

3. HID LAMP / BALLAST

METAL HALIDE

50MH	50 watt ballast	20MMC	20 watt electronic ballast, PGJ5 base ¹
70MH	70 watt ballast		
70MHEB	70 watt electronic ballast	39MMC	39 watt electronic ballast, PGJ5 base ¹
70MHT6	70 watt ballast, G12 base		
70MHT6EB	70 watt electronic ballast, G12 base		

HIGH PRESSURE SODIUM

50HPS	50 watt ballast
70HPS	70 watt ballast

OTHER

CF	26,32 or 42 watt compact fluorescent
60CO	60 watt CosmoPolis ballast

¹ - Requires selection of vertical lens optics

² - Requires selection of flat lens optics

³ - HID only

4. COLOR

WT Arctic White	BL Black	BLT Matte Black	DGN Dark Green	DB Dark Bronze
WDB Weathered Bronze	MDB Bronze Metallic	VBU Verde Blue	CRT Corten	MAL Matte Aluminum
MG Medium Grey	AGN Antique Green	LG Light Grey	RAL Premium Color	CUSTOM Custom Color

5. OPTIONS

DECORATIVE SCREEN

DSIN Infinity pattern ¹	DSTR Trio pattern ¹	DSOF Offset pattern ¹	DSSH Shutter pattern ¹	DSWH Wheat pattern ¹	DSCS Custom pattern ¹
---	---------------------------------------	---	--	--	---

HOOD FINISH

COP Hood in natural copper, brushed horizontal grain	STS Hood in natural Stainless Steel, brushed horizontal grain
---	--

SCREEN FINISH

SSP Decorative screen in natural Stainless Steel, brushed horizontal grain ¹	CPR Decorative screen in natural Copper, brushed horizontal grain ¹
--	---

CONTROLS

SCP Sensor Control Programmable pole accessory is available to provide occupancy detection for outdoor applications meeting California Title 24. For complete spec sheet and ordering information, visit www.aal.net/products/sensor_control_programmable/
--

OTHER

347 347VAC input, HID only except for 50 MH and 50HPS	ULS Upper lens shield ¹	HSS House side shield ¹	LDL Lightly diffused lens ³
--	---	---	---

6. MOUNTING - Standard mounting slips over a 3"/76mm tenon or may choose one-

POLE MOUNTED ARM

PSA-TU	Fixture on top of bracket, upward swept arm
PSA-TD	Fixture on top of bracket, downward swept arm
PSA-BU	Fixture hangs below bracket, upward swept arm
PSA-BD	Fixture hangs below bracket, downward swept arm

WALL MOUNTED ARM

PSWM-TU	Fixture on top of bracket, upward swept arm
PSWM-TD	Fixture on top of bracket, downward swept arm
PSWM-BU	Fixture hangs below bracket, upward swept arm
PSWM-BD	Fixture hangs below bracket, downward swept arm

Designer Mounting Options

The versatile design of the Parkway Square family

allows for a multitude of mounting options, including post top, arm and wall mount.

Parkway Square mounts to a 4" square pole for pedestrian scale, or a 3" square pole for accent scale. AAL offers a wide variety of decorative poles to complement the elegant design of Parkway Square and carry the styling throughout the entire project.



BU

*Mounted below with arm
in the up position*



TD

*Mounted above with arm in
the down position*



TU

*Mounted above with
arm in the up position*



BD

*Mounted below with arm
in the down position*

Parkway Square is a designer's dream, offering endless configurations and true customization without the custom price.

Designer Mounting Options



Unique Arm Design

The unique design of Parkway Square's arms provide a multitude of configurations allowing the same arm and luminaire to be used throughout the site, providing a consistent and complimentary look and feel.

Available as a post or wall mount, Parkway Square can be mounted above or below its decorative arms, and the arms themselves can be rotated to have the arm in the up or down position.

ARM MOUNTING

POLE MOUNT Arm mounts to side of a 4" O.D. pole.



PSA-TU

Fixture above with arm mounted up.



PSA-TD

Fixture above with arm mounted down.



PSA-BU

Fixture below with arm mounted up. Not available with IND.



PSA-BD

Fixture below with arm mounted down. Not available with IND.

Parkway Square is a designer's dream, offering endless configurations and true customization without the custom price.

Available as a post or wall mount, Parkway Square can be mounted above or below its decorative arms, and the arms themselves can be rotated to have the arm in the up or down position.

Parkway Square arms feature unitized, one-piece designs for structural rigidity and easy installation.

WALL MOUNT Mounting plate provided. Hardware by others.



PSWM-TU

Fixture above with arm mounted up.



PSWM-TD

Fixture above with arm mounted down.



PSWM-BU

Fixture below with arm mounted up. Not available with IND.



PSWM-BD

Fixture below with arm mounted down. Not available with IND.

AAL offers a wide variety of poles to install Parkway Square as a post top luminaire. The pedestrian scale mounts to a 4" O.D. open top square pole or to a 2 3/8" tenon. Visit www.aal.net for a complete listing of poles.

Sconce LED



PKSA/PKSP



ORDERING EXAMPLE – SCONCE

1. LUMINAIRE AND HOOD
PKSA-DBUS

3. LIGHT ENGINE
24LED-WW

3. COLOR
DB

4. OPTIONS
DSTR-CPR

ORDERING INFORMATION

1. LUMINAIRE – Small housing scale

PKSA-DB	Down beam & egress
PKSA-DS	Down spread & egress
PKSA-UB	Up beam & egress
PKSA-US	Up spread & egress
PKSA-DBUS	Down beam/up spread & egress
PKSA-UBDS	Up beam/down spread & egress
PKSA-USDS	Up spread/down spread & egress

2. LED LIGHT ENGINE OR LAMP / BALLAST

15LED-WW	20 watts, 3000K CCT ¹
15LED-NW	20 watts, 4000K CCT ¹
15LED-BW	20 watts, 5000K CCT ¹
24LED-WW	28 watts, 3000K CCT ²
24LED-NW	28 watts, 4000K CCT ²
24LED-BW	28 watts, 5000K CCT ²
24PLL	Integral ballast and 2G11 4-Pin Base ³
35R111EB	35 watt electronic ballast, GX8.5 base ³
20MMC	20 watt electronic ballast, PGJ5 base
39MMC	39 watt electronic ballast, PGJ5 base
DS20MMC	Dual source 20 watt electronic ballast, PGJ5 base USDS only
DS39MMC	Dual source 39 watt electronic ballast, PGJ5 base USDS only

¹ - DB/DS/UB/US only

² - DBUS/UBDS/USDS only

³ - DBUS/UBDS/USDS only

1. LUMINAIRE – Medium housing scale

PKSP-DB	Down beam & egress
PKSP-DS	Down spread & egress
PKSP-UB	Up beam & egress
PKSP-US	Up spread & egress
PKSP-DBUS	Down beam/up spread & egress
PKSP-UBDS	Up beam/down spread & egress
PKSP-USDS	Up spread/down spread & egress

2. LED LIGHT ENGINE OR LAMP / BALLAST

18LED-WW	22 watts, 3000K CCT ¹
18LED-NW	22 watts, 4000K CCT ¹
18LED-BW	22 watts, 5000K CCT ¹
30LED-WW	36 watts, 3000K CCT ²
30LED-NW	36 watts, 4000K CCT ²
30LED-BW	36 watts, 5000K CCT ²
55PLL	Integral ballast and 2G11 4-Pin Base ³
35R111EB	35 watt electronic ballast, GX8.5 base ³
70R111EB	70 watt electronic ballast, GX8.5 base ³
35MHT6EB	39 watt electronic ballast, G12 base
70MHT6EB	70 watt electronic ballast, G12 base
DS39MHT6EB	Dual source 39 watt electronic ballast, G12 base USDS only

3. COLOR

WT	Arctic White	BL	Black	BLT	Matte Black	DGN	Dark Green	DB	Dark Bronze
WDB	Weathered Bronze	MDB	Bronze Metallic	VBU	Verde Blue	CRT	Corten	MAL	Matte Aluminum
MG	Medium Grey	AGN	Antique Green	LG	Light Grey	RAL	Premium Color	CUSTOM	Custom Color

4. OPTIONS

DECORATIVE SCREEN

DSIN	Infinity pattern ¹	DSTR	Trio pattern ¹	DSOF	Offset pattern ¹	DSSH	Shutter pattern ¹	DSWH	Wheat pattern ¹	DSCS	Custom pattern ¹
------	-------------------------------	------	---------------------------	------	-----------------------------	------	------------------------------	------	----------------------------	------	-----------------------------


SCREEN FINISH

SSP	Decorative screen in natural Stainless Steel, brushed horizontal grain ¹	CPR	Decorative screen in natural Copper, brushed horizontal grain ¹
-----	---	-----	--

OTHER OPTIONS

BBU	Integral battery backup for PKSA...24PLL only	NEG	No egress lamp, aperture is sealed with cap in fixture finish
-----	---	-----	---

Bollard



PKWB



ORDERING EXAMPLE – BOLLARD

1. LUMINAIRE
PKWB

2. OPTICS
T5-36LED

3. LIGHT ENGINE
NW

4. COLOR
DB

5. OPTIONS
DSTR-COP

ORDERING INFORMATION

1. LUMINAIRE

PKWB Parkway Square Bollard

2. LED OPTICS – choice of lensing, distribution, and wattage

T1-36LED Flat lens, Type I, 3000K CCT, 38 watts
T3-36LED Flat lens, Type III, 3000K CCT, 38 watts
T5-36LED Flat lens, Type V, 3000K CCT, 38 watts

GLA-9LED Vertical lens, Type III, 3000K CCT, 13 watts
GLA-18LED Vertical lens, Type V, 3000K CCT, 21 watts

2. HID OPTICS

GLA Vertical lens, internal frosted glass diffuser, symmetric distribution
GR3 Vertical lens, Internal glass refractor, asymmetric distribution
GR5 Vertical lens, Internal glass refractor, symmetric distribution
-3 Vertical lens, Indirect hood and optics, asymmetric distribution
-5 Vertical lens, Indirect hood and optics, symmetric distribution

H2 Horizontal lens, Type II distribution
H3 Horizontal lens, Type III distribution
H4 Horizontal lens, Type IV distribution
H5 Horizontal lens, Type V distribution

3. LED LIGHT ENGINE – choice of color temperature

WW 3000K CCT
NW 4000K CCT
BW 5000K CCT

3. HID LAMP / BALLAST

METAL HALIDE

50MH	50 watt ballast	20MMC	20 watt electronic ballast, PGJ5 base ¹
70MH	70 watt ballast		
70MHEB	70 watt electronic ballast	39MMC	39 watt electronic ballast, PGJ5 base ¹
70MHT6	70 watt ballast, G12 base		
70MHT6EB	70 watt electronic ballast, G12 base		

HIGH PRESSURE SODIUM

50HPS 50 watt ballast
70HPS 70 watt ballast

OTHER

CF 26,32 or 42 watt compact fluorescent
60CO 60 watt CosmoPolis ballast

¹ - Requires selection of vertical lens optics

² - Requires selection of flat lens optics

³ - HID only

4. COLOR

WT Arctic White	BL Black	BLT Matte Black	DGN Dark Green	DB Dark Bronze
WDB Weathered Bronze	MDB Bronze Metallic	VBU Verde Blue	CRT Corten	MAL Matte Aluminum
MG Medium Grey	AGN Antique Green	LG Light Grey	RAL Premium Color	CUSTOM Custom Color

5. OPTIONS

DECORATIVE SCREEN

DSIN Infinity pattern ¹ **DSTR** Trio pattern ¹ **DSOF** Offset pattern ¹ **DSSH** Shutter pattern ¹ **DSWH** Wheat pattern ¹ **DSCS** Custom pattern ¹

HOOD FINISH

COP Hood in natural copper, brushed horizontal grain **STS** Hood in natural Stainless Steel, brushed horizontal grain

SCREEN FINISH

SSP Decorative screen in natural Stainless Steel, brushed horizontal grain ¹ **CPR** Decorative screen in natural Copper, brushed horizontal grain ¹

OTHER

347 347VAC input, HID only except for 50 MH and 50HPS **ULS** Upper lens shield ¹ **HSS** House side shield ¹ **LDL** Lightly diffused lens ³

The attention to detail and quality craftsmanship that goes into every AAL fixture ensures the luminaires will last as long as the buildings and spaces they illuminate.





PKWM-ANG-GLA-LG-DSWH-PSWM-TU

Parkway SQUARE LED



Parkway Square™ is a registered trademark of Architectural Area Lighting and Hubbell Lighting, Inc.

©2012 Architectural Area Lighting | PWS 0116

16555 East Gale Ave. | City of Industry | CA 91745

T 626.968.5666 | F 626.369.2695 | www.aal.net | www.aal.net/aal/pws.html | Printed on recycled paper

