

**Catalog 1250 June 2021** 







Samson SSR-100-3 Polyolefin-Polyester Blend Rope 3-strand rope with an excellent wear life and high strength-to-weight ratio. Produced with high strength plied-filament polyester surface yarns wrapped over Samson's high-tenacity Ultra Blue fiber. This rope offers the durability of polyester, but with higher strengths than other combination ropes.

#### Features & Applications

- · Easy to splice
- Economical
- Hockle resistant

| Catalog No. | Size | Tensile<br>Strength, Lbs. | Approx. Wt.<br>Per 100 Feet |
|-------------|------|---------------------------|-----------------------------|
| M18962      | 3/8" | 3,700                     | 3.4 lbs                     |
| M18963      | 1/2" | 6,200                     | 6.0 lbs                     |
| M18964      | 5/8" | 9,000                     | 9.5 lbs                     |

Standard 600 feet coils on wooden reel.



### SAMSON ULTRA-BLUE 3 POLYOLEFIN ROPE

3-strand construction, high-strength Ultra Blue fiber creates a rope 30-35% higher in strength than the equivalent polypropylene construction, which gives Ultra Blue 3 up to three times more wear life than polypropylene.

#### Features & Applications

- Abrasion resistant, durable, excellent grip, and good dielectric properties
- Water resistant, UV resistant, and easy to splice
- · Not for use on capstans, with running hitches, or in any friction heating environments

|             |      | Tensile        | Approx. Wt.  |
|-------------|------|----------------|--------------|
| Catalog No. | Size | Strength, Lbs. | Per 100 Feet |
| †M18951     | 1/4" | 1,500          | 1.1 lbs      |
| *M18952     | 3/8" | 3,300          | 2.6 lbs      |
| *M18953     | 1/2" | 5,500          | 4.5 lbs      |
| *M18954     | 5/8" | 9,500          | 8.0 lbs      |
| *M18955     | 3/4" | 10,800         | 10.2 lbs     |

<sup>\*</sup>Standard 600 feet coils on wooden reel.

#### SAMSON DURA-PLEX COMPOSITE FIBER BRAIDED ROPE 12-strand single braid, where the composite strands are braided together using parallay construction to produce a rope with an excellent strength-to-weight ratio.



- Abrasion resistant
- Easy to splice and flexible
- Good grip and knot-holding ability
- Good strength compared to other "combo" ropes

| Catalog No. | Size | Tensile Strength, Lbs. | Approx. Wt. Per 100 Feet |
|-------------|------|------------------------|--------------------------|
| C4000798    | 3/8" | 3,500                  | 3.4 lbs                  |
| C4000799    | 1/2" | 6,000                  | 5.8 lbs                  |
| C4170586    | 5/8" | 10,400                 | 11.0 lbs                 |
| C4000800    | 3/4" | 13,100                 | 15.0 lbs                 |

Standard 600 feet coils on wooden reel.



<sup>†</sup>Standard 1200 feet coils on wooden reel.

#### GLASS FIBER FILLED NYLON ROPE BLOCKS

#### **Features & Applications**

Shells and sheaves are made of high dielectric, fiber-filled natural nylon

Shaft is silicon bronze and sheave bearings are oil-impregnated bronze

- Blocks available with Samson 1/2" Ultra-Blue 3, SSR-100-3, or **Dura-Plex Rope**
- For working-load considerations, blocks are rated as follows:
- Double Sheave Blocks, max. 3,500 lb.
- Triple Sheave Blocks, max. 3,500 lb.
- Dielectric Strength: Dielectric rating in dry weather is 30,000 Volts between bearing and mounting bolt nut
- Maximum rope size is ½"

| Catalog No. | Description                 | Weight   |
|-------------|-----------------------------|----------|
| C4000919    | Double Block with Becket    | 31/4 lb. |
| C4000918    | Triple Block without Becket | 31/2 lb. |

| Catalog No. | Description                         | Weight                             |
|-------------|-------------------------------------|------------------------------------|
| C4000914    | Two Double Blocks with 120' of 1/2" | 12 <sup>1</sup> / <sub>2</sub> lb. |
|             | Samson Ultra-Blue 3 Rope            |                                    |
| C4000924    | Two Double Blocks with 120' of 1/2" | 16¹/₄ lb.                          |
|             | Samson SSR-100-3 Rope               |                                    |
| C4000915    | Double and Triple Blocks with 150'  | 16 lb.                             |
|             | of 1/2", Samson Ultra-Blue 3 Rope   |                                    |
| C4000925    | Double and Triple Blocks with 150'  | 20 <sup>1</sup> / <sub>2</sub> lb. |
|             | of 1/2", Samson SSR-100-3 Rope      |                                    |
| T4001257    | Two Double Blocks with 120'         | 14¹/₂ lb.                          |
|             | of 1/2", Samson Dura-Plex Rope      |                                    |
| T4001258    | Double and Triple Blocks with 150'  | 16 <sup>1</sup> / <sub>2</sub> lb. |
|             | of 1/2", Samson Dura-Plex Rope      |                                    |







### HAND LINE BLOCK, SAFETY ORANGE Features & Applications

- •1,000 lb. working load
- Safety orange color
- •Fiberglass reinforced nylon body & sheave
- Side-opening body design for easy rigging

Catalog No. PSC4033478 Weight: 2<sup>1</sup>/<sub>4</sub> lb. (1.0 kg.)

Rated working load: 1,000 lb. (454 kg.)

- 3"-diameter sheave accepts up to 5/8"-diameter
- Plated-steel swivel eye allows 360° orientation
- Plated-forged-steel hook has as it is 34 inches throat opening, plus spring-loaded safety latch
- Side-opening design includes high-strength detent-ball pin that is easy to remove and is secured to body with a lanyard

#### Components available as separate items

| Catalog No. | Description         | Weight            |
|-------------|---------------------|-------------------|
| PSC4033479  | Lanyard and Pin Kit | 1/4 lb./0.1 kg    |
| PSC4033480  | Spring Latch Kit    | 1/8 lb. / 0.1 kg. |



#### **Features & Applications**

- Lightweight, cast-aluminum housing and sheave with hinged, cotter-lock voke and either forgedsteel or steel meat hook makes for quick, easy rigging in various applications
- Hand line and block and tackle efficiency is increased with forged-steel, swivel-eye suspension ring, plus three-inch sheave operating on bronze oilite bearings
- Maximum rope size is 5/8"
- Maximum load capacity is 1,250 lbs. on 2230 Series only

|   | Catalog No. | Description with Retainer Latch       | Weight                    |
|---|-------------|---------------------------------------|---------------------------|
| Ī | 22301       | 1250 lb. Block with forged steel hook | 2 lb./0.9 kg.             |
| Ī | 22302       | 1250 lb. Block with steel meat hook   | 2 lb./0.9 kg.             |
| Ī | C4176067    | 2500 lb. Block with forged steel hook |                           |
|   | PS400006    | Ball Lok Pin Chain for 22301 or 22302 | $\frac{1}{4}$ lb./0.1 kg. |



or 22301



HAND LINE HOOK

#### **Features & Applications**

- · Hook can be attached any place along the hand line by two large holes
- The long point accommodates most items to be raised and lowered at the
- Maximum load of hook is 500 lbs. with load seated at bottom of hook M1849





### WEBBING SLINGS

#### **Features & Applications**

- Made in high-visibility "safety yellow"
- Latex-treated for increased abrasion resistance
- Softest, most pliable of nylon webbing slings
- Standard fabrication does not include metal of any kind in body or end fittings
- Designed to handle delicate loads
- Flexible design allows for easy handling and storage
- Two basic types include 10 sizes in Endless version and one size in Return Eye style

**WARNING:** When selecting slings, the following must be considered:

- 1. Weight of load
- 2. Number of slings used to make lift
- 3. Type of hitch (vertical, choker, basket)
- 4. Effect of sling-to-load angle on sling capacity (see table A). Increasing the angle of the sling increases the strain. Therefore, it decreases the lifting capacity of the sling. Capacities listed are for vertical lifts
- 5. CHANCE slings must be considered as non-insulating

#### NOTE

- All CHANCE slings are identified with a heat-imprinted sewn-on tag that includes capacities, width, style and length
- All CHANCE slings carry the required OSHA identification tags




### **BASIC SLING TYPES**

#### **Endless**

- Most versatile
- Used in vertical, basket or choker hitch, it conforms precisely to shape of load
- Provides best gripping and holding power in upright position
- Easiest to use and lasts the longest because there are no eyes to predetermine wearing points
- Endless construction permits the two parts of the sling which go around the load to spread apart and provide a "cradle" for load

#### **Return Eye**

- Designed primarily for use in choker hitch
- Works equally well for basket and vertical hitch applications
- Constructed with two widths of side-by-side webbing and held in place by third width of webbing which binds the two together
- This design results in eye openings which are in the same place as the sling body, which is best for choking as the sling body remains flat against the load





Phone: 573-682-5521 Email: hpsliterature@hubbell.com Web: hubbellpowersystems.com

Page 1254 June 2021

### WEBBING SLINGS







## TABLE A SLING ANGLES


500


1,000 lb.

30°

1,000 lb.

|   | Sling Angle<br>with<br>Vertical | Stresses per<br>Sling Leg<br>Per 1000 lb.<br>Total Load |
|---|---------------------------------|---|
| İ | 0                               | 500   |
|   | 5                               | 502   |
|   | 10                              | 508   |
|   | 15                              | 518   |
|   | 20                              | 532   |
|   | 25                              | 552   |
|   | 30                              | 577   |
|   | 35                              | 610   |
|   | 40                              | 653   |
|   | 45                              | 707   |
|   | 50                              | 778   |
|   | 55                              | 872   |
|   | 60                              | 1000  |
|   | 80                              | 2880  |





#### **How To Carry Two Full Buckets**

- Above illustrations typify the stresses imposed on slings when legs are attached to the load at various angles
- While rated capacities are shown in this catalog, these tables were inserted primarily to show the severe reduction in capacity when a sling is operated at a wide angle
- Whenever head room permits, it is recommended that the angle with the vertical not exceed 45°
- Where head room is small and sling must be spread at an excessive angle, special care must be used in selecting a sling
- In such cases, consult your distributor or Hubbell Power Systems, Inc.



June 2021

## CHANCE WEBBING SLINGS RATED LIFTING CAPACITIES

<u>6</u>



| CATALOG  | WIDTH  | LENGTH | MAXIMUM CAPACITIES* (LBS.) |       |          |                     |
|----------|--------|--------|----------------------------|-------|----------|---------------------|
| NUMBER   | Inches | Feet   | Basket                     | Choke | Vertical | TYPE                |
|          |        |        |                            |       |          | Return Eye (Eye     |
| C4170133 | 2"     | 6′     | 7200                       | 2900  | 3600     | length: Approx. 4") |
| C4170134 | 1"     | 3′     | 6400                       | 2500  | 3200     | Endless             |
| C4170135 | 1"     | 4′     | 6400                       | 2500  | 3200     | Endless             |
| C4170136 | 1"     | 5′     | 6400                       | 2500  | 3200     | Endless             |
| C4170137 | 1"     | 6′     | 6400                       | 2500  | 3200     | Endless             |
| C4170138 | 1"     | 8′     | 6400                       | 2500  | 3200     | Endless             |
| C4170139 | 2"     | 3′     | 12800                      | 5000  | 6400     | Endless             |
| C4170140 | 2"     | 4′     | 12800                      | 5000  | 6400     | Endless             |
| C4170141 | 2"     | 5′     | 12800                      | 5000  | 6400     | Endless             |
| C4170142 | 2"     | 6′     | 12800                      | 5000  | 6400     | Endless             |
| C4170143 | 2"     | 8′     | 12800                      | 5000  | 6400     | Endless             |
| C4170588 | 1"     | 3′     | 12800                      | 5000  | 6400     | Endless             |
| C4170589 | 1¾"    | 5′     | 17200                      | 6900  | 8600     | Endless             |

<sup>\*</sup>MAXIMUM WORKING LOAD IN POUNDS - DO NOT USE SLINGS BEYOND RATED CAPACITY





# POLE HANDLING TOOLS EPOXIGLAS® HANDLE CANT HOOK





- Handle is made of 2" diameter x 4' long orange **EPOXIGLAS**
- Hook is one-piece high carbon steel, end upset, forged and drawn to a point
- Gripper casting incorporates two sets of teeth for improved grip on all pole sizes
- Hook base casting is adjustable to set poles of varying diameters
- A hex head bolt and lockwasher hold base casting in desired position

| Catalog No. | Description | Approx. Wt. Ea. |
|-------------|-------------|-----------------|
| C3050008    | Cant Hook   | 10 lb./4.5 kg.  |

#### **EPOXIGLAS® PIKE POLE**

- The point, secured by a spring-button lock, can be reversed to protect point and avoid damage to equipment when not in use
- Does not absorb moisture so it will not rot or warp
- Features excellent mechanical properties and is relatively lightweight

| Catalog | Pole Diameter | Approx.           |
|---------|---------------|-------------------|
| No.     | & Length      | Weight            |
| 214PH   | 2" x 14'      | 10¹/₂ lb./4.8 kg. |
| 216PH   | 2" x 16'      | 11³/₄ lb./5.3 kg. |
| 218PH   | 2" x 18'      | 13 lb./5.9 kg.    |

| Catalog No. | Description                 | Approx. |
|-------------|-----------------------------|---------|
| Catalog No. | Description                 | Weight  |
| 024095P     | Pike Pole Point Replacement | 0.5 lb  |



- Designed to be used like giant pliers, one worker can guide a pole into place during installation
- Before this tool was developed, it took two workers with peavey sticks to do the job
- Applying pressure to keep the jaws closed, a worker controls forward, backward, side-to-side, and rotary movements of pole as it is lowered by winch or winch line on a hydraulic boom
- Not necessary to regrip the pole once jaws are firmly hooked slightly above ground level
- Fits poles from 7" to 16" in diameter

| Catalog N | . Handle Length | Approx. Weight |
|-----------|-----------------|----------------|
| C200T     | 3 ft.           | 17 lb./6.6 kg. |

#### **POLE WRENCH**

- Two-in-one tool performs functions of a cant hook and pole tong without spiking the pole
- With positive control, it grasps poles of round or other geometric cross sections made of metal, fiber, concrete
- Latex-impregnated nylon-web strap (1-3/4" x 6') rated at 7,500-lb. tensile strength, securely grips even largediameter poles
- Rugged design also includes a 2"diameter x 4' CHANCE orange Epoxiglas® handle with plastisol butt cap, a cast-aluminum head and two forged-steel bails.

| Catalog No. | Description | Weight                                    |
|-------------|-------------|---|
| C3050021    | Pole Wrench | 6 <sup>1</sup> / <sub>2</sub> lb./2.9 kg. |









### **KELLEMS PULLING GRIPS**



- for Overhead Pulling
- made of high-strength galvanized-steel strand

#### **Features & Applications**

- Designed for overhead pulling
- Made of high-strength galvanized-steel strand

**WARNING:** When selecting slings, the following must be considered:

- Do not run grips or swivels over bullwheels while under tension
- 2. Two Punch-Lok® bands should be firmly attached, approximately 1" and 2" from the grip's tail. Banding is required to ensure maximum reliability and guard against accidental release
- 3. **DUA-Pull type grips only:** Double-braided rope, as in 2-in-1 type, must be back-spliced for approximately 2/3 of the mesh length for best gripping results. Grip size must be selected by diameter of back splice.

### **A** WARNING

Never use wire mesh grips up to listed approximate breaking strength. Always use an appropriate safety factor when selecting grips for the working load in your application. Kellems minimum recommended factor of safety for pulling grips is five (5). Additionally, banding the tail end of the grip is recommended for maximum grip performance.

### **DUA-Pull® Type Grips**

#### **Features**

- Highest-strength pulling grips manufactured for overhead transmission line stringing
- Work with both bare and insulated conductors, plus synthetic rope
- Two-over/two-under weave design delivers exceptional strength and gripping ability
- This is made possible by putting more steel mesh in contact with cable or rope surfaces


#### **Ordering Information**

| Catalog   | Diameter Ranges<br>(inches) |             | Approx.<br>Breaking | Di<br>(ir |    | Eye<br>(in.) | Dia.,<br>Cable &<br>Grip** | Color     |
|-----------|-----------------------------|-------------|---------------------|-----------|----|--------------|----------------------------|-----------|
| Number    | Conductor                   | Rope*       | Strength            | E         | М  | Dia.B        | diip                       | Code      |
| 033271037 |                             |             | -,                  |           |    | 0.218        |                            | Black     |
| 033271038 | .3862                       | .5090       | 14,000 lb.          | 12        | 36 | 0.375        | .280"                      | Dk. Green |
| 033271039 | .6387                       | .75 - 1.10  | 20,000 lb.          | 13        | 48 | 0.437        | .360"                      | Red       |
| 033271040 | .88 - 1.12                  | 1.00 - 1.50 | 30,600 lb.          | 15        | 60 | 0.500        | .500"                      | Blue      |

Dimension E = Eye length Dimension M = Mesh length at nominal dia. \*For rope, select smallest size grip which meets required working load.


### **Applications**

- Primarily used in overhead transmission line construction
- Designed for loads and safety considerations that require an extra high-strength grip
- Will mate with swivels and link-type connectors
- Also used for attaching pulling lines to conductors, conductors to running boards, and "double socking" for conductor-to-conductor connections
- DUA pull line accommodates ACSR, ACAR, plus, all aluminum and copper conductors
- Grips also accommodate ground wires, messenger strands, plus wire and synthetic ropes



# Multiple-Strength Type Grips Features

- Designed for pulling ACSR, aluminum or copper bare conductor, ground wires, messenger strands, wire rope and insulated cables
- Made of high-strength, galvanized-steel strand
- Feature a mesh construction of single, double and triple weave for firm holding power
- Endless-weave Grip end lies flat on the cable and will not snag
- Flexible Eye: Flexible, wire-rope eye will mate with a swivel and pass through blocks and sheaves without binding



#### **Applications**

- Ideal for overhead transmission and distribution line stringing for moderate loading
- An economical tool for attaching conductors to pull lines and "double socking" for conductor-to-conductor connections

### **Ordering Information**

| Catalog  | Cable<br>Dia. Range | Approx. Breaking Strength |    | nsion<br>n.) | Eye<br>(inches)              | COIOI      |
|----------|---------------------|---------------------------|----|--------------|------------------------------|------------|
| Number   | (inches)            | Juengui                   | E  | M            | Dia. A                       | Code       |
| 03302044 | 0.25 - 0.49         | 6,800 lb.                 | 9  | 26           | 1/4                          | Green      |
| 03302046 | 0.50 - 0.74         | 10,000 lb.                | 9  | 32           | <sup>5</sup> / <sub>16</sub> | Brown      |
| 03302048 | 0.75 - 0.99         | 14,400 lb.                | 11 | 41           | <sup>3</sup> / <sub>8</sub>  | Light Blue |
| 03302050 | 1.00 - 1.24         | 24,600 lb.                | 12 | 52           | 1/2                          | Gold       |
| 03302052 | 1.25 - 1.49         | 30,600 lb.                | 12 | 56           | 1/2                          | Black      |
| 03302054 | 1.50 - 1.74         | 30,600 lb.                | 12 | 60           | 1/2                          | Red        |

Dimension E = Eye length

Dimension M = Mesh length at nominal diameter

HUBBELL

<sup>\*\*</sup>Add to cable or rope diameter.



### **KELLEMS PULLING GRIPS**

### • for Underground Pulling

### **K-Type Grips**

#### **Features**

- Kellems Rotating-Eye K-Type Pulling Grips are made of high-strength galvanized-steel strand
- Feature double-weave mesh for greater strength and added mesh contact with the cable
- Designed to handle longer or heavier pulling jobs
- Forged eye mates with a swivel or shackle

#### **Applications**

- Specially designed for use in the installation of underground power cables
- Also made for communication and service lines into factories, shopping centers, construction projects, and general underground electrical construction

#### **Ordering Information**

| Catalog  | Cable<br>Diameter Range | Approximate<br>Breaking | Dimension<br>(in.) |    | Eye<br>(inches)               |
|----------|-------------------------|-------------------------|--------------------|----|-------------------------------|
| Number   | (inches)                | Strength (lb.)          | E                  | М  | Diameter A                    |
| 03301024 | 0.75 - 0.99             | 9,600                   | 6                  | 32 | 1                             |
| 03301025 | 1.00 - 1.49             | 16,400                  | 7                  | 33 | 1³/ <sub>8</sub>              |
| 03301026 | 1.50 - 1.99             | 16,400                  | 7                  | 34 | 1³/ <sub>8</sub>              |
| 03301027 | 2.00 - 2.49             | 27,200                  | 9                  | 36 | 1 <sup>5</sup> / <sub>8</sub> |
| 03301028 | 2.50 - 2.99             | 33,000                  | 10                 | 38 | 17/8                          |
| 03301029 | 3.00 - 3.49             | 41,000                  | 10                 | 39 | 17/8                          |

Dimension E = Eye length Dimension M = Mesh length at nominal diameter

#### **Rotating Eye Feature**

- Equipped with a forged-steel rotating eye which can be attached to a swivel
- Durable and compact eye threads through blocks and sheaves without binding
- Rotating eye is not a swivel and will not turn while under tension
- Can turn to relieve pulling torque when tension is relaxed
- If constant swivel action is required, a swivel should be used

| Eye<br>Diameter               | Rota                          | iting E | ye Di                         | mens                          | ions                           | 3/16 R.                    |
|-------------------------------|-------------------------------|---------|-------------------------------|-------------------------------|--------------------------------|----------------------------|
| (inches)                      | Α                             | В       | С                             | D                             | F                              |                            |
| 1                             | 1                             | 1/2     | 9/16                          | <sup>13</sup> / <sub>16</sub> | 31/2                           | F                          |
| 1³/ <sub>8</sub>              | 1³/ <sub>8</sub>              | 1/2     | <sup>11</sup> / <sub>16</sub> | 1                             | 41/2                           | 1/8 R.                     |
| 1 <sup>5</sup> / <sub>8</sub> | 1 <sup>5</sup> / <sub>8</sub> | 5/8     | <sup>7</sup> / <sub>8</sub>   | 13/ <sub>16</sub>             | 5 <sup>5</sup> / <sub>16</sub> | <del> </del>   - - - - - - |
| 1 <sup>7</sup> / <sub>8</sub> | 1 <sup>7</sup> / <sub>8</sub> | 21/32   | 1                             | 13/8                          | 6 <sup>1</sup> / <sub>8</sub>  | -0-                        |
|                               | <b>\</b>                      | м —     |                               |                               |                                | E                          |
|                               |                               |         |                               |                               |                                |                            |

### **A** WARNING

Never use wire mesh grips up to listed approximate breaking strength. Always use an appropriate safety factor when selecting grips for the working load in your application. Kellems minimum recommended factor of safety for pulling grips is five (5). Additionally, banding the tail end of the grip is recommended for maximum grip performance.




Phone: 573-682-5521 Email: hpsliterature@hubbell.com Web: hubbellpowersystems.com

Page 1258 June 2021



## **KELLEMS PULLING GRIPS**

### **Bands and Tools for Pulling Grips**



#### **Features & Applications**

- Punch-Lok® Bands are applied over the tail of a grip to prevent mesh from being tripped or pulled loose
- Ensure full gripping action by locking mesh of tail in tight contact with cable or rope
- When tail of grip is the leading end, the bands are particularly important to prevent accidental release caused by tripping on obstructions
- A conductor-to-conductor (double socking) pulling operation is a good example of two grips connecting two conductors to form a temporary splice
- Bands should be applied to the ends of grips as illustrated herein
- It is also common to tape over the banded tail area to ensure smooth passage through sheaves

#### Note:

- During installation, each end of the grip should be taped down securely to the cable to ensure smooth passage with the cable and guard against accidental release
- · See end bands listed below

#### Note:

- In all cases, two Punch-Lok Bands should be doubled, wrapped approximately 1" and 2" from the grip's tail
- Banding is required to ensure maximum reliability and guard against accidental release

#### **Punch-Lok Tools**

| Catalog No. | Description    |
|-------------|----------------|
| 20320048    | P-1 Heavy Duty |

#### **Punch-Lok Bands**

| Catalog No. | Grip Banding  | Band Width                  | Band Inside       |       |
|-------------|---|-----------------------------|-------------------|-------|
| (one each)  | Range (Inches)  | (Inches)                    | Diameter (Inches) | Model |
| 20320050    | <sup>1</sup> / <sub>4</sub> - 1 <sup>1</sup> / <sub>8</sub>   | <sup>3</sup> / <sub>8</sub> | 13/8              | 0-311 |
| 20320051    | 1 <sup>1</sup> / <sub>8</sub> - 1 <sup>5</sup> / <sub>8</sub> | <sup>3</sup> / <sub>8</sub> | 2                 | 0-316 |
| 20320052    | 1 <sup>5</sup> / <sub>8</sub> - 2 <sup>1</sup> / <sub>4</sub> | 5/8                         | 21/2              | 0-10  |
| 20320053    | 11/4 - 31/5   | 5/8                         | 4                 | 0-16  |
| 20320054    | 3 <sup>1</sup> / <sub>2</sub> - 5                             | <sup>5</sup> / <sub>8</sub> | 6                 | 0-24  |

HUBBELL


Phone: 573-682-5521 Email: hpsliterature@hubbell.com Web: hubbellpowersystems.com

June 2021 Page 1259

<sup>&</sup>lt;sup>®</sup>Punch-Lok is a registered trademark of Punch-Lok Co.

## **CHANCE**®

#### **Hot Line Wire Grips**



#### **Features & Applications**

- Designed for use with hot line tools or regular line work
- Top ring for placing the grip on a hot line with a hot stick
- When released, the grip locks on line and will not fall off
- Holds grip firmly and prevents slipping
- Body is heat-treated steel alloy and made to rigid specifications

|          |          |                    |                    | Safe  |         |
|----------|----------|--------------------|--------------------|-------|---------|
|          | Catalog  | WIRE SIZE — A      | AWG OR MCM         | Load, | Weight  |
| Jaws     | No.      | Max.               | Min.               | lb.   | lb./kg. |
| <b>A</b> | T161340H | 1/0 Str. (.373")   | 8 Sol. (.120")     | 4500  | 3/1.4   |
| <b>A</b> | T16845H  | 4/0 Str. (.550")   | 4 Str. (.218")     | 8000  | 6.3/2.8 |
| •        | T165640H | 336.4 ACSR (.741") | 3/0 ACSR (.530")   | 8000  | 7.8/3.5 |
| •        | T165650H | 477 ACSR (.860")   | 397.5 ACSR (.740") | 8000  | 7.8/3.5 |

- ▲ = for use on small bare wire and cable (solid and strand).
- = for use on bare aluminum, ACSR and copper conductor.

#### Wire Puller Hook



#### Features & Applications

- Fits most popular porcelain or polymer deadend insulators
- For use in cutting deadends and pulling slack on automatic deadends
- Holds the insulator and deadend assembly directly iln line with the conductor, eliminating the need to hold the insulator up with an insulator fork for inserting wire into the automatic deadend
- Can be applied by hand or with hot stick
- · Has maximum rated load of 3500 lbs.

| Catalog No. | Description      | Weight                                    |
|-------------|------------------|---|
| WPH3        | Wire-Puller Hook | 1 <sup>1</sup> / <sub>2</sub> lb./0.7 kg. |

#### **Standard Pulling Eyes**

#### **Features & Applications**

- Economical resource provides a large offset eye to accommodate three-ton chain hoist hooks
- Leaves anchor eye free with plenty of clearances for attaching formed wire grips
- E95B Adapter Bushing quickly adjusts to fit 1/2", 5/8", 3/4", or 1" anchor rods
- By removing the Adapter Bushing, the E96 Pulling Eye fits
   1 1/4" rods
- E96 Pulling Eye is inexpensive and easy to use
- One man can assemble and hook up in minutes
- For working loads to approximately 6,000 pounds (ultimate strength — 18,000 pounds)



| E96 5 lb./2.3 kg. |  |
|-------------------|--|

E95B Adapter Bushing (included) Replacement kit C3031661

Cadmium Plated Bolt with Nut

HUBBELL

Phone: 573-682-5521 Email: hpsliterature@hubbell.com Web: hubbellpowersystems.com

Page 1260 June 2021



| NOTES |
|-------|
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |
|       |



# HUBBELL<sup>®</sup> Power Systems, Inc.

• 210 N. Allen St. • Centralia, MO 65240 • (573) 682-5521

NOTICE: For the latest revision of our Catalog and Literature, click here or visit our web site: www.hubbellpowersystems.com

NOTE: Hubbell has a policy of continuous product improvement. We reserve the right to change design and specifications without notice. ©Copyright 2020 Hubbell Incorporated

### **NEVER COMPROMISE**<sup>™</sup>

www.hubbellpowersystems.com

June 2021 Catalog 1250

