








WALL PACKS

PRODUCT SELECTION GUIDE

| | | GOOD | | | BETTER | | | | | | BEST | | | | | | | | | | | |
|---|-----------------------------------|--|---|----------|--------------------------|---|----------|--------------------------|--|----------|--------------------------|---|----------|--------------------------|--|----------|--|---|--------------------|----------------------------|---------|------|
| | | tradeSELECT®  NRG® 300L | tradeSELECT®  PRS PERIMASHIELD | | | tradeSELECT®  WGH | | | tradeSELECT®  WGH2/WGH3 | | | tradeSELECT®  SLING Wall | | | tradeSELECT®  Prelude Wallpacks | | | tradeSELECT®  Ratio Wall | | | | |
| FEATURES | Easy to Install | Yes | | | Yes | | | Yes | | | Yes | | | Yes | | | Yes | | | | | |
| | Mounting Options | Junction box | | | Junction box | | | Junction box | | | Junction box | | | Side Door, Junction box | | | Mounting Plate, Junction box | | | Junction box, Conduit | | |
| | Features | + | | | + | | | ++ | | | +++ | | | +++ | | | +++ | | | +++ | | |
| | Maintenance | Low | | | Low | | | Low | | | Low | | | Low | | | Low | | | Low | | |
| PERFORMANCE | Lumens | 1800 | | | 2500 | | | 2900–12,800 | | | 4600-17,200 | | | 2200–8100 | | | 2500–8600 | | | 1000–19,500 | | |
| | Watts | 17W | | | 20W | | | 32–110W | | | 30–120W | | | 21–80W | | | 18–60W | | | 10–155W | | |
| | Efficacy (maximum LPW) | 110 | | | 125 | | | 105–120 | | | 140-147 | | | 110–115 | | | 139–144 | | | 148 | | |
| | Distribution | Type IV | | | Type IV | | | Type IV | | | Type IV | | | Type IV | | | Type II (Cut Off), Type IV (Refractor) | | | Type II, Type III, Type IV | | |
| | CCT | 4000K, 5000K | | | 4000K, 5000K | | | 4000K, 5000K | | | 4000K, 4500K, 5000K | | | 3000K, 4000K, 5000K | | | 3000K, 4000K, 5000K | | | 3000K, 4000K, 5000K | | |
| | CRI | 70 | | | 70 | | | 70 | | | 70 | | | 70 | | | 70 | | | 70 | | |
| | Certifications | Listed for Wet Locations | UL 1598 | IP65 | Listed for Wet Locations | UL 1598 | IP65 | Listed for Wet Locations | UL 1598 | IP65 | Listed for Wet Locations | UL 1598 | IP65 | Listed for Wet Locations | UL 1598 | IP65 | Listed for Wet Locations | UL 1598 | IP65 | Listed for Wet Locations | UL 1598 | IP65 |
| | | Yes | Yes | – | Yes | Yes | – | Yes | Yes | Yes | Yes | Yes | Yes | Yes | Yes | Yes | Yes | Yes | Yes | Yes | Yes | Yes |
| | Product Life | 60,000hrs. | | | 60,000 hrs. | | | 60,000hrs. | | | >60,000hrs. | | | >60,000hrs. | | | >60,000hrs. | | | >60,000hrs. | | |
| | HID Equivalence | 70W | | | 150W | | | 150–400W | | | 150–400W | | | 100–250W | | | 70–250W | | | 42–400W | | |
| Energy Savings (Based on HID Equivalence) | 75% | | | 77% | | | 75–80% | | | 75–80% | | | 70–80% | | | 75–80% | | | 76% | | | |
| Voltage | 120–277V | | | 120–277V | | | 120–277V | | | 120–277V | | | 120–277V | | | 120–277V | | | 120–277V, 347–480V | | | |
| CONTROLS | Basic occupancy | Yes | | | Yes | | | Yes | | | Yes | | | Yes | | | – | | | Yes | | |
| | Occupancy and Daylight Harvesting | – | | | – | | | – | | | Yes | | | Yes | | | – | | | Yes | | |
| | Integrated Controls | – | | | – | | | – | | | – | | | SiteSync™ | | | Switchable | | | SiteSync™, NX | | |