

C24 LED Spun Copper Bullet



KIM LIGHTING



HUBBELL
Lighting

Accents Gracefully.



D. C. Smith Greenhouse, University of Wisconsin, Madison

High lumen output LED performance and timeless corrosion resistant copper and brass sets the C24 Luminaire apart from ordinary accent lighting. The brass and copper luminaire ages to a fine patina blending into its surrounding and carries an unmatched 25 year warranty.

Corrosion Resistance

The spun copper housing and fittings are offer exceptionally long life and resists the damaging effects salts, water and soil. The sealed LED light engine with acrylic lens prevents ingress of moisture and debris providing weather-tight protection against the elements.


Higher Lumen Output

Our 11-watt light engine utilizes 9 high-performance LEDs to deliver 1500 lumens, the equivalent of a 150-watt metal halide lamp. Two distributions are available: 15° spot and a 35° narrow flood.

Features and Benefits

- IP68 sealed light engine resists corrosion, dust and dirt intrusion
- 15° spot and 35° narrow flood distributions
- Energy efficient 11W LED light engine
- Delivers up to 1500 lumens
- Three standard color temperatures: 3000K, 4200K and 5100K
- Internal heat sink for maximum thermal dissipation
- Mounting options include: wall mount, stanchion mount or in-grade junction box
- Copper/Brass housing 25 year warranty
- Replacement Kits available

Refer to kimlighting.com for a more detailed specification sheet and ordering information



Unique swivel mount provides superior aiming without loosening over time.



LED Light Engine



KIM LIGHTING



HUBBELL
Lighting

16555 East Gale Avenue • City of Industry, CA 91745 • Phone: 626.968.5666 • Fax: 626.369.2695 • www.kimlighting.com

Because of continuing product improvement programs, Kim Lighting reserves the right to change specifications without notice.
Entire contents © Copyright 2014 Kim Lighting Inc. All rights reserved. Reproduction in whole or in part without permission is strictly prohibited. Printed in USA.