

CABLE GLANDS **PART CODE LOGIC**

Construct order codes from our easy to use guide

The part code logic table below allows for a quick, easy, colour coded method to configure our cable gland products.

Order Code Example - **453UBM25** (501/453/UNIV - B size - M25 entry thread)

KEY	
Required selection	
Optional selection	
Not required	

Cable Gland Part Code Logic					
Datasheet Name	Gland Type	Gland Size	Male Entry Thread Type/Size	Female Thread Type/Size	Thread Length
Do not include the below reference in the part code	Start part code with the below reference	See gland datasheet for available trade sizes. G size and larger are supplied with a 2mm pitch thread as standard. If 1.5mm pitch is required please add a 1 to the gland size, e.g. G1	See gland datasheet for available entry thread based on gland size Show NPT as Decimal e.g. 3/4" = 0.75	Only applies to conduit glands Show NPT as Decimal e.g. 3/4" = 0.75	Metric Thread Length is 15mm as standard. Metric options are defined as below: No Selection = 15mm B = 20mm C = 22mm D = 25mm E = 30mm* *30mm only available on M50 and larger Always leave blank for NPT
Coldflow Compliant Glands					
501/453/UNIV	453U				
ICG/653/UNIV	653U				
PSG/553/RAC	553R				
Compression Glands					
501/421	421				
501/423	423				
501/453/RAC	453R				
Barrier Glands					
PSG/553/RAC	553R				
ICG/653/UNIV	653U				
Conduit Glands					
CSB/656/N	656N				
SB/474	474				
501/414	414				
NEC Compliant Glands					
701	701				
710	710				
711	711				
153X	153X				
753	753				
Industrial Glands					
114	114				
121	121				
123	123				
150/RAC	150				
151/RAC	151R				
153/RAC	153R				
153/UNIV	153U				
Mining Glands					
453/RAC	453RM				
453/UNIV	453UM				
653/UNIV	653UM				

Accessory kits

Please select accessory kits number by combination of accessories required

Locknut	Sealing Washer	Earth Tag	Serrated Washer	Shroud	Kit Number
					01
					02
					03
					04
					05
					06
					07
					08
					09
					10
					11
					12
					13
					14
					15
					16

United Kingdom

Hawke International Oxford Street West Ashton-under-Lyne Lancashire OL7 0NA
Chalmit 388 Hillington Road Glasgow G52 4BL
GAI-Tronics Brunel Drive Stretton Park Burton Upon Trent DE13 0BZ
Tel: +44 (0) 141 882 5555 Email: quoteuk@hubbell.com orderuk@hubbell.com getintouchuk@hubbell.com

U.S.A.

Killark 2112 Fenton Logistics Park Blvd. Fenton, MO 63026
Tel: (314) 531-0460 E-mail: killarkinfo@hubbell.com

Middle East

Building No. 5EA Office No. G03 Dubai Airport Free Zone (DAFZ) PO Box 23529 Dubai UAE
Tel: +974 6612 0728 Email: middle-east@ehawke.com

Asia Pacific

130 Joo Seng Road #03-02 Singapore 368357
Tel: +65 6282 2242 Fax: +65 6284 4244 Email: asia@ehawke.com

Korea

#1212 (IS Biz. Tower), 427Bungil 57-2, Heungandae-Ro, Dongan-Gu,
Anyang-Si, Kyunggi-Do, 14059, Republic of Korea
Email: yyu@hubbell.com.sg

China

Room L, 18F, No. 720 Pudong Avenue
Shanghai International Ocean and Finance Building Shanghai 200120 P.R. China
Tel: +86 (21) 3392 6550 ext. 317 Fax: +86 (21) 3392 6551 Mob: +86 139 1829 4175 Email: weiyi@hubbell.com.cn



A proud member of the Hubbell family.

©2023 Hubbell Incorporated. Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.

HHI-HKE-Mult-CABLE-GLANDS-PART-CODE-LOGIC-SUPPLEMENT-BR-2022

HAWKE
International