



ouro  
EDGE-LIT

**KIM**LIGHTING

 **HUBBELL**  
Lighting



# performance

edge-lit

Pedestrian cityscape requires an architectural luminaire to enhance the site by day and to provide visual comfort and security by night.

Ouro  
EDGE-LIT

Ouro Edge-Lit features advanced light guide lens technology with optical precision that maximizes fixture spacing. With this exceptional light distribution and high peak angles, Ouro Edge-Lit delivers more light where you need it (street side) and less where do not (house side).

FORM | PERFORMANCE | CONTROL

KIM LIGHTING | OURO 3



theory of  
relativity

IES Distributions

IES Type II (Medium) Distribution

Medium rectangular distribution for maximizing pole spacing along pathways or sidewalks.



IES Type III (Short) Distribution

Wide distribution with forward throw for general illumination. Primarily used at the perimeter in conjunction with IES Type V luminaires.



IES V (Wide) Distribution

Wide symmetrical distribution with optimized pole spacing for perimeter site lighting applications.



Today's urban green spaces, parks and pedestrian walkways provide outdoor space for exercise, entertainment, family and community gatherings. The design of these spaces improves the quality of life for local citizens and is in high demand.

From large scale parking areas that require higher mounting heights, greater outputs, and wider distributions to pedestrian walkways where visual comfort is a must, the Ouro is offered in arm, wall, and post top mounting is the ideal solution for any architectural application.

Theory of Relativity

The Kim Lighting Theory of Relativity promotes harmony between the outdoor lighting and architecture through a seamless blending of the two. Comprehensive product families allow specifiers to carry a continuous aesthetic through the project regardless of the application. As distance to structures decreases, luminaire height and scale decrease accordingly, maintaining visual comfort and contextual balance. This maximizes efficiency while preserving and enhancing the architectural experience.



Arm Mount 30 ft

Arm Mount 24 ft

Post Top 12 ft

Wall Mount 9ft

Bollard 4ft

In-Grade



ordering information

UR20 | arm mount  
edge-lit

UR20 | post top/solo arm  
edge-lit

1. SERIES	2. LED ENGINE	3. CCT	4. DISTRIBUTION	5. ROTATION	6. VOLTAGE
Ouro	Type 2M and 3	3K7	2M <sup>5</sup> Type II Medium	(Blank)	UNV 120-277V
UR20	Edge-Lit	3K8	3 <sup>5</sup> Type III Short		347 347V
	96L-30	3K9	5W <sup>6</sup> Type V Wide		480 480V
	96L-50				
	96L-70				
	96L-90				
	96L-135				
	Type 5W				
	192L-30				
	192L-45				
	192L-60				
	192L-75				
	192L-110				
	192L-135				

1. SERIES	2. LED ENGINE	3. CCT	4. DISTRIBUTION	5. ROTATION	6. VOLTAGE
Ouro	Type 2M and 3	3K7	2M <sup>5</sup> Type II Medium	(Blank)	UNV 120-277V
UR20	Edge-Lit	3K8	3 <sup>5</sup> Type III Short		347 347V
	96L-30	3K9	5W <sup>6</sup> Type V Wide		480 480V
	96L-50				
	96L-70				
	96L-90				
	96L-135				
	Type 5W				
	192L-30				
	192L-45				
	192L-60				
	192L-75				
	192L-110				
	192L-135				

7. MOUNTING	8. FINISH	9. CONTROL OPTIONS
Arm Mount	BLS	7PR-TL
ASQ	BLT	7PR-SC
A34	DBS	7PR
A46	DBT	AD-01 <sup>2</sup>
MAF	GTT	AD-02 <sup>2</sup>
	LGS	AD-03 <sup>2</sup>
SVSF	LGT	AD-04 <sup>2</sup>
	PSS	NXWE <sup>8</sup>
VSF	VGT	SWP <sup>2,3,4,8</sup>
	WHS	WSP-40F
	WHT	
WB	Color Option	
	CC	

7. MOUNTING	8. FINISH	9. CONTROL OPTIONS
Post Top	BLS	7PR-TL
FM33	BLT	7PR-SC
FM44	DBS	7PR
	DBT	AD-01 <sup>2</sup>
PT23	GTT	AD-02 <sup>2</sup>
	LGS	AD-03 <sup>2</sup>
PT24	LGT	AD-04 <sup>2</sup>
	PSS	NXWE <sup>8</sup>
PT34	VGT	SWP <sup>2,3,4,8</sup>
	WHS	WSP-40F
	WHT	
	Color Option	
	CC	

10. OPTIONS	11. CONTROL ACCESSORIES
SF	SW7PR
DF	SWUSB
TPL	SWTAB
WBFM3 <sup>7</sup>	SWBRG
WBFM4 <sup>7</sup>	WIR-RME-L
TAFM3 <sup>9</sup>	NXOFM1R1D-UNV
TAFM4 <sup>9</sup>	

10. OPTIONS	11. CONTROL ACCESSORIES
SF	SW7PR
DF	SWUSB
TPL	SWTAB
WBFM3 <sup>7</sup>	SWBRG
WBFM4 <sup>7</sup>	WIR-RME-L
TAFM3 <sup>9</sup>	NXOFM1R1D-UNV
TAFM4 <sup>9</sup>	

<sup>1</sup> Consult factory for custom color, marine and corrosive finish options

<sup>2</sup> Not available with other sensor or wireless control options.

<sup>3</sup> Specify group and zone at time of order. See www.hubbelllighting.com/sitesync for more details. Order at least one SiteSync interface accessory SWUSB or SWTAB. Each option contains SiteSync License, GUI, and Bridge Node.

<sup>4</sup> Not available with 347V and 480V.

<sup>5</sup> Only available with 96L.

<sup>6</sup> Only available with 192L.

<sup>7</sup> Must order with Flush Mount "FM" mounting option and correct pole diameter.

<sup>8</sup> Not available with Solo Arm Post Top (FMSA/PTSA)

<sup>1</sup> Consult factory for custom color, marine and corrosive finish options

<sup>2</sup> Not available with other sensor or wireless control options.

<sup>3</sup> Specify group and zone at time of order. See www.hubbelllighting.com/sitesync for more details. Order at least one SiteSync interface accessory SWUSB or SWTAB. Each option contains SiteSync License, GUI, and Bridge Node.

<sup>4</sup> Not available with 347V and 480V.

<sup>5</sup> Only available with 96L.

<sup>6</sup> Only available with 192L.

<sup>7</sup> Must order with Flush Mount "FM" mounting option and correct pole diameter.

<sup>8</sup> Not available with Solo Arm Post Top (FMSA/PTSA)





ARCHITECTURAL AREA LIGHTING

BEACON PRODUCTS

COLUMBIA LIGHTING

COMPASS

DUAL-LITE

HUBBELL CONTROL SOLUTIONS

HUBBELL OUTDOOR LIGHTING

KIM LIGHTING

KURT VERSEN

LITECONTROL

PRESCOLITE

**KIM**LIGHTING

17760 Rowland Street  
City of Industry, CA 91748  
[kimlighting.com](http://kimlighting.com)

Kim-001 02/01/2022 Edition 2

Copyright © 2022 Kim Lighting, a division of Hubbell Lighting, Inc. All rights reserved. Please refer to online specifications for most up-to-date content as specifications are subject to change without notice.