

EVE4X

Wet Location/NEMA 4X Thermoplastic Exit Sign

EXIT SIGNS



FEATURES

- Exit sign for wall mounting in harsh applications or industrial environments
- High-impact, corrosion resistant, gasketed, polycarbonate housing with polyamide screws
- Neutral grey, water and dust tight, vented enclosure
- Energy saving, long-life LED lamps exceed brightness and uniformity requirements
- Snap-in chevron arrows; 6" letters with 3/4" stroke
- Long life Nickel Metal Hydride battery
- Temperature range: 0°C to 40°C (32°F to 104°F), EM: 10°C to 40°C (50°F to 104°F)
- UL924 Wet Location Listed/UL type 50 4X rated

ORDERING INFORMATION

EVE4X					-	
MODEL	LETTER COLOR	FINISH	OPERATION	SELF DIAGNOSTICS	OPTIONS	
	R Red G Green	W White	Blank AC Only E Emergency	Blank None I Spectron® Self-diagnostic ^{1,7}	DC Remote DC Operation ^{3,5,6} FAP Fire Alarm Panel ^{2,4,6,7} FM Flasher Module ^{2,7}	

¹ For use with emergency models only

² For use with Spectron® Self-Test/Self-Diagnostic models only

³ For use with AC models only

⁴ Operates with 24-volt AC or DC fire alarm panels

⁵ For emergency illumination of sign from remote 6-24 VDC power sources

⁶ DC option may not be specified with 2C and FAP options

⁷ FM and FAP options may not be specified together

ELECTRONICS

- Transformer isolation, surge, transient, and low voltage disconnect protection
- Pre-stripped pigtail leads with push in wiring connectors
- 90 minute emergency operation
- Reverse polarity, short circuit and AC lockout protection
- 120/277VAC 60Hz operation, test switch and LED AC-On indicator light

POWER CONSUMPTION

Model	120VAC, 60Hz			277VAC, 60Hz		
	A	W	PF	A	W	PF
Red AC Only	0.02	1.42	0.59	0.009	1.36	0.54
0.02	0.02	1.36	0.57	0.009	1.30	0.57
0.027	0.027	2.01	0.62	0.0127	1.94	0.55
Green Emergency	0.027	2.01	0.62	0.0127	1.94	0.55

