

# Ground Fault Devices

## Commercial Tamper-Resistant and/or Weather-Resistant GFCI Receptacles




### Features

- Patented shutter design for tamper-resistant protection
- Tamper-Resistant/Weather-Resistant Series meets NEC® requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Weather-Resistant Only Series meets NEC® requirements for weather resistance (406.9), UV and corrosion resistance for harsh and damp applications
- Patented CIRCUITPRO® self-test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired



### Tamper-Resistant Weather-Resistant



Rating	Color	Standard	Isolated Ground	
NEMA 5-15, 15A 125V 	Black	GFTWRST15BK	GFTWRST15BKIG	
	Brown	GFTWRST15	GFTWRST15IG	
	Gray	GFTWRST15GY	GFTWRST15GYIG	
	Ivory	GFTWRST15I	GFTWRST15IIG	
	Light Almond	GFTWRST15LA	GFTWRST15LAIG	
	Orange	—	GFTWRST15ORIG	
	Red	GFTWRST15R	GFTWRST15RIG	
	White	GFTWRST15W	GFTWRST15WIG	
	NEMA 5-20, 20A 125V 	Black	GFTWRST20BK	GFTWRST20BKIG
		Brown	GFTWRST20	GFTWRST20IG
Gray		GFTWRST20GY	GFTWRST20GYIG	
Ivory		GFTWRST20I	GFTWRST20IIG	
Light Almond		GFTWRST20LA	GFTWRST20LAIG	
Orange		—	GFTWRST20ORIG	
Red		GFTWRST20R	GFTWRST20RIG	
White		GFTWRST20W	GFTWRST20WIG	




### Weather-Resistant Only



Rating	Color	Standard
NEMA 5-15, 15A 125V 	Black	GFWRST15BK
	Brown	GFWRST15
	Gray	GFWRST15GY
	Ivory	GFWRST15I
	Light Almond	GFWRST15LA
	Red	GFWRST15R
NEMA 5-20, 20A 125V 	Black	GFWRST20BK
	Brown	GFWRST20
	Gray	GFWRST20GY
	Ivory	GFWRST20I
	Light Almond	GFWRST20LA
	Red	GFWRST20R
White	GFWRST20W	




### Hospital Grade • Tamper-Resistant Weather-Resistant



Rating	Color	Standard	Isolated Ground	
NEMA 5-15, 15A 125V 	Black	GFST82BKTR	GFST82BKIG	
	Brown	GFST82TR	GFST82IG	
	Gray	GFST82GYTR	GFST82GYIG	
	Ivory	GFST82ITR	GFST82IIG	
	Light Almond	GFST82LATR	GFST82LAIG	
	Orange	—	GFST82ORIG	
	Red	GFST82RTR	GFST82RIG	
	White	GFST82WTR	GFST82WIG	
	NEMA 5-20, 20A 125V 	Black	GFST83BKTR	GFST83BKIG
		Brown	GFST83TR	GFST83IG
Gray		GFST83GYTR	GFST83GYIG	
Ivory		GFST83ITR	GFST83IIG	
Light Almond		GFST83LATR	GFST83LAIG	
Orange		—	GFST83ORIG	
Red		GFST83RTR	GFST83RIG	
White		GFST83WTR	GFST83WIG	

### Product Dimensions Inches (mm)

	GFCI Receptacle
A	3.27" (83.1)
B	2.75" (69.8)
C	1.75" (44.5)
D	1.47" (37.4)
E	1.10" (27.9)



NEC® is a registered trademark of the National Fire Protection Association (NFPA).