

# Locking Devices

## 10 Amp and 15 Amp Non-NEMA Locking Devices


10A 250V and 15A 125V Locking Devices,  
3-Pole 3-Wire Non-Grounding and 2-Pole 3-Wire Grounding Inches (mm)




Rating	Poles/ Wires	Cord Diameter	Description	Triple Gripper		Flanged Devices Equipment Base with Binding Screw Terminals		Receptacle, Back and Side Wired	
				Nylon Plug	Nylon Connector	Male White Nylon	Female White Nylon	Single All Black Nylon	Duplex All Black RTP
10A 250V, Non-Grounding	3-Pole 3-Wire	.300"-.655" (7.6-16.6)	Black/White	<b>7568NP</b>	<b>7565NC</b>	<b>7556MB</b>	<b>7557ER</b>	<b>7582</b>	<b>7580DR</b>
			Corrosion- Resistant Yellow/ White	<b>7568NPCR</b>	<b>7565NCCR</b>	—	—	—	—
15A 125V, Grounding	2-Pole 3-Wire		All Black	—	—	—	—	<b>7582G</b>	<b>7580GDR</b>


Note: Wiring devices on this page are **no longer listed by Underwriters Laboratories Inc.**, and are intended for **replacement use only** in existing installations. We recommend that they not be used in new installations. These devices formerly complied with UL Standards, however, due to revisions of these Standards, the devices can no longer be listed. For new installations, refer to the NEMA configuration chart on page H-2 for the products suited for your particular current and voltage requirements. **CAUTION:** To Avoid Electric Shock-Review premises carefully and do not use if slot or blade configuration (design) is already in a circuit having a rating differing from the rating of this device. See page H-20 for weather protective boots for 10 and 15 amp nylon locking plugs.

## Product Dimensions Inches (mm)

	Plug		
	10A	20A	
A	2.18" (55.4)	2.60" (66.0)	
B	1.38" (35.1)	1.80" (45.7)	
C	1.53" (38.9)	2.11" (53.6)	

	Connector		
	10A	20A	
A	2.95 (75.0)	3.73 (94.7)	
B	1.38" (35.1)	1.80 (45.7)	
C	1.53" (38.9)	2.11 (53.6)	

	Flanged Devices	
	10A	20A
A	2.38" (60.5)	2.87" (73.9)
B	2.19" (55.5)	2.20
C	2.00" (50.8)	2.50" (63.5)
D	1.84" (46.7)	1.27" (32.3)
E	1.68" (42.6)	2.01" (51.1)
F	1.58" (40.1)	(3) 0.19" (4.8)



	Duplex Receptacles	Single Receptacles	
	10A	10A	20A
A	3.28" (83.3)	3.28" (83.3)	3.28" (83.3)
B	2.38" (60.5)	2.38" (60.5)	2.38" (60.5)
C	1.38" (35.1)	1.38" (35.1)	1.38" (35.1)
D	1.41" (35.8)	1.41" (35.8)	1.39" (35.3)
E	1.37" (34.8)	1.37" (34.8)	2.20" (55.9)
F	1.01" (25.7)	1.01" (25.7)	0.86" (21.8)

