



- Three-piece thermoplastic clamp assembly with fast-lead stainless screws provides a more consistent durable grip
- Superior wire terminations are assured with box terminals and screws with pressure pads
- No “lazy” connections because a spring-loaded safety shutter automatically ejects the plug if it hasn't been properly locked into the female device
- Insulated non-metallic housing enhances safety and resistance to impact
- Positive locking is ensured by the nose of the plug being keyed into a detent in female device

20A 125V AC or DC, 10A 250V DC, 480V AC, 2-Pole 3-Wire and 3-Pole 3-Wire Inches (mm)



| Rating | Poles/ Wires | Cord Diameter | Description | Clamp-Type Terminals | | Single Receptacle, Back Wired |
|--|------------------|----------------------------|----------------|----------------------|-----------------|----------------------------------|
| | | | | Nylon Plug | Nylon Connector | |
| 20A 125V AC or DC, 10A 250V DC, 480V AC, Grounding | 2-Pole | .320"-.660" (8.1- 16.8) | Black/White | 23005G* | 23002G* | — |
| | 3-Wire | | Black Phenolic | — | — | 23000G* |
| 20A 125V AC or DC, 10A 250V DC, 480V AC, Non-Grounding | 3-Pole 3-Wire | .320"-.660" (8.1- 16.8) | Black/White | 23005 | — | — |



Note: *These devices are not UL Listed and are for replacement use only in existing installations. See page H-27 for weather protective boots and accessories.

Product Dimensions Inches (mm)

| | Plug | Connector | Single Receptacle |
|---|--------------|--------------|-------------------|
| A | 3.22" (81.8) | 3.56" (90.4) | 3.28" (83.3) |
| B | 1.72" (43.7) | 1.62" (41.4) | 2.38" (60.5) |
| C | 2.31" (58.7) | — | 1.38" (35.1) |
| D | — | — | 2.50" (63.5) |
| E | — | — | 1.62" (41.4) |
| F | — | — | 1.47" (37.3) |

