

Temporary Lighting

Maintenance and Worklights



Choose Bryant's industrial work lights for maximum user safety. The fluorescent lights are designed with all electrical components located inside a closed chamber for your protection. Lamps stay cool while spreading light over large areas. Work light models can be paired with an adjustable hanging kit or magnetic mounts for positioning flexibility.

Portable work lights can be transported and re-mounted.

Long cords allow free movement in work space.

LED Maintenance Worklights

Description	Outlet Rating	Rating	Wattage	Lumen Output	Cord Type	Cord Length	Catalog Number
LED Industrial maintenance light, 1 vertical hanging hook included.	N/A	15A 125V	20	2400	#16/3 SJEOW	25 ft.	BRYML2825L
LED worklight with end light feature.	N/A	15A 125V	9	920/120	#18/2 SJTOW	25 ft.	BRYWL25LED
LED worklight with end light feature and tool tap.	12 Amp	15A 125V	9	920/120	#16/3 SJTOW	25 ft.	BRYWL25LEDT



Fluorescent Maintenance Worklights

Description	Outlet Rating	Rating	Wattage	Lumen Output	Cord Type	Cord Length	Catalog Number
Fluorescent worklight with straight blade plug.	N/A	15A 125V	13	825	#16/3 SJTOW	25 ft.	BRYTW25F1



Accessories and Replacement Items

Description	Catalog Number
Magnetic mounting bracket for ML style lights, 82 lb. capacity.	BRYMLMM
Magnetic mounting bracket for WL style lights, 58 lb. capacity.	BRYWLMM
Replacement rough service fluorescent bulb for 13 watt style lamps.	BRYREPPFB
Replacement LED panel fixture, 90 LEDs, 450 lumen.	BRYREP450LED
5 base LED string only, 50 ft., 18/2.	BRYREP182S50
10 base LED string only, 100 ft., 18/2.	BRYREP182S100

