


Wire Management Products

Support Grips Quick Reference Selection Guide




Single U Eye

For single hook attachment of permanent indoor/outdoor cable. Available on heavy duty, standard duty, and service drop grips. See pages N-9, N-10, N-11, N-13, N-15, N-17 and N-18.



Double U Eye

For double hook attachment of permanent indoor/outdoor cable. Available on heavy duty and standard duty grips. See pages N-9, N-10, N-11, N-13 and N-15.




Universal

For wraparound attachment to an existing fastener in permanent indoor/outdoor applications. Available on standard duty and light duty service drop grips. See pages N-12, N-14, N-16, N-17 and N-18.



Single Offset Eye


For offset hook attachment of permanent indoor/outdoor cable. Available on heavy duty, standard duty and light duty support grips. See pages N-12, N-14 and N-16.



Wide Range Bus Drop

Used indoors for cable support where flexible cable connects electrical equipment to bus duct. Support or restrain air hose and water hose. See page N-18.

Heavy Duty Support Grips



Application:

Permanent support of heavy loads and long runs of vertical and horizontal cables indoors and outdoors where ends of cable are available


- Closed mesh fits over cable end while split mesh is used when cable end is inaccessible
- Strand equalizers reinforce gripping strength and position, distributes load equally

Ideal For Use In:

- Industrial applications
- Communication towers
- Utility work
- Heavy equipment
- Construction

Single Eye and Double Eye, Closed Mesh Inches (cm)

| Cable Diameter Range Inches (cm) | Inches (cm) | | Tin-Coated Bronze | | Stainless Steel | | | |
|----------------------------------|-------------|--------------|------------------------------------|------------|-----------------|------------------------------------|------------|------------|
| | E | M | Approx. Breaking Strength Lbs. (N) | Single Eye | Double Eye | Approx. Breaking Strength Lbs. (N) | Single Eye | Double Eye |
| .75"-1.99" (1.90-2.51) | 10" (25.40) | 25" (63.50) | 2,820 (12,543) | SHC075U | SHC075 | 4,200 (18,682) | SHC075US | — |
| | 12" (30.48) | 28" (71.12) | 4,280 (19,037) | SHC100U | — | 7,300 (32,470) | SHC100US | — |
| 1.00"-1.24" (2.54-3.15) | 10" (25.40) | 28" (71.12) | 4,280 (19,037) | — | SHC100 | — | — | — |
| | 12" (30.48) | 30" (76.20) | 4,280 (19,037) | SHC125U | — | 7,300 (32,470) | SHC125US | — |
| 1.25"-1.49" (3.17-3.78) | 10" (25.40) | 30" (76.20) | 4,280 (19,037) | — | SHC125 | — | — | — |
| | 12" (30.48) | 34" (86.36) | 4,280 (19,037) | SHC150U | — | 11,150 (49,595) | SHC150US | — |
| 1.50"-1.99" (3.81-5.05) | 10" (25.40) | 34" (86.36) | 4,280 (19,037) | — | SHC150 | — | — | — |
| | 12" (30.48) | 36" (91.44) | 8,050 (35,806) | — | SHC200 | 20,100 (89,405) | — | SHC200DES |
| 2.00"-2.49" (5.08-6.32) | 12" (30.48) | 38" (96.52) | 8,050 (35,806) | — | SHC250 | 20,100 (89,405) | — | SHC250DES |
| 2.50"-2.99" (6.35-7.59) | 12" (30.48) | 40" (101.60) | 10,060 (44,747) | — | SHC300 | 25,200 (112,090) | — | SHC300DES |
| 3.00"-3.49" (7.62-8.86) | 12" (30.48) | 44" (111.76) | 12,070 (53,687) | — | SHC350 | — | — | — |
| 3.50"-3.99" (8.89-10.13) | 12" (30.48) | 46" (116.84) | 12,070 (53,687) | — | SHC400 | — | — | — |
| 4.00"-4.49" (10.16-11.40) | 12" (30.48) | 68" (172.72) | 13,790 (61,338) | — | SHC450 | — | — | — |
| 4.50"-5.00" (11.43-12.70) | 12" (30.48) | | | | | | | |



SHC125

CAUTION

Never use grip to approximate breaking strength. Refer to page N-26 for safety and working load factors. Banding is necessary to guard against accidental release of grip and provide maximum reliability.