

Wire Management Products

Standard Duty Support Grips



Application:

Permanent support of vertical and horizontal cable indoors and outdoors where ends of cable are available

- Closed mesh fits over cable end while split mesh is used when cable end is inaccessible
- Strand equalizers reinforce gripping strength and position, distributes load equally


Ideal For Use In:

- Industrial applications
- Communication towers
- Utility work
- Heavy equipment
- Construction



Single Eye, Closed Mesh Inches (cm)

Cable Diameter Range Inches (cm)	Inches (cm)		Tin-Coated Bronze		Stainless Steel	
	E	M	Approx. Breaking Strength Lbs. (N)	Single Eye	Approx. Breaking Strength Lbs. (N)	Single Eye
.50"-.62" (1.27-1.57)	7" (17.78)	10" (25.40)	530 (2,357)	SPC050U	1,370 (6,094)	SPC050US
.63"-.74" (1.60-1.88)	8" (20.32)	10" (25.40)	790 (3,514)	SPC062U	2,060 (9,163)	SPC062US
.75"-.99" (1.90-2.51)	8" (20.32)	13" (33.02)	1,020 (4,537)	SPC075U	2,060 (9,163)	SPC075US
1.00"-1.24" (2.54-3.15)	9" (22.86)	14" (35.56)	1,610 (7,161)	SPC100U	2,678 (11,912)	SPC100US
1.25"-1.49" (3.17-3.78)	10" (25.40)	15" (38.10)	1,610 (7,161)	SPC125U	4,490 (19,972)	SPC125US
1.50"-1.74" (3.81-4.42)	12" (30.48)	17" (43.18)	1,610 (7,161)	SPC150U	4,490 (19,972)	SPC150US
1.75"-1.99" (4.44-5.05)	14" (35.56)	19" (48.26)	2,150 (9,563)	SPC175U	5,000 (22,240)	SPC175US
2.00"-2.49" (5.08-6.32)	16" (40.64)	21" (53.34)	3,260 (14,500)	SPC200U	8,940 (39,765)	SPC200US
2.50"-2.99" (6.35-7.59)	18" (45.72)	23" (58.42)	3,260 (14,500)	SPC250U	8,940 (39,765)	SPC250US
3.00"-3.49" (7.62-8.86)	21" (53.34)	25" (63.50)	4,900 (21,795)	SPC300U	13,420 (59,692)	SPC300US
3.50"-3.99" (8.89-10.13)	24" (60.96)	27" (68.58)	4,900 (21,795)	SPC350U	-	-



Double Eye, Closed Mesh Inches (cm)

Cable Diameter Range Inches (cm)	Inches (cm)		Tin-Coated Bronze		Stainless Steel	
	E	M	Approx. Breaking Strength Lbs. (N)	Double Eye	Approx. Breaking Strength Lbs. (N)	Single Eye
.50"-.62" (1.27-1.57)	4" (10.16)	10" (25.40)	530 (2,357)	SPC050DE	1,370 (6,094)	SPC050DES
.63"-.74" (1.60-1.88)	4" (10.16)	10" (25.40)	790 (3,514)	SPC062DE	2,060 (9,163)	SPC062DES
.75"-.99" (1.90-2.51)	5" (13.97)	12" (30.48)	1,020 (4,537)	SPC075DE	2,060 (9,163)	SPC075DES
1.00"-1.24" (2.54-3.15)	5" (12.70)	14" (35.56)	1,610 (7,161)	SPC100DE	2,670 (11,876)	SPC100DES
1.25"-1.49" (3.17-3.78)	5" (12.70)	15" (38.10)	1,610 (7,161)	SPC125DE	4,490 (19,972)	SPC125DES
1.50"-1.74" (3.81-4.42)	5" (12.70)	17" (43.18)	1,610 (7,161)	SPC150DE	4,490 (19,972)	SPC150DES
1.75"-1.99" (4.44-5.05)	6" (15.24)	19" (48.26)	2,150 (9,563)	SPC175DE	5,000 (22,240)	SPC175DES
2.00"-2.49" (5.08-6.32)	6" (15.24)	21" (53.34)	3,260 (14,500)	SPC200DE	8,940 (39,765)	SPC200DES
2.50"-2.99" (6.35-7.59)	6" (15.24)	23" (58.42)	3,260 (14,500)	SPC250DE	8,940 (39,765)	SPC250DES
3.00"-3.49" (7.62-8.86)	8" (20.32)	25" (63.50)	4,900 (21,795)	SPC300DE	12,000 (53,376)	SPC300DES
3.50"-3.99" (8.89-10.13)	8" (20.32)	27" (68.58)	4,900 (21,795)	SPC350DE	12,000 (53,376)	SPC350DES

CAUTION

Never use grip to approximate breaking strength. Refer to page N-26 for safety and working load factors. Banding is necessary to guard against accidental release of grip and provide maximum reliability.