

# Wire Management Products

## Standard Duty Support Grips



### Application:

Permanent support of vertical and horizontal cable indoors and outdoors where ends of cable are available

- Available for light duty, standard duty and heavy duty applications
- Closed mesh fits over cable end while split mesh is used when cable end is inaccessible
- Strand equalizers reinforce gripping strength and position, distributes load equally

### Ideal For Use In:

- Industrial applications
- Communication towers
- Heavy equipment
- Utility work
- Construction



### Offset Eye, Closed Mesh Inches (cm)

Cable Diameter Range Inches (cm)	Inches (cm)		Tin-Coated Bronze		Stainless Steel	
	E	M	Approx. Breaking Strength Lbs. (N)	Offset Eye	Approx. Breaking Strength Lbs. (N)	Offset Eye
.50"-.62" (1.27-1.57)	4" (10.16)	10" (25.40)	500 (2,724)	<b>SPC050SO</b>	1,370 (6,094)	<b>SPC050SOS</b>
.63"-.74" (1.60-1.88)	4" (10.16)	10" (25.40)	750 (3,336)	<b>SPC062SO</b>	1,950 (8,674)	<b>SPC062SOS</b>
.75"-.99" (1.90-2.51)	4" (10.16)	13" (33.02)	950 (4,226)	<b>SPC075SO</b>	2,060 (9,163)	<b>SPC075SOS</b>
1.00"-1.24" (2.54-3.15)	5" (12.70)	14" (35.56)	1,500 (6,672)	<b>SPC100SO</b>	2,670 (11,876)	<b>SPC100SOS</b>
1.25"-1.49" (3.17-3.78)	5" (12.70)	15" (38.10)	1,500 (6,672)	<b>SPC125SO</b>	4,490 (19,972)	<b>SPC125SOS</b>
1.50"-1.74" (3.81-4.42)	5" (12.70)	17" (43.10)	1,500 (6,672)	<b>SPC150SO</b>	3,700 (16,458)	<b>SPC150SOS</b>
1.75"-1.99" (4.44-5.05)	6" (15.24)	19" (48.26)	2,000 (8,896)	<b>SPC175SO</b>	4,370 (19,438)	<b>SPC175SOS</b>
2.00"-2.49" (5.08-6.32)	9" (22.86)	21" (53.34)	3,100 (13,789)	<b>SPC200SO</b>	5,500 (24,464)	<b>SPC200SOS</b>
2.50"-2.99" (6.35-7.59)	9" (22.86)	23" (58.42)	—	—	5,500 (24,464)	<b>SPC250SOS</b>
3.00"-3.49" (7.62-8.86)	9" (22.86)	25" (63.50)	3,800 (16,902)	<b>SPC300SO</b>	—	—
3.50"-3.99" (8.89-10.13)	11" (27.94)	27" (68.58)	3,250 (14,456)	<b>SPC350SO</b>	—	—



### Universal Eye, Closed Mesh Inches (cm)

Cable Diameter Range Inches (cm)	Inches (cm)		Tin-Coated Bronze		Stainless Steel	
	E	M	Approx. Breaking Strength Lbs. (N)	Double Eye	Approx. Breaking Strength Lbs. (N)	Offset Eye
.50"-.62" (1.27-1.57)	18" (45.72)	10" (25.40)	530 (2,357)	<b>SPC050L</b>	—	—
.63"-.74" (1.60-1.88)	18" (45.72)	10" (25.40)	790 (3,514)	<b>SPC062L</b>	—	—
.75"-.99" (1.90-2.51)	18" (45.72)	13" (33.02)	1,020 (4,537)	<b>SPC075L</b>	—	—
1.00"-1.24" (2.54-3.15)	18" (45.72)	14" (35.56)	1,610 (7,161)	<b>SPC100L</b>	—	—
1.25"-1.49" (3.17-3.78)	18" (45.72)	15" (38.10)	1,610 (7,161)	<b>SPC125L</b>	—	—
1.50"-1.74" (3.81-4.42)	18" (45.72)	17" (43.10)	1,610 (7,161)	<b>SPC150L</b>	—	—
1.75"-1.99" (4.44-5.05)	18" (45.72)	19" (48.26)	2,150 (9,563)	<b>SPC175L</b>	—	—
2.00"-2.49" (5.08-6.32)	18" (45.72)	21" (53.34)	3,260 (14,500)	<b>SPC200L</b>	—	—
2.50"-2.99" (6.35-7.59)	18" (45.72)	23" (58.42)	3,260 (14,500)	<b>SPC250L</b>	—	—
3.00"-3.49" (7.62-8.86)	18" (45.72)	25" (63.50)	4,900 (21,795)	<b>SPC300L</b>	—	—

### CAUTION

Never use grip to approximate breaking strength. Refer to page N-26 for safety and working load factors. Banding is necessary to guard against accidental release of grip and provide maximum reliability.