

Wire Management Products

Service Drop, Heavy Duty Support Grips


Application:

For heavy duty support of all types of suspended service cables used in indoor or outdoor minimum abuse environments

- Closed mesh fits over cable end while split mesh is used when cable end is inaccessible
- Strand equalizers reinforce gripping strength and position, distributes load equally

Ideal For Use In:

- Industrial
- Communication towers
- Utility work and construction
- Transportation power systems
- Residential



Single Eye and Universal Eye, Split Mesh, Rod Closing

Cable Diameter Range Inches (cm)	Approx. Breaking Strength Lbs. (N)	Single Eye			Universal Eye		
		Inches (cm)		Tin-Coated Bronze	Inches (cm)		Tin-Coated Bronze
		E	M		E	M	
.23"-.31" (.58-.79)	500 (2,224)	5" (13.97)	4" (11.43)	SPJ023UD	11" (27.94)	4" (11.43)	SPJ023LD
.29"-.37" (.74-.94)	500 (2,224)	5" (13.97)	5" (13.97)	SPJ029UD	11" (27.94)	5" (13.97)	SPJ029LD
.35"-.44" (.89-1.12)	870 (3,870)	6" (15.24)	6" (16.51)	SPJ035UD	12" (30.48)	6" (16.51)	SPJ035LD
.41"-.50" (1.04-1.27)	870 (3,870)	6" (15.24)	7" (19.05)	SPJ041UD	12" (30.48)	7" (19.05)	SPJ041LD
.46"-.56" (1.17-1.42)	1,050 (4,670)	6" (15.24)	8" (20.32)	SPJ046UD	12" (30.48)	8" (20.32)	SPJ046LD
.52"-.62" (1.32-1.57)	1,050 (4,670)	7" (17.78)	8" (21.59)	SPJ052UD	13" (33.02)	8" (21.59)	SPJ052LD
.58"-.68" (1.47-1.73)	1,050 (4,670)	7" (17.78)	9" (24.13)	SPJ058UD	13" (33.02)	9" (24.13)	SPJ058LD
.64"-.75" (1.63-1.90)	1,390 (6,183)	7" (17.78)	9" (24.13)	SPJ064UD	13" (33.02)	9" (24.13)	SPJ064LD
.75"-.87" (1.90-2.21)	1,390 (6,183)	8" (20.32)	10" (26.67)	SPJ075UD	14" (35.56)	10" (26.67)	SPJ075LD
.87"-.1.00" (2.21-2.54)	1,790 (7,962)	8" (20.32)	11" (29.21)	SPJ087UD	14" (35.56)	11" (29.21)	SPJ087LD
1.00"-1.18" (2.54-3.00)	1,790 (7,962)	9" (22.86)	13" (34.29)	SPJ100UD	15" (38.10)	13" (34.29)	SPJ100LD
1.06"-1.24" (2.69-3.15)	1,790 (7,962)	9" (22.86)	14" (36.83)	SPJ106UD	15" (38.10)	14" (36.83)	SPJ106LD

Service Drop, Light Duty Support Grips


Application:

For light duty support of all types of suspended service cables used in indoor or outdoor minimum abuse environments

- Closed mesh fits over cable end while split mesh is used when cable end is inaccessible
- Strand equalizers reinforce gripping strength and position, distributes load equally

Ideal For Use In:

- Industrial applications
- Communication towers
- Utility work and construction
- Transportation power systems
- Residential



Single Eye and Universal Eye, Split Mesh, Rod Closing

Cable Diameter Range Inches (cm)	Approx. Breaking Strength Lbs. (N)	Single Eye			Universal Eye		
		Inches (cm)		Tin-Coated Bronze	Inches (cm)		Tin-Coated Bronze
		E	M		E	M	
.23"-.31" (.58-.79)	290 (1,290)	3" (7.62)	3" (9.52)	SPJ023U	9" (22.86)	3" (9.52)	SPJ023L
.29"-.37" (.74-.94)	290 (1,290)	5" (12.70)	4" (11.43)	SPJ029U	10" (25.40)	4" (11.43)	SPJ029L
.35"-.44" (.89-1.12)	500 (2,224)	5" (13.97)	4" (12.06)	SPJ035U	10" (25.40)	4" (12.06)	SPJ035L
.41"-.50" (1.04-1.27)	500 (2,224)	5" (13.97)	5" (12.70)	SPJ041U	11" (27.94)	5" (12.70)	SPJ041L
.46"-.56" (1.17-1.42)	660 (2,936)	6" (15.24)	5" (13.33)	SPJ046U	12" (30.48)	5" (13.33)	SPJ046L
.52"-.62" (1.32-1.57)	790 (3,514)	7" (17.78)	6" (15.87)	SPJ052U	13" (33.02)	6" (15.87)	SPJ052L
.58"-.68" (1.47-1.73)	790 (3,514)	7" (17.78)	6" (16.51)	SPJ058U	13" (33.02)	6" (16.51)	SPJ058L
.64"-.75" (1.63-1.90)	790 (3,514)	7" (17.78)	6" (17.14)	SPJ064U	13" (33.02)	6" (17.14)	SPJ064L
.75"-.87" (1.90-2.21)	1,020 (4,537)	8" (20.32)	8" (20.32)	SPJ075U	14" (35.56)	8" (20.32)	SPJ075L
.87"-.1.00" (2.21-2.54)	1,020 (4,537)	8" (20.32)	8" (22.22)	SPJ087U	14" (35.56)	8" (22.22)	SPJ087L
1.00"-1.18" (2.54-3.00)	1,020 (4,537)	9" (22.86)	9" (24.13)	SPJ100U	15" (38.10)	9" (24.13)	SPJ100L
1.06"-1.25" (2.69-3.17)	1,020 (4,537)	9" (22.86)	9" (24.13)	SPJ106U	15" (38.10)	9" (24.13)	SPJ106L

CAUTION

Never use grip to approximate breaking strength. Refer to page N-26 for safety and working load factors. Banding is necessary to guard against accidental release of grip and provide maximum reliability.