



2 Position Single-Phase Cutout / Arrester Bracket (15°)



RUS Accepted.

Catalog Number	Length A	Minimum Ultimate*			Weight (Each)
		Vertical V	Longitudinal L	Transverse T	
Medium Duty 1 1/2" (38 mm) Dia. Fiberglass Rod					
1SBM12AMT	12" (30.5 cm)	1800 lbs. (817 kg)	1400 lbs. (635 kg)	10,000 lbs. (4536 kg)	6.6 lbs. (3.0 kg)
1SBM15AMT	15" (38.1 cm)	1500 lbs. (680 kg)	1100 lbs. (499 kg)	10,000 lbs. (4536 kg)	7.0 lbs. (3.2 kg)
1SBM18AMT	18" (45.7 cm)	1200 lbs. (544 kg)	950 lbs. (431 kg)	10,000 lbs. (4536 kg)	7.4 lbs. (3.3 kg)
1SBM24AMT	24" (61.0 cm)	900 lbs. (408 kg)	700 lbs. (318 kg)	10,000 lbs. (4536 kg)	7.8 lbs. (3.5 kg)
1SBM12AMTB	12" (30.5 cm)	1800 lbs. (817 kg)	1400 lbs. (635 kg)	10,000 lbs. (4536 kg)	6.6 lbs. (3.0 kg)
1SBM15AMTB	15" (38.1 cm)	1500 lbs. (680 kg)	1100 lbs. (499 kg)	10,000 lbs. (4536 kg)	7.0 lbs. (3.2 kg)
1SBM18AMTB	18" (45.7 cm)	1200 lbs. (544 kg)	950 lbs. (431 kg)	10,000 lbs. (4536 kg)	7.4 lbs. (3.3 kg)
1SBM24AMTB	24" (61.0 cm)	900 lbs. (408 kg)	700 lbs. (318 kg)	10,000 lbs. (4536 kg)	7.8 lbs. (3.5 kg)
Heavy Duty 2" (51 mm) Dia. Fiberglass Rod					
1SBH18AMT	18" (45.7 cm)	2250 lbs. (1021 kg)	1400 lbs. (635 kg)	10,000 lbs. (4536 kg)	9.6 lbs. (4.3 kg)
1SBH21AMT	21" (53.3 cm)	2100 lbs. (953 kg)	1250 lbs. (567 kg)	10,000 lbs. (4536 kg)	10.0 lbs. (4.5 kg)
1SBH24AMT	24" (61.0 cm)	1900 lbs. (862 kg)	1100 lbs. (499 kg)	10,000 lbs. (4536 kg)	10.4 lbs. (4.7 kg)
1SBH18AMTB	18" (45.7 cm)	2250 lbs. (1021 kg)	1400 lbs. (635 kg)	10,000 lbs. (4536 kg)	9.6 lbs. (4.3 kg)
1SBH21AMTB	21" (53.3 cm)	2100 lbs. (953 kg)	1250 lbs. (567 kg)	10,000 lbs. (4536 kg)	10.0 lbs. (4.5 kg)
1SBH24AMTB	24" (61.0 cm)	1900 lbs. (862 kg)	1100 lbs. (499 kg)	10,000 lbs. (4536 kg)	10.4 lbs. (4.7 kg)

*Recommended maximum working load is 50% of minimum ultimate ratings listed.

Consult factory for additional lengths.

Add "SC" suffix to the end of the catalog number to denote Silicone Coated rod