




3 Position (Cloverleaf) Single-Phase Cutout / Arrester Bracket (15°)



1/2" - 13 x 2"
Captive Carriage Bolt


1SBH—CLH Series
includes bolt, nut
and washers

Keyhole for 5/8"
Mounting Bolt



B

Bandable



Mounting Base and
Cloverleaf End Fitting are
aluminum alloy.

B Dimension is 8" & 10"

| Catalog Number | Length A | Minimum Ultimate* | | | Weight (Each) |
|--|---------------|---------------------|--------------------|-----------------------|-------------------|
| | | Vertical V | Longitudinal L | Transverse T | |
| Heavy Duty 2" (51 mm) Dia. Fiberglass Rod | | | | | |
| 1SBH18CL | 18" (45.7 cm) | 2250 lbs. (1021 kg) | 1400 lbs. (635 kg) | 10,000 lbs. (4536 kg) | 7.5 lbs. (3.4 kg) |
| 1SBH21CL | 21" (53.3 cm) | 2000 lbs. (907 kg) | 1250 lbs. (567 kg) | 10,000 lbs. (4536 kg) | 8.1 lbs. (3.7 kg) |
| 1SBH24CL | 24" (61.0 cm) | 1750 lbs. (794 kg) | 1100 lbs. (499 kg) | 10,000 lbs. (4536 kg) | 8.8 lbs. (4.0 kg) |
| 1SBH18CLH | 18" (45.7 cm) | 2250 lbs. (1021 kg) | 1400 lbs. (635 kg) | 10,000 lbs. (4536 kg) | 7.5 lbs. (3.4 kg) |
| 1SBH21CLH | 21" (53.3 cm) | 2000 lbs. (907 kg) | 1250 lbs. (567 kg) | 10,000 lbs. (4536 kg) | 8.1 lbs. (3.7 kg) |
| 1SBH24CLH | 24" (61.0 cm) | 1750 lbs. (794 kg) | 1100 lbs. (499 kg) | 10,000 lbs. (4536 kg) | 8.8 lbs. (4.0 kg) |

*Recommended maximum working load is 50% of minimum ultimate ratings listed.

Consult factory for additional lengths.

Add "SC" suffix to the end of the catalog number to denote Silicone Coated rod

