


Wire Management Products

Heavy Duty Underground Pulling Grips



PHS150




PH150

Application:

- Pulling underground power cables, communication lines and service lines
- Designed to be a reusable tool, pulling grips can be used in a variety of overhead and underground pulling applications
- Galvanized steel mesh is flexible for navigating through a variety of cable paths
- Multiple weave provides strength and positive gripping power

Ideal For Use In:

- Utility work
- Factory maintenance
- Construction



Rotating Eye, Closed Mesh Inches (cm)

Cable Diameter Range Inches (cm)	Approx. Breaking Strength Lbs. (N)	Inches (cm)		Rotating Eye Dia. Inches (cm)	Catalog Number
		E	M		
.50"- .61" (1.27-1.55)	4,800 (21,350)	5" (12.70)	16" (40.64)	7/8" (2.22)	PHS050
.62"- .74" (1.57-1.88)	6,800 (30,246)	5" (12.70)	16" (40.64)	7/8" (2.22)	PHS062
.75"- .99" (1.90-2.51)	9,600 (42,700)	6" (15.24)	32" (81.28)	1" (2.54)	PHS075
1.00"-1.49" (2.54-3.78)	16,400 (72,947)	7" (17.78)	33" (83.82)	1 3/8" (3.49)	PHS100
1.50"-1.99" (3.81-5.05)	16,400 (72,947)	7" (17.78)	34" (86.36)	1 3/8" (3.49)	PHS150
2.00"-2.49" (5.08-6.32)	27,200 (120,986)	9" (22.86)	36" (91.44)	1 5/8" (4.13)	PHS200
2.50"-2.99" (6.35-7.59)	33,000 (146,784)	10" (25.40)	38" (96.52)	1 7/8" (4.76)	PHS250
3.00"-3.49" (7.62-8.86)	41,000 (182,368)	10" (25.40)	39" (99.06)	1 7/8" (4.76)	PHS300
3.50"-3.99" (8.89-10.13)	48,000 (213,504)	10" (25.40)	41" (104.14)	1 7/8" (4.76)	PHS350
4.00"-4.49" (10.16-11.40)	48,000 (213,504)	10" (25.40)	42" (106.68)	1 7/8" (4.76)	PHS400
4.50"-4.99" (11.43-12.67)	48,000 (213,504)	10" (25.40)	58" (147.32)	1 7/8" (4.76)	PHS450
5.00"-5.99" (12.70-15.21)	40,000 (177,920)	10" (25.40)	60" (152.40)	1 7/8" (4.76)	PHS500
6.00"-6.99" (15.24-17.75)	54,000 (240,192)	10" (25.40)	66" (167.64)	1 7/8" (4.76)	PHS600

Note: Eye revolves when pressure is released to reduce twisting and turning. If constant swivel action is required, a swivel should be used. Rotating eye is not a swivel and will not turn under tension, it can turn to relieve pulling torque when the tension is relaxed.

Flexible Eye, Closed Mesh Inches (cm)

Cable Diameter Range Inches (cm)	Approx. Breaking Strength Lbs. (N)	Inches (cm)		Catalog Number
		E	M	
.50"- .61" (1.27-1.55)	4,500 (20,016)	8" (20.32)	21" (53.34)	PH050
.62"- .74" (1.57-1.88)	5,600 (24,909)	8" (20.32)	24" (60.96)	PH062
.75"- .99" (1.90-2.51)	6,800 (30,246)	9" (22.86)	24" (60.96)	PH075
1.00"-1.49" (2.54-3.78)	9,600 (42,701)	9" (22.86)	24" (60.96)	PH100
1.50"-1.99" (3.81-5.05)	16,400 (72,947)	11" (27.94)	24" (60.96)	PH150
2.00"-2.49" (5.08-6.32)	18,500 (82,288)	12" (30.48)	24" (60.96)	PH200
2.50"-2.99" (6.35-7.59)	24,500 (108,976)	12" (30.48)	24" (60.96)	PH250
3.00"-3.49" (7.62-8.86)	24,500 (108,976)	14" (35.56)	24" (60.96)	PH300
3.50"-3.99" (8.89-10.13)	31,000 (137,888)	14" (35.56)	26" (66.04)	PH350

CAUTION

Never use grip to approximate breaking strength. Refer to page N-26 for safety and working load factors. Banding is necessary to guard against accidental release of grip and provide maximum reliability.