Mechanical Grounding

Temporary Protective Ground Studs

The need for higher-rated grounding components and accessories is driven by continuous increases in the national electric grid's power capability. The ASTM F855 standard outlines specifications for temporary protective grounding with updates that reflect these changing requirements.

Temporary Protective Ground Studs are single point ground connections for Temporary Ground Sets. The H-Rated Ground Studs are designed and tested to meet the requirements of ASTM F855 Table 2. The ball stud covers serve as animal mitigation and stud surface protectant.

Features & Benefits

- Constructed of Tin-Plated Cast Copper alloy
- NEMA spaced terminal pad
- Animal mitigation / Stud Protector Cover Available
- Ball and Socket design accommodates industry standard Ground Set Clamps
- Available in Straight, 45°, and 90° variations
- Third-party laboratory test results available



Type GSC88

35mm Ground Ball Stud with 90° NEMA Pad								
Catalog Number	Description	Mounting Details & Orientation	Pad Angle	Ball Diameter	Rating			
GSC882NH35B7H	Ground Stud	1/2" holes with 1.75" NEMA Spacing; 90° Pad	Straight	35 mm (1.38")	Grade 7H			
GSC882NH35BCOVER	Ground Stud Cover	Not applicable for cover						

Type GSC75

0mm Ground Ball Stud with Inline NEMA Pad								
Catalog Number	Description	Mounting Details & Orientation	Pad Angle	Ball Diameter	Rating			
GSC752N30B5H	Ground Stud	1/2" holes with 1.75" NEMA Spacing; Inline Pad	Straight	30 mm (1.18")	Grade 5H			
GSC752N30B	Ground Stud	1/2" holes with 1.75" NEMA Spacing; Inline Pad	Straight	30 mm (1.18")	Grade 5			
GSC752N30B45	Ground Stud	1/2" holes with 1.75" NEMA Spacing; Inline Pad	45°	30 mm (1.18")	-			
GSC752N30B90	Ground Stud	1/2" holes with 1.75" NEMA Spacing; Inline Pad	90°	30 mm (1.18")	-			
GSC7530BCOVER	Ground Stud Cover	Not applicable for cover						

Type GSC63

25mm Ground Ball Stud 90° and Inline NEMA Pad								
Catalog Number	Description	Mounting Details & Orientation	Pad Angle	Ball Diameter	Rating			
GSC632NH1B	Ground Stud	1/2" holes with 1.75" NEMA Spacing; 90° Pad	Straight	25mm (1")	Grade 4			
GSC632NH25B5H	Ground Stud	1/2" holes with 1.75" NEMA Spacing; 90° Pad	Straight	25mm (1")	Grade 5H			
GSC632N25B5H	Ground Stud	1/2" holes with 1.75" NEMA Spacing; Inline Pad	Straight	25mm (1")	Grade 5H			
GSC632NH1BCOVER1	Ground Stud Cover	Not applicable for cover						

