


Fiberglass Crossarm Pin



**NYLON
THREAD
OPTION**



Base is Aluminum Alloy and End Fitting is hot-dip-galvanized ductile iron.

Catalog Number	Length A	Minimum Ultimate*			Weight (Each)
		Vertical V	Longitudinal L	Transverse T	
Medium Duty 1½" (38 mm) Dia. Fiberglass Rod					
1XPM131	13" (33.0 cm)	2500 lbs. (1134 kg)	1200 lbs. (544 kg)	1200 lbs. (544 kg)	2.4 lbs. (1.1 kg)
1XPM181	18" (45.7 cm)	2500 lbs. (1134 kg)	1000 lbs. (454 kg)	1000 lbs. (454 kg)	2.9 lbs. (1.3 kg)

*Recommended maximum working load is 50% of minimum ultimate ratings listed.

NOTES:

1XPM—1 series has 1" plastisol coated threads.

For 1" Nylon threads, replace the last "1" in number with "2"

For 1" Lead threads, replace the last "1" in number with "3".

For 1.375" Lead threads, replace the last "1" in number with "4".

Add "5" suffix for 5" mounting bolt.

Add "SC" suffix to the end of the catalog number to denote Silicone Coated rod