




ENCLOSURES

EXBLT SERIES

EXBLT Series is up to 35% lighter than EXB Series




Predrilled internal mounting pan bosses. Uses same mounting pans as the EXB series.




Hinges are extruded aluminum with stainless steel pin and hardware

Mounting lugs can be rotated 90°




Nitrile (BUNA-N) "O" ring gasket is located inside the bolt circle for wet locations, Type 4 & IP66



Ductile mounting lugs. Lugs are made of a ductile aluminum alloy to adjust to irregular mounting surfaces without damaging the enclosure. Easily replaced if damaged.

Fewer cover bolts required – faster in and out





JUNCTION BOXES

EXBLITE



EXBLT

Empty / Control Enclosure

NEC / CEC Certifications

Class I, Div. 1 & 2, Groups B, C, & D

Class I, Zone 1, IIB+H2

Class II, Div. 1 & 2, Groups E, F, & G

Class III

Type 3, 4, 4X

Ta = -25°C to +70°C (UL)

Ta = -50°C to +70°C (CSA)

UL Files E83969

IEC File LR11716 - 1723354

ATEX Certificate

II 2 G D CE 2813

Ex d IIB+H2 Gb 6 or T5

Ex tb IIIC Db IP66 T85°C or T100°C

Ta = -50°C to +70°C

QPS 21 ATEX 0001U

QPS 21 ATEX 0002X

IEC Ex Certificate

Ex db IIB+H2 Gb T6 or T5

Ex tb IIIC Db IP66 T85°C or T100°C

Ta = -50°C to +70°C

IECEX QPS 17.0013U

IECEX QPS 17.0014X

FEATURES-SPECIFICATIONS

EXBLT- For North America and for Global Applications by Adding Suffix "CEN".

Features

- The EXBLT Series is up to 35% lighter than the EXB Series enclosures.
- Copper-free cast/plate aluminum construction. High strength, lighter in weight, highly corrosion resistant.
- Choice of two covers:
 - » Flat aluminum plate cover (EXBLTP)
 - » Original aluminum sand cast cover (EXBLTC)
- Fewer cover bolts – reduces installation and maintenance time. Offered in plated carbon steel, 316SS and 316SS Tri-Lead for quicker access.
- Gasketed cover flange as standard. Nitrile (BUNA-N) "O" ring gasket is located inside the bolt circle to prevent water from seeping into the enclosure
- Mounting lugs are made of ductile aluminum alloy to adjust to irregular mounting surfaces without damaging the enclosure. EXBLTs 8x12x6x and larger supplied with bi-directional mounting pads. Lugs can installed either horizontal or vertical by the factory or in the field. Easily replaced if damage does occur.

- Hinges supplied as standard on the 6x12x4, 6x12x6 8x12x6 and larger. Smaller sizes can be ordered with hinges by adding SU2 to the catalog number. Hinges can be mounted on any of the 4 sides.
- Enclosures can be drilled and tapped with conduit openings up to 2" NPT or M63 in factory or field.
- Covers can be drilled and tapped (factory or field) for GZ Series control operators openings and EXH disconnect handles. The original aluminum sand cast cover, EXBLTC, can be provided with the GLXR rectangular viewing windows and the GL round threaded viewing windows.
- Cover flanges supplied with recessed notches for prying the covers open without damaging the ground flame path
- The mounting pan bosses are pre-drilled for the factory or field installation of the optional back pans

Material/Finish

- **BOX:** Molded from 356-T6 copper free aluminum, less than 1/10 of 1% copper alloy and less than 6% magnesium
- **COVER:** EXBLTP plate cover is made of 6061-T6 aluminum alloy
- **COVER:** EXBLTC cast from 310 copper free aluminum, less than 1/10 of 1% copper alloy and less than 6% magnesium
- **BOLTS:** Plated carbon steel
- **HINGES:** Extruded aluminum with stainless steel pin and hardware
- **OPTIONAL:** Mounting pans sheet aluminum 6061-T6 or 5052-H34
- **OPTIONAL:** Viewing windows tempered soda lime glass
- **FINISH:** Plate cover supplied with natural finish. Box and cast cover are painted with wet lacquer

Notes:


- Conduits must be sealed within 18" for Class I Group B applications
- All conduits or gland openings must be sealed adjacent to the wall for Ex d applications
- For Type 4X rating, add N4X or N4XTL



ENCLOSURES EXBLT SERIES

CATALOG LOGIC AND MODIFICATIONS

MODIFICATIONS	
SUFFIX NUMBER	DESCRIPTION
N4CEN	ATEX & IEC Ex Certifications, IP66 Type 4X
N4X	Stainless steel external hardware for Type 4X
N4TL	Tri-lead stainless steel external hardware for Type 4X
KIT-251	100 amp ground lug
KIT-252	200 amp ground lug
SU3B-QA	cCSAus, ATEX, IEC Ex drain and breather installed Class I Groups B, C, & D Ex d IIB + H2, Type 4, 4x IP66 (enclosures up to 28 liters*)
SU3B-4X	Drain and breather installed Class I Groups B, Type 4, 4X
SU2	Install hinges - EXB-8106 and smaller.
SU14	Fungus Proof Internal
SU9	Special paint
SU93	Do not paint



SUFFIXES ++

- SU3-B-4X** – Type 4X drain and breather installed Groups BCD
 - SU3-ATEX** – ATEX IEC Ex drain and breather installed Groups B and Ex d+IIB
 - SU2** – Install hinges - EXBLT-8106 and smaller
 - SU9** – Special paint
 - SU93** – Do not paint
- ++ Additional suffixes are available

ENVIRONMENTAL RATING

- N4** – Type 4 Steel external hardware
- N4X** – Type 4X Stainless steel external hardware
- N4TL** – Type 4X Tri-lead stainless steel external hardware
- N4CEN** – Type 4X, IP66 ATEX and IEC Ex Certifications

EXBLT - Global Application, IEC Ex and ATEX
 Add Suffix "N4CEN" to the catalog logic.

* For enclosures greater than 28 liters, the KBQA drain/breather can be ordered separately and new ratings are: Class I Groups C & D Ex d IIB, Type 4, 4x IP66. The chart below indicates which enclosures are less than 28 liters.

CATALOG NUMBER	NOMINAL ENCLOSURE INSIDE DIMENSIONS W" L" D" (MM)	MAXIMUM SIZES - NPT / METRIC	OPTIONAL MOUNTING PAN NUMBER	MAXIMUM NUMBER OF OPERATORS	EXBLTP WEIGHT LBS (KGS)	EXBLTC WEIGHT LBS (KGS)	EXBLTP HINGES	EXBLTC HINGES
EXBLT*-664 N4*	6x6x4 (152x152x102)	2" / M63	7997-5	2 rows of 2 = 4	18.2 (8.3)	20.4 (9.3)	HINGE-12L	HINGE-12L
EXBLT*-684 N4*	6x8x4 (152x203x102)	2" / M63	7997-1	2 rows of 3 = 6	21.1 (9.6)	22.7 (10.3)	HINGE-12L	HINGE-12L
EXBLT*-686 N4*	6x8x6 (152x203x152)	2" / M63	7997-1	2 rows of 3 = 6	23.7 (10.8)	25.3 (11.5)	HINGE-12L	HINGE-12L
EXBLT*-6124 N4*	6x12x4 (152x305x102)	2" / M63	7997-6	4 rows of 2 = 8	29.2 (13.2)	39.2 (17.8)	HINGE-12L	HINGE-12L
EXBLT*-6126 N4*	6x12x6 (152x305x152)	2" / M63	7997-6	4 rows of 2 = 8	32.6 (14.8)	42.6 (19.3)	HINGE-12L	HINGE-12L
EXBLT*-886 N4*	8x8x6 (203x203x152)	2" / M63	7996-1	3 rows of 3 = 9	27.9 (12.7)	32.6 (17.8)	HINGE-12L	HINGE-12L
EXBLT*-8104 N4*	8x10x4 (203x254x102)	2" / M63	7996-2	4 rows of 3 = 12	28.6 (13)	35.5 (16.1)	HINGE-12L	HINGE-12L
EXBLT*-8106 N4*	8x10x6 (203x254x152)	2" / M63	7996-2	4 rows of 3 = 12	31.9 (14.5)	38.8 (17.6)	HINGE-12L	HINGE-12L
EXBLT*-8126 N4*	8x12x6 (203x305x152)	2" / M63	17619	4 rows of 3 = 12	46.9 (21.3)	58.3 (26.4)	HINGE-12L	HINGE-11L
EXBLT*-8128 N4*	8x12x8 (203x305x203)	2" / M63	17619	4 rows of 3 = 12	51.6 (23.4)	63 (28.6)	HINGE-12L	HINGE-11L
EXBLT*-9116 N4*	9x11x6 (229x280x152)	2" / M63	25803	4 rows of 3 = 12	36.2 (16.4)	42.5 (19.3)	HINGE-12L	HINGE-12L
EXBLT*-10106 N4*	10x10x6 (254x254x152)	2" / M63	17618	4 rows of 3 = 12	48.8 (22.1)	64.5 (29.3)	HINGE-12L	HINGE-11L
EXBLT*-10108 N4*	10x10x8 (254x254x203)	2" / M63	17618	4 rows of 3 = 12	53.5 (24.3)	69.2 (31.4)	HINGE-12L	HINGE-11L
EXBLT*-10146 N4*	10x14x6 (254x356x152)	2" / M63	17617	5 rows of 3 = 15	59.7 (27.07)	77.9 (35.3)	HINGE-12L	HINGE-11L
EXBLT*-10148 N4*	10x14x8 (254x356x203)	2" / M63	17617	5 rows of 3 = 15	65.3 (29.6)	83.5 (37.9)	HINGE-12L	HINGE-11L
EXBLT*-12126 N4*	12x12x6 (305x305x152)	2" / M63	7988-1	4 rows of 4 = 16	55 (25)	71.8 (32.6)	HINGE-12L	HINGE-11L
EXBLT*-12128 N4*	12x12x6 (305x305x203)	2" / M63	7988-1	4 rows of 4 = 16	60.3 (27.4)	77.1 (35)	HINGE-12L	HINGE-11L
EXBLT*-12186 N4*	12x18x6 (305x457x152)	2" / M63	15515	7 rows of 4 = 28	82 (37.2)	93 (42.2)	HINGE-11L	HINGE-11L
EXBLT*-12188 N4	12x18x8 (305x457x203)	2" / M63	15515	7 rows of 4 = 28	89 (40.7)	100 (45.4)	HINGE-11L	HINGE-11L
EXBLT*-12246 N4*	12x24x6 (305x610x152)	4" / M100	7988-4	9 rows of 4 = 36	110 (50)	133 (60.3)	HINGE-11L	HINGE-11L
EXBLT*-12248 N4	12x24x8 (305x610x203)	4" / M100	7988-4	9 rows of 4 = 36	122 (55.4)	145 (65.8)	HINGE-11L	HINGE-11L
EXBLT*-14148 N4*	14x14x8 (356x356x203)	2" / M63	17621	5 rows of 5 = 25	88 (40)	108 (49)	HINGE-11L	HINGE-11L
EXBLT*-14248 N4	14x24x8 (406x610x203)	4" / M100	51705-1	9 rows of 5 = 45	142 (64.4)	N/A	HINGE-11L	HINGE-11L
EXBLT*-14308 N4	14x30x8 (406x762x203)	4" / M100	51698-1	11 rows of 5 = 55	166 (75.3)	N/A	HINGE-11L	HINGE-11L
EXBLT*-16168 N4	16x16x8 (406x406x203)	2" / M63	7995-1	6 rows of 6 = 36	98 (44.4)	118 (53.5)	HINGE-11L	HINGE-11L
EXBLT*-16248 N4	16x24x8 (406x610x203)	5" / M100	17622	8 rows of 5 = 40	166 (75.3)	213 (96.6)	HINGE-11L	HINGE-11L

* Add "P" for aluminum plate cover. Add "C" for sand cast cover. Cast cover not available for 14x24x8 and 14x30x8 sizes.

+ Enclosures less than 28 liters. KBQA breather/drain rated for Class I Groups B, C, & D Ex d IIB + H2, Type 4, 4x IP66.

Mounting Pan - Order mounting pan as separate item and specify if factory of field installed.

Note: For Group B applications all conduit must be sealed within 18" of enclosure wall.


Note: For IEC Ex applications all conduit must be sealed at the wall of the enclosure.



DIMENSIONS

ENCLOSURE CATALOG NUMBER	INTERNAL DIMENSIONS - INCHES (MM)						EXTERNAL DIMENSIONS - INCHES (MM)			
	PAN		AVAILABLE EQUIPMENT SPACE				F	G	H ("P" PLATE)	H ("C" CAST)
	A	B	C	D	E ("P" PLATE)	E ("C" CAST)				
EXBLT-664 N4	5 (127)	5 (127)	6 (152)	6 (152)	4 (102)	4.25 (108)	10.32 (262)	10.32 (262)	5.94 (151)	6.18 (157)
EXBLT-684 N4	5 (127)	7 (178)	6 (152)	8 (203)	4 (102)	4.32 (110)	10.25 (260)	12.25 (311)	5.88 (149)	6.13 (156)
EXBLT-686 N4	5 (127)	7 (178)	6 (152)	8 (203)	6 (152)	6.32 (160)	10.25 (260)	12.25 (311)	7.88 (200)	8.13 (206)
EXBLT-6124 N4	5 (127)	11 (279)	6.25 (159)	12.25 (311)	4 (102)	4.56 (116)	10.69 (272)	16.69 (424)	5.88 (149)	6.75 (171)
EXBLT-6126 N4	5 (127)	11 (279)	6.25 (159)	12.25 (311)	6 (152)	6.56 (167)	10.69 (272)	16.69 (424)	7.88 (200)	8.75 (222)
EXBLT-886 N4	7 (178)	7 (178)	8 (203)	8 (203)	6 (152)	6.16 (156)	12.32 (313)	12.32 (313)	7.94 (202)	8.34 (212)
EXBLT-8104 N4	7 (178)	9 (229)	8 (203)	10 (254)	4 (102)	4.18 (106)	12.32 (313)	14.32 (364)	5.94 (151)	6.53 (166)
EXBLT-8106 N4	7 (178)	9 (229)	8 (203)	10 (254)	6 (152)	6.18 (157)	12.32 (313)	14.32 (364)	7.94 (202)	8.53 (217)
EXBLT-8126 N4	7 (178)	11 (279)	8.5 (216)	12.5 (318)	6 (152)	6.6 (167)	13.25 (337)	17.25 (438)	8 (203)	8.88 (225)
EXBLT-8128 N4	7 (178)	11 (279)	8.5 (216)	12.5 (318)	8 (203)	8.6 (218)	13.25 (337)	17.25 (438)	10 (254)	10.88 (276)
EXBLT-9116 N4	8 (203)	10 (254)	9 (229)	11 (279)	6 (152)	6.18 (157)	13.32 (338)	15.32 (389)	7.94 (202)	8.53 (217)
EXBLT-10106 N4	9 (229)	9 (229)	10.5 (267)	10.5 (267)	6 (152)	6.41 (163)	15.25 (387)	15.25 (387)	8.18 (208)	9.13 (232)
EXBLT-10108 N4	9 (229)	9 (229)	10.5 (267)	10.5 (267)	8 (203)	8.41 (214)	15.25 (387)	15.25 (387)	10.18 (259)	11.13 (284)
EXBLT-10146 N4	9 (229)	13 (330)	10.5 (267)	14.5 (368)	6 (152)	6.22 (158)	15.25 (387)	19.25 (489)	8.18 (208)	9.13 (232)
EXBLT-10148 N4	9 (229)	13 (330)	10.5 (267)	14.5 (368)	8 (203)	8.22 (209)	15.25 (387)	19.25 (489)	10.18 (259)	11.13 (284)
EXBLT-12126 N4	10.5 (267)	10.5 (267)	11.87(301)	11.87(301)	6 (152)	6.3 (160)	16.38 (416)	16.38 (416)	8.18 (208)	9.06 (230)
EXBLT-12128 N4	10.5 (267)	10.5 (267)	11.87(301)	11.87(301)	8 (203)	8.3 (211)	16.38 (416)	16.38 (416)	10.18 (259)	11.06 (281)
EXBLT-12186 N4	10 (254)	16 (406.4)	11.88 (301)	17.88 (454)	6 (152)	6.09 (155)	16.38 (416)	22.38 (568.4)	8.44 (214.4)	8.97 (228)
EXBLT-12188 N4	10 (254)	16 (406.4)	11.88 (301)	17.88 (454)	8 (203)	8.09 (206)	16.38 (416)	22.38 (568.4)	10.44 (265)	10.97 (279)
EXBLT-12246 N4	10.25 (260)	22.25 (565)	11.88 (301)	23.88 (606)	6 (152)	6.13 (156)	16.38 (416)	28.38 (722)	8.57 (218)	9.28 (236)
EXBLT-12248 N4	10.25 (260)	22.25 (565)	11.88 (301)	23.88 (606)	8 (203)	8.13 (206)	16.38 (416)	28.38 (722)	10.57 (268.5)	11.28 (286)
EXBLT-14148 N4	13 (330)	13 (330)	14.5 (368)	14.5 (368)	8 (203)	8.34 (212)	19.25 (489)	19.25 (489)	10.44 (265)	11.34 (288)
EXBLT-14248 N4	13 (330)	22.25 (565)	14.5 (368)	24.5 (622)	8 (203)	N/A	19.25 (489)	29.25 (743)	10.57 (268.5)	N/A
EXBLT-14308 N4	13 (330)	29 (736)	14.5 (368)	30.5 (775)	8 (203)	N/A	19.25 (489)	35.25 (895.3)	10.57 (268.5)	N/A
EXBLT-16168 N4	14 (355)	14 (355)	15.88 (403)	15.88 (403)	8 (203)	8.14 (207)	20.38 (518)	20.38 (518)	10.44 (265)	11.11 (282)
EXBLT-16248 N4	15 (381)	23 (584)	16.5 (419)	24.5 (622)	8 (203)	8.34 (212)	21.25 (540)	29.25 (743)	10.69 (271.5)	11.91 (302)

All dimensions in. (mm)






ENCLOSURES

EXBLT SERIES

ENCLOSURE CATALOG NUMBER	MOUNTING DIMENSIONS - INCHES (MM)						CONDUIT AREA - INCHES (MM)					OPERATOR AREA SPECIFICATION	
							SIDE WALL		CENTER	TOP/ BOTTOM WALL			
	I	J	K	L	M	SLOT WIDTH	O	Q	R	S	U	W	X
EXBLT-664 N4	N/A	4 (102)	7.88 (200)	N/A	0.19 (5)	0.44 (11)	2.81 (71)	4.72 (120)	2.75 (70)	4.72 (120)	2.5 (63)	5 (127)	5 (127)
EXBLT-684 N4	N/A	4 (102)	7.88 (200)	N/A	0.19 (5)	0.44 (11)	2.81 (71)	6.59 (167)	2.75 (70)	4.59 (117)	2.5 (63)	5 (127)	5 (127)
EXBLT-686 N4	N/A	4 (102)	7.88 (200)	N/A	0.19 (5)	0.44 (11)	4.81 (122)	6.59 (167)	3.75 (95)	4.59 (117)	2.5 (63)	5 (127)	5 (127)
EXBLT-6124 N4	N/A	7.82 (199)	7.88 (200)	N/A	0.19 (5)	0.44 (11)	2.81 (71)	10.84 (275)	2.75 (70)	4.84 (123)	2.5 (63)	5 (127)	5 (127)
EXBLT-6126 N4	N/A	7.82 (199)	7.88 (200)	N/A	0.19 (5)	0.44 (11)	4.81 (122)	10.84 (275)	3.75 (95)	4.84 (123)	2.5 (63)	5 (127)	5 (127)
EXBLT-886 N4	N/A	6 (152)	9.88 (251)	N/A	0.19 (5)	0.44 (11)	4.81 (122)	6.56 (167)	3.75 (95)	6.56 (167)	2.5 (63)	7 (178)	7 (178)
EXBLT-8104 N4	N/A	8 (203)	9.88 (251)	N/A	0.19 (5)	0.44 (11)	2.81 (71)	8.56 (217)	2.75 (70)	6.56 (167)	2.5 (63)	7 (178)	7 (178)
EXBLT-8106 N4	N/A	8 (203)	9.88 (251)	N/A	0.19 (5)	0.44 (11)	4.81 (122)	8.56 (217)	3.75 (95)	6.56 (167)	2.5 (63)	7 (178)	7 (178)
EXBLT-8126 N4	3.82 (97)	7.82 (199)	10.38 (264)	14.38 (365)	0.19 (5)	0.44 (11)	3.94 (100)	10.13 (257)	3.95 (100)	6.13 (156)	2.5 (63)	7 (178)	7 (178)
EXBLT-8128 N4	3.82 (97)	7.82 (199)	10.38 (264)	14.38 (365)	0.19 (5)	0.44 (11)	5.94 (151)	9.97 (253)	4.95 (126)	5.97 (152)	2.5 (63)	7 (178)	7 (178)
EXBLT-9116 N4	N/A	7.5 (191)	10.88 (276)	N/A	0.19 (5)	0.44 (11)	4.81 (122)	9.56 (243)	3.81 (97)	7.56 (192)	2.5 (63)	8 (203)	8 (203)
EXBLT-10106 N4	4.94 (125)	4.94 (125)	12.94 (329)	12.94 (329)	0.25 (6)	0.56 (14)	3.94 (100)	8.13 (206)	4.09 (104)	8.13 (206)	2.5 (63)	9 (229)	9 (229)
EXBLT-10108 N4	4.94 (125)	4.94 (125)	12.94 (329)	12.94 (329)	0.25 (6)	0.56 (14)	5.94 (151)	7.97 (202)	5.09 (129)	7.97 (202)	2.5 (63)	9 (229)	9 (229)
EXBLT-10146 N4	4.94 (125)	8.94 (227)	12.94 (329)	16.94 (430)	0.25 (6)	0.56 (14)	3.94 (100)	12.13 (308)	4.09 (104)	8.13 (206)	2.5 (63)	9 (229)	9 (229)
EXBLT-10148 N4	4.94 (125)	8.94 (227)	12.94 (329)	16.94 (430)	0.25 (6)	0.56 (14)	5.94 (151)	11.97 (303)	5.09 (129)	7.97 (202)	2.5 (63)	9 (229)	9 (229)
EXBLT-12126 N4	6.94 (176)	6.94 (176)	14.94 (379)	14.94 (379)	0.25 (6)	0.56 (14)	3.94 (100)	9.5 (241)	4.09 (104)	9.5 (241)	2.5 (63)	10 (254)	10 (254)
EXBLT-12128 N4	6.94 (176)	6.94 (176)	14.94 (379)	14.94 (379)	0.25 (6)	0.56 (14)	5.94 (151)	9.34 (237)	5.09 (129)	9.34 (237)	2.5 (63)	10 (254)	10 (254)
EXBLT-12186 N4	6.94 (176)	12.88 (327)	14.94 (379)	20.88 (530)	0.25 (6)	0.56 (14)	3.88 (98)	15.5 (394)	4.03 (102)	9.5 (241)	2.5 (63)	10 (254)	10 (254)
EXBLT-12188 N4	6.94 (176)	12.88 (327)	14.94 (379)	20.88 (530)	0.25 (6)	0.56 (14)	5.88 (149)	15.34 (390)	5.03 (128)	9.34 (237)	2.5 (63)	10 (254)	10 (254)
EXBLT-12246 N4	6.94 (176)	18.88 (480)	14.91 (379)	26.88 (683)	0.25 (6)	0.56 (14)	3.88 (98)	21.5 (546)	4.03 (102)	9.5 (241)	2.5 (63)	10 (254)	10 (254)
EXBLT-12248 N4	6.94 (176)	18.88 (480)	14.91 (379)	26.88 (683)	0.25 (6)	0.56 (14)	5.88 (149)	21.34 (542)	5.03 (128)	9.34 (237)	2.5 (63)	10 (254)	10 (254)
EXBLT-14148 N4	9.00 (229)	9.00 (229)	17 (432)	17 (432)	0.25 (6)	0.56 (14)	5.94 (151)	11.97 (304)	5.09 (129)	11.97 (304)	2.5 (63)	13 (330)	13 (330)
EXBLT-14248 N4	9.00 (229)	19.38 (492)	17 (432)	27.38 (695)	0.25 (6)	0.56 (14)	5.88 (149)	21.97 (686)	5.16 (131)	11.97 (304)	2.5 (63)	13 (330)	13 (330)
EXBLT-14308 N4	9.00 (229)	26.25 (668)	17 (432)	34.25 (870)	0.25 (6)	0.56 (14)	5.94 (151)	27.97 (710)	5.19 (132)	11.97 (304)	2.5 (63)	13 (330)	13 (330)
EXBLT-16168 N4	10.94 (278)	10.94 (278)	17.19 (437)	18.94 (481)	0.25 (6)	0.56 (14)	5.94 (151)	13.34 (339)	5.06 (129)	13.34 (339)	2.5 (63)	14 (356)	14 (356)
EXBLT-16248 N4	10.94 (278)	19.38 (492)	19.38 (492)	27.38 (695)	0.25 (6)	0.56 (14)	5.94 (151)	21.97 (686)	5.31 (135)	13.97 (355)	2.5 (63)	14 (356)	14 (356)

Use "LONG" style GZ Series Operators

All dimensions in. (mm)





CONDUIT OPENING DATA

Instructions


Drilled and tapped conduit openings will be evenly spaced and located in the area indicated on the location chart. Critical conduit opening locations may be indicated by supplying a diagram similar to the one shown at right indicating critical dimensions and locations. Specific conduit openings must be located dimensionally from box centerlines to conduit centerlines and from outside back surface of box to conduit centerline.

Ordering Information:

- (1) Select the letter on location chart which indicates conduit opening position desired.
- (2) Select symbol number from chart which indicates conduit opening type and size.

- (3) Combine the conduit location letter, size and type number, and add as a suffix to junction box catalog number.

Example: EXB-12248 N34-C3-J5-PI3-AH4



Drawing indicates position as looking into open face of box with short side (top) up.

EXB/EXBLT/B7/GR SYMBOL NUMBERS		
CONDUIT SIZE	CONDUIT OPENINGS DRILLED AND TAPPED	UNION
1/2"	1	11
3/4"	2	12
1"	3	13
1-1/4"	4	14
1-1/2"	5	15
2"	6	16
2-1/2"	7	17
3"	8	18
3-1/2"	9	19
4"	0	10
5"	02	—
6"	04	—

Union = GUM series male NPT unions

EXB/EXBLT/B7/GR - MINIMUM CENTER TO CENTER SPACING FOR DRILLED AND TAPPED OPENINGS AND UNION HUBS													
NPT (METRIC)	SPACE CENTERS	1/2" (M16)	3/4" (M20)	1" (M25)	1-1/4" (M32)	1-1/2" (M40)	2" (M50)	2-1/2" (M63)	3" (M75)	3-1/2" (M80)	4" (M100)	5"	6"
1/2" (M16)	MIN	1.18 (30)	—	—	—	—	—	—	—	—	—	—	—
	PRE	1.38 (35)	—	—	—	—	—	—	—	—	—	—	—
	GU	1.63 (41)	—	—	—	—	—	—	—	—	—	—	—
3/4" (M20)	MIN	1.38 (35)	1.5 (38)	—	—	—	—	—	—	—	—	—	—
	PRE	1.5 (38)	1.63 (41)	—	—	—	—	—	—	—	—	—	—
	GU	1.75 (44)	1.81 (46)	—	—	—	—	—	—	—	—	—	—
1" (M25)	MIN	1.5 (38)	1.75 (44)	1.81 (46)	—	—	—	—	—	—	—	—	—
	PRE	1.75 (44)	1.88 (48)	2 (108)	—	—	—	—	—	—	—	—	—
	GU	1.88 (48)	2 (108)	2.13 (54)	—	—	—	—	—	—	—	—	—
1-1/4" (M32)	MIN	1.69 (43)	1.94 (49)	2.06 (52)	2.31 (59)	—	—	—	—	—	—	—	—
	PRE	1.94 (49)	2.06 (52)	2.25 (57)	2.5 (64)	—	—	—	—	—	—	—	—
	GU	2.06 (52)	2.25 (57)	2.31 (59)	2.5 (64)	—	—	—	—	—	—	—	—
1-1/2" (M40)	MIN	1.94 (49)	2.06 (52)	2.19 (56)	2.5 (64)	2.63 (67)	—	—	—	—	—	—	—
	PRE	2.13 (54)	2.25 (57)	2.38 (60)	2.63 (67)	2.75 (70)	—	—	—	—	—	—	—
	GU	2.19 (56)	2.28 (58)	2.44 (62)	2.63 (67)	2.75 (70)	—	—	—	—	—	—	—
2" (M50)	MIN	2.25 (57)	2.38 (60)	2.56 (65)	2.81 (71)	2.94 (75)	3.19 (81)	—	—	—	—	—	—
	PRE	2.38 (60)	2.5 (64)	2.75 (70)	3 (76)	3.13 (97)	3.38 (86)	—	—	—	—	—	—
	GU	2.5 (64)	2.59 (66)	2.75 (70)	3 (76)	3.13 (97)	3.38 (86)	—	—	—	—	—	—
2-1/2" (M63)	MIN	2.44 (62)	2.56 (65)	2.75 (70)	3 (76)	3.13 (97)	3.38 (86)	3.63 (92)	—	—	—	—	—
	PRE	2.63 (67)	2.75 (70)	3 (76)	3.25 (82)	3.38 (86)	3.63 (92)	4 (102)	—	—	—	—	—
	GU	3.13 (97)	3.22 (82)	3.38 (86)	3.56 (90)	3.69 (94)	4 (102)	4.63 (117)	—	—	—	—	—
3" (M75)	MIN	2.81 (71)	2.94 (75)	3.06 (78)	3.31 (84)	3.44 (87)	3.75 (95)	4 (102)	4.31 (110)	—	—	—	—
	PRE	3 (76)	3.13 (97)	3.38 (86)	3.63 (92)	3.75 (95)	4 (102)	4.38 (111)	4.75 (121)	—	—	—	—
	GU	3.56 (90)	3.66 (93)	3.81 (97)	4 (102)	4.13 (105)	4.44 (113)	5.06 (129)	5.5 (140)	—	—	—	—
3-1/2" (M80)	MIN	3.13 (97)	3.25 (82)	3.38 (86)	3.63 (92)	3.75 (95)	4.06 (103)	4.31 (110)	4.63 (117)	4.94 (125)	—	—	—
	PRE	3.38 (86)	3.5 (89)	3.63 (92)	3.88 (98)	4 (102)	4.38 (111)	4.63 (117)	5 (127)	5.38 (136)	—	—	—
	GU	4 (102)	4.09 (104)	4.25 (108)	4.44 (113)	4.56 (116)	4.88 (124)	5.5 (140)	5.94 (151)	6.38 (162)	—	—	—
4" (M100)	MIN	3.44 (87)	3.56 (90)	3.69 (94)	3.94 (100)	4.06 (103)	4.38 (111)	4.63 (117)	4.94 (125)	5.25 (133)	5.56 (141)	—	—
	PRE	3.75 (95)	3.88 (98)	4 (102)	4.25 (108)	4.38 (111)	4.75 (121)	5 (127)	5.75 (146)	5.63 (143)	6 (152)	—	—
	GU	4 (102)	4.09 (104)	4.25 (108)	4.44 (113)	4.56 (116)	4.88 (124)	5.5 (140)	5.94 (151)	6.38 (162)	6.38 (162)	—	—
5"	MIN	4.13 (105)	4.25 (108)	4.38 (111)	4.63 (117)	4.75 (121)	5 (127)	5.25 (133)	5.56 (141)	5.88 (149)	6.19 (157)	6.19 (157)	—
	PRE	4.38 (111)	4.5 (114)	4.63 (117)	4.88 (124)	5 (127)	5.38 (136)	5.63 (143)	6 (152)	6.25 (159)	6.63 (168)	7.25 (184)	—
	MIN	4.75 (121)	4.88 (124)	5 (127)	5.25 (133)	5.38 (136)	5.63 (143)	5.88 (149)	6.19 (157)	6.5 (165)	6.81 (173)	7.44 (190)	8.13 (206)
6"	MIN	5 (127)	5.13 (130)	5.25 (133)	5.5 (140)	5.63 (143)	6 (152)	6.25 (159)	6.63 (168)	7 (178)	7.25 (184)	8 (203)	8.63 (220)
	LOCKNUT O.D.	1.25 (32)	1.13 (29)	1.69 (43)	2.19 (56)	2.44 (62)	3 (76)	3.44 (87)	4.19 (106)	4.81 (122)	5.38 (136)	6.69 (170)	7.94 (202)
	CONDUIT BUSHING	1 (25)	1.25 (32)	1.5 (38)	1.88 (48)	2.13 (54)	2.63 (67)	3.19 (81)	3.88 (98)	4.44 (113)	5 (127)	6.25 (159)	7.38 (187)
CONDUIT O.D.		1.06 (27)	1.38 (35)	1.69 (43)	1.94 (49)	2.38 (60)	2.88 (73)	3.5 (89)	4 (102)	4.5 (114)	5.56 (141)	6.63 (168)	

All dimension in. (mm)

- MIN:** The minimum space required to provide enough clearance over locknuts and bushings.
- PRE:** The preferred more liberal center to center spacing of openings. To be used whenever possible.
- GU:** The required spacing between openings using GUM Series male NPT unions.



REPLACEMENT PARTS

REPLACEMENT PARTS										
ENCLOSURE CATALOG NUMBER	COVER GASKET	MOUNTING LUG KIT (Contains four mounting lugs and hardware)	COVER BOLTS – SOLD PER EACH						HINGES	
			NO. OF BOLTS PER ENCLOSURE	CARBON STEEL “N4”	316 STAINLESS STEEL “N4X”	316 STAINLESS STEEL TRI-LEAD PLATE COVERS “N4XTL”	316 STAINLESS STEEL TRI-LEAD CAST COVERS “N4XTL”	ATEX IEC EX 316 STAINLESS STEEL “N4CEN”	EXBLTP BOXES (*) ADD “L” FOR LEFT OR “R” FOR RIGHT	EXBLTC BOXES (*) ADD “L” FOR LEFT OR “R” FOR RIGHT
EXBLT*-664 N4	EXB66RG	EXB-MTL1	8	0725115B	25952BAAB	xxxxx	xxxxx	20790AAAB	HINGE-12*	HINGE-12*
EXBLT*-684 N4	EXB68RG	EXB-MTL1	10	0725115B	25952BAAB	xxxxx	xxxxx	20790AAAB	HINGE-12*	HINGE-12*
EXBLT*-686 N4	EXB68RG	EXB-MTL1	10	0725115B	25952BAAB	xxxxx	xxxxx	20790AAAB	HINGE-12*	HINGE-12*
EXBLT*-6124 N4	EXB612RG	EXB-MTL1	12	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-12*	HINGE-12*
EXBLT*-6126 N4	EXB612RG	EXB-MTL1	12	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-12*	HINGE-12*
EXBLT*-886 N4	EXB88RG	EXB-MTL1	12	0725115B	25952BAAB	xxxxx	xxxxx	20790AAAB	HINGE-12*	HINGE-12*
EXBLT*-8104 N4	EXB810RG	EXB-MTL1	14	0725115B	25952BAAB	xxxxx	xxxxx	20790AAAB	HINGE-12*	HINGE-12*
EXBLT*-8106 N4	EXB810RG	EXB-MTL1	14	0725115B	25952BAAB	xxxxx	xxxxx	20790AAAB	HINGE-12*	HINGE-12*
EXBLT*-8126 N4	EXB812RG	EXB-MTL1	12	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-12*	HINGE-11*
EXBLT*-8128 N4	EXB812RG	EXB-MTL1	12	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-12*	HINGE-11*
EXBLT*-9116 N4	EXB911RG	EXB-MTL1	14	0725115B	25952BAAB	xxxxx	xxxxx	20790AAAB	HINGE-12*	HINGE-12*
EXBLT*-10106 N4	EXB1010RG	EXB-MTL2	12	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-12*	HINGE-11*
EXBLT*-10108 N4	EXB1010RG	EXB-MTL2	12	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-12*	HINGE-11*
EXBLT*-10146 N4	EXB1014RG	EXB-MTL2	16	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-12*	HINGE-11*
EXBLT*-10148 N4	EXB1014RG	EXB-MTL2	16	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-12*	HINGE-11*
EXBLT*-12126 N4	EXB1212RG	EXB-MTL2	16	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-12*	HINGE-11*
EXBLT*-12128 N4	EXB1212RG	EXB-MTL2	16	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-12*	HINGE-11*
EXBLT*-12186 N4	EXB1218RG	EXB-MTL2	28	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-11*	HINGE-11*
EXBLT*-12188 N4	EXB1218RG	EXB-MTL2	28	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-11*	HINGE-11*
EXBLT*-12246 N4	EXB1224RG	EXB-MTL2	36	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-11*	HINGE-11*
EXBLT*-12248 N4	EXB1224RG	EXB-MTL2	36	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-11*	HINGE-11*
EXBLT*-14148 N4	EXB1224RG	EXB-MTL2	20	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-11*	HINGE-11*
EXBLT*-14248 N4	EXB1224RG	EXB-MTL2	28	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-11*	HINGE-11*
EXBLT*-14308 N4	EXB1224RG	EXB-MTL2	36	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-11*	HINGE-11*
EXBLT*-16168 N4	EXB1224RG	EXB-MTL2	24	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-11*	HINGE-11*
EXBLT*-16248 N4	EXB1224RG	EXB-MTL2	30	0720361B	25952AAAB	25904AAAB	17339AAAB	20790BAAB	HINGE-11*	HINGE-11*

Hinges

Hinges are provided as a standard on EXBLT*-6124, EXBLT*-6126 and sizes EXBLT*-8126 and larger. See chart for replacement hinge catalog number. Sold in sets of (2).

“G” Series Operators

The EXBLT* uses the GZ Long Style operators.

Touch-Up Paint

The touch-up paint comes in a 12 oz aerosol can.

Wet lacquer silver gray touch-up paint: KTPALS.

Epoxy powder gray touch-up paint: KTPEPG.



BLANK MOUNTING PANS

EXB / EXBLT Series Mounting Pans Ordering Instructions

Select proper mounting pan based on inside (length and width) of box. Order and price as separate item from junction box catalog number.

EXAMPLE:


EXB-12186N34 (box)
15155 (mounting pan) } assembly

EXB / EXBLT Series boxes have cast bosses which are drilled and tapped for direct mounting when pans are ordered.

Mounting pans are 1/8" or 3-16" thick sheet aluminum and are sized to provide the maximum usable surface area when installed.

All EXB / EXBLT series boxes have internal bosses that are factory machined to accept mounting pans.

Dimensions



CATALOG NUMBER	NOMINAL INSIDE BOX SIZE		MOUNTING PAN DIMENSION		MOUNTING HOLE SPACINGS			PAN THICKNESS
	WIDTH	LENGTH	A WIDTH	B LENGTH	C	D	E	
7997-5	6"	6"	5"	5"	3"	3"	—	.125
7997-1	6"	8"	5"	7"	5"	3"	—	.125
7997-6	6"	12"	5"	11"	9"	3"	—	.125
7996-1	8"	8"	7"	7"	5"	5"	—	.125
7996-2	8"	10"	7"	9"	7"	5"	—	.125
17619	8"	12"	7"	11"	9"	5"	—	.125
17617	10"	14"	9"	13"	11"	7"	—	.125
17618	10"	10"	9"	9"	7"	7"	—	.125
7988-1	12"	12"	10-1/2"	10-1/2"	9"	9"	—	.125
15515	12"	18"	10"	16"	15"	9"	—	.125
7988-4	12"	24"	10-1/4"	22-1/4"	21"	9"	—	.125
17620	12"	36"	11"	35"	33"	9"	17-1/2"	.125
17621	14"	14"	13"	13"	11"	11"	—	.125
51705-1	14"	24"	12-1/2"	22-1/2"	11"	21"	—	.125
51698-1	14"	30"	12-1/2"	28-1/2"	11"	27"	13-1/2"	.125
7995-1	16"	16"	14"	14"	13"	13"	—	.125
7995-2	16"	24"	14-1/2"	23"	21"	13"	—	.125
17622	16"	24"	15"	23"	21"	13"	—	.125
17623	18"	18"	17"	17"	15"	15"	—	.190
15516	18"	24"	16-3/8"	22-1/8"	21"	15"	—	.125
22061	18"	30"	16"	29"	28"	15"	14"	.125
15517	18"	36"	16"	34"	33"	15"	16-1/2"	.125
17596	20"	36"	18-3/4"	34-3/4"	32-3/4"	16-3/4"	16-3/8"	.190
8000-1	24"	24"	22-1/4"	22-1/4"	21"	21"	—	.125
17624	24"	36"	23"	35"	33"	21"	16-1/2"	.190
20567	24"	30"	23"	29"	27"	21"	13-1/2"	.190

HINGES



HINGE-10L and HINGE-10R
HINGE-11L and HINGE-11R
HINGE-12L and HINGE-12R

For use with all EXB & EXBLT series boxes. Set of two hinges installed on flanged enclosures for easier and safer installation and maintenance of internal components.

HINGES		
CATALOG NUMBER	SERIES USED	MOUNTING SIDE
HINGE-10L	Larger sizes	Left
HINGE-10R	EXB / EXBLT	Right
HINGE-11L	Mid Sizes EXB / EXBLT	Left
HINGE-11R		Right
HINGE-12L	Small	Left
HINGE-12R	EXB / EXBLT	Right



ROUND GLASS LENS COVERS / RECTANGULAR VIEWING WINDOWS



GL Series

GL ROUND GLASS LENS COVERS


For use with all EXB and EXBLTC series boxes.

Tempered soda lime glass mounted into a copper free sand cast aluminum threaded frame. Five viewing sizes, 2.75" through 7.75". Factory installation only.

Maintains all third party certifications of the EXBs and EXBLTCs.

GL RECOMMENDED MINIMUM SPACING – CENTERLINE TO CENTERLINE							VIEWING DIAMETER	OUTSIDE DIAMETER
GLASS LENS TYPE	GL-275	GL-300	GL-375	GL-537	GL-600	GL-775		
GL-275	7 (177.8)	7.5 (190.5)	7.75 (196.9)	8.75 (222.3)	9 (228.6)	10 (254.0)	2.75 (69.9)	4.63 (117.6)
GL-300	7.5 (190.5)	8 (203.2)	8.25 (209.6)	9.25 (235.0)	9.5 (241.3)	10.5 (266.7)	2.93 (74.4)	5.25 (133.4)
GL-375	7.75 (196.9)	8.25 (209.6)	8.5 (215.9)	9.5 (241.3)	9.75 (247.7)	10.75 (273.1)	3.75 (95.3)	6.25 (158.8)
GL-537	8.75 (222.3)	9.25 (235.0)	9.5 (241.3)	10.5 (266.7)	10.75 (273.1)	11.75 (298.5)	5.38 (136.7)	7.88 (200.2)
GL-600	9 (228.6)	9.5 (241.3)	9.75 (247.7)	10.75 (273.1)	11 (279.4)	12 (304.8)	6 (152.4)	8.88 (225.6)
GL-775	10 (254.0)	10.5 (266.7)	10.75 (273.1)	11.75 (298.5)	12 (304.8)	13 (330.2)	7.75 (196.9)	10.25 (260.4)

Note: For spacing less than minimum in table, (shown in inches) consult factory.




GLXR Series

GLXR RECTANGULAR VIEWING WINDOWS

For use with all EXB and EXBLTC series boxes. Tempered soda lime glass viewing lens. Additional viewing sizes available contact the factory for information.

Factory installation only.

Maintains all third party certifications of the EXBs and EXBLTCs.




GLXR RECTANGULAR LENS COVER ASSEMBLIES								
CATALOG NUMBER	VIEWING AREA		MINIMUM SPACE		OTHER DIMENSIONS			
	A	B	C	D	E	F	G	H
GLXR13	1 (25.4)	3 (76.2)	4.5 (114.3)	6.5 (165.1)	0.5 (12.7)	1.5 (38.1)	2.25 (57.2)	3.25 (82.6)
GLXR24	2 (50.8)	4 (101.6)	5.5 (139.7)	7.5 (190.5)	1 (25.4)	2 (50.8)	2.72 (69.1)	3.75 (95.3)
GLXR27	2 (50.8)	7 (177.8)	5.5 (139.7)	10.5 (266.7)	1 (25.4)	3.5 (88.9)	2.75 (69.9)	5.25 (133.4)
GLXR34	3.5 (88.9)	4 (101.6)	7 (177.8)	7.5 (190.5)	1.75 (44.5)	2 (50.8)	3.5 (88.9)	3.75 (95.3)
GLXR36	3 (76.2)	6 (152.4)	6.5 (165.1)	9.5 (241.3)	1.5 (38.1)	3 (76.2)	3.25 (82.6)	4.75 (120.7)
GLXR47	4 (101.6)	7 (177.8)	7.5 (190.5)	10.5 (266.7)	2 (50.8)	3.5 (88.9)	3.75 (95.3)	5.25 (133.4)
GLXR59	5 (127.0)	9 (228.6)	8.5 (215.9)	12.5 (317.5)	2.5 (63.5)	4.5 (114.3)	4.25 (108.0)	6.25 (158.8)
GLXR99	9 (228.6)	9 (228.6)	12.5 (317.5)	12.5 (317.5)	4.5 (114.3)	4.5 (114.3)	6.25 (158.8)	6.25 (158.8)

All dimension in. (mm)



GLASS LENS COVER



GLXR LAYOUT GUIDE										
CATALOG NUMBER	USEABLE COVER AREA		Z = MAXIMUM CENTER LINE OF COVER TO CENTERLINE OF GLASS LENS							
	X	Y	GLXR13	GLXR24	GLXR27	GLXR34	GLXR36	GLXR47	GLXR59	GLXR99
EXBLTC-684	5 (127)	7 (178)	1.25 (32)	N	N	N	N	N	N	N
EXBLTC-686	5 (127)	7 (178)	1.25 (32)	N	N	N	N	N	N	N
EXBLTC-6124	5 (127)	11 (279)	3.25 (83)	R	N	N	N	N	N	N
EXBLTC-6126	5 (127)	11 (279)	3.25 (83)	R	N	N	N	N	N	N
EXB/EXBLTC-886	7 (178)	7 (178)	1.25 (32)	0.75 (19)	N	N	N	N	N	N
EXB/EXBLTC-8104	7 (178)	9 (229)	2.25 (57)	1.75 (44)	N	1 (25)	N	N	N	N
EXB/EXBLTC-8106	7 (178)	9 (229)	2.25 (57)	1.75 (44)	N	1 (25)	N	N	N	N
EXB/EXBLTC-8126	7 (178)	11 (279)	3.25 (83)	2.75 (70)	N	2 (51)	N	N	N	N
EXB/EXBLTC-8128	7 (178)	11 (279)	3.25 (83)	2.75 (70)	N	2 (51)	N	N	N	N
EXBLTC-9116	8 (203)	10 (254)	2.75 (70)	2.25 (57)	N	1.5 (38)	N	N	N	N
EXB/EXBLTC-10106	9 (229)	9 (229)	2.25 (57)	1.75 (44)	N	1 (25)	N	N	N	N
EXB/EXBLTC-10108	9 (229)	9 (229)	2.25 (57)	1.75 (44)	N	1 (25)	N	N	N	N
EXB/EXBLTC-10146	9 (229)	13 (330)	4.25 (108)	3.75 (95)	R	3 (76)	R	R	R	N
EXB/EXBLTC-10148	9 (229)	13 (330)	4.25 (108)	3.75 (95)	R	3 (76)	R	R	R	N
EXB/EXBLTC-12126	10 (254)	10 (254)	2.75 (70)	2.25 (57)	2.25 (57)	1.5 (38)	1.75 (44)	1.25 (32)	N	N
EXB/EXBLTC-12128	10 (254)	10 (254)	2.75 (70)	2.25 (57)	2.25 (57)	1.5 (38)	1.75 (44)	1.25 (32)	N	N
EXB/EXBLTC-12186	10 (254)	16 (406)	5.75 (146)	5.25 (133)	5.25 (133)	4.5 (114)	4.75 (121)	4.25 (108)	N	N
EXB/EXBLTC-12188	10 (254)	16 (406)	5.75 (146)	5.25 (133)	5.25 (133)	4.5 (114)	4.75 (121)	4.25 (108)	N	N
EXB/EXBLTC-12246	10.3 (260)	22.3 (565)	8.88 (226)	8.38 (213)	8.38 (213)	7.63 (194)	7.88 (200)	7.38 (188)	R	N
EXB/EXBLTC-12248	10.3 (260)	22.3 (565)	8.88 (226)	8.38 (213)	8.38 (213)	7.63 (194)	7.88 (200)	7.38 (188)	R	N
EXB-122412	10.3 (260)	22.3 (565)	8.88 (226)	8.38 (213)	8.38 (213)	7.63 (194)	7.88 (200)	7.38 (188)	R	N
EXB-12368	11 (279)	35 (889)	15.25 (387)	14.75 (375)	14.75 (375)	14 (356)	14.25 (362)	13.75 (349)	N	N
EXB-123610	11 (279)	35 (889)	15.25 (387)	14.75 (375)	14.75 (375)	14 (356)	14.25 (362)	13.75 (349)	N	N
EXB-14146	13 (330)	13 (330)	4.25 (108)	3.75 (95)	3.75 (95)	3 (76)	3.25 (83)	2.75 (70)	2.25 (57)	*
EXB/EXBLTC-14148	13 (330)	13 (330)	4.25 (108)	3.75 (95)	3.75 (95)	3 (76)	3.25 (83)	2.75 (70)	2.25 (57)	*
EXB-16166	14 (356)	14 (356)	4.75 (121)	4.25 (108)	4.25 (108)	3.5 (89)	3.75 (95)	3.25 (83)	2.75 (70)	0.75 (19)
EXB/EXBLTC-16168	14 (356)	14 (356)	4.75 (121)	4.25 (108)	4.25 (108)	3.5 (89)	3.75 (95)	3.25 (83)	2.75 (70)	0.75 (19)
EXB/EXBLTC-16248	14 (356)	22 (559)	8.75 (222)	8.25 (210)	8.25 (210)	7.5 (190)	7.75 (197)	7.25 (184)	6.75 (172)	4.75 (121)
EXB-162410	14 (356)	22 (559)	8.75 (222)	8.25 (210)	8.25 (210)	7.5 (190)	7.75 (197)	7.25 (184)	6.75 (172)	4.75 (121)
EXB-18186	16 (406)	16 (406)	5.75 (146)	5.25 (133)	5.25 (133)	4.5 (114)	4.75 (121)	4.25 (108)	3.75 (95)	1.75 (44)
EXB-18188	16 (406)	16 (406)	5.75 (146)	5.25 (133)	5.25 (133)	4.5 (114)	4.75 (121)	4.25 (108)	3.75 (95)	1.75 (44)
EXB-18248	16 (406)	22 (559)	8.75 (222)	8.25 (210)	8.25 (210)	7.5 (190)	7.75 (197)	7.25 (184)	6.75 (172)	4.75 (121)
EXB-182410	16 (406)	22 (559)	8.75 (222)	8.25 (210)	8.25 (210)	7.5 (190)	7.75 (197)	7.25 (184)	6.75 (172)	4.75 (121)
EXB-18308	16 (406)	29 (737)	12.25 (311)	11.75 (298)	11.75 (298)	11 (279)	11.25 (286)	9.75 (248)	10.25 (260)	8.25 (210)
EXB-18368	16 (406)	34 (864)	14.75 (375)	14.25 (362)	14.25 (362)	13.5 (343)	13.75 (349)	13.25 (336)	12.75 (324)	10.75 (273)
EXB-183610	16 (406)	34 (864)	14.75 (375)	14.25 (362)	14.25 (362)	13.5 (343)	13.75 (349)	13.25 (336)	12.75 (324)	10.75 (273)
EXB-203611	18.9 (480)	34.9 (886)	15.18 (386)	14.68 (373)	14.68 (373)	13.94 (354)	14.19 (360)	13.68 (348)	13.19 (335)	11.19 (284)
EXB-24248	22 (559)	22 (559)	8.75 (222)	8.25 (210)	8.25 (210)	7.5 (190)	7.75 (197)	7.25 (184)	6.75 (172)	4.75 (121)
EXB-242410	22 (559)	22 (559)	8.75 (222)	8.25 (210)	8.25 (210)	7.5 (190)	7.75 (197)	7.25 (184)	6.75 (172)	4.75 (121)
EXB-24308	22 (559)	28 (711)	11.75 (298)	11.25 (286)	11.25 (286)	10.5 (267)	10.75 (273)	10.25 (260)	9.75 (248)	7.75 (197)
EXB-24368	22 (559)	34 (864)	14.75 (375)	14.25 (362)	14.25 (362)	13.5 (343)	13.75 (349)	13.25 (336)	12.75 (324)	10.75 (273)
EXB-243610	22 (559)	34 (864)	14.75 (375)	14.25 (362)	14.25 (362)	13.5 (343)	13.75 (349)	13.25 (336)	12.75 (324)	10.75 (273)

All dimension in. (mm)

Symbols: N = Enclosure will not accommodate this lens size
R = Rotate lens 90°, consult factory for layout assistance
* = Indicates center line