

Concourse LED

FINISH

● Brushed Nickel - 009

ALSO IN

Pendants

P300093-009-30

Architectural details and a full size canopy are key elements in Concourse LED vanity fixtures. A dual tone reflector frames the canopy to provide a mirror like effect. Etched opal glass is paired with Brushed Nickel and polished stainless accents in this versatile cylindrical fixture.

Etched Opal Glass

Full-Size Canopy



Architectural Details



P300093-009-30
mounted vertical



P300093-009-30



P300094-009-30

24" LINEAR LED BATH

P300093-009-30 Brushed Nickel
24" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
One 37w LED module, 3000K,
90CRI, 2191 delivered lumens.

36" LINEAR LED BATH

P300094-009-30 Brushed Nickel
36" W., 4-3/4" ht.
Extends 3-1/2". H/CTR 2-3/8".
One 53w LED module, 3000K,
90CRI, 2969 delivered lumens.

*All fixtures can be installed
horizontally or vertically.*

All fixtures:



Concourse LED

The Concourse LED linear pendant features minimalist design styling and a slim profile that appears to float along the ceiling. Offering energy efficiency and low maintenance benefits, Concourse LED is suitable for both home and commercial applications providing direct, ambient, beautifully diffused light. A Brushed Nickel frame completes the clean seamless look.

FINISH

● Brushed Nickel - 009

LED LINEAR PENDANT

P500002-009-30 Brushed Nickel

40" W., 5-1/4" D., 3" ht.

Overall ht. w/cord 113"; wire 9'.

39w integrated LED, 3000K, 90CRI,
2400 delivered lumens.

JAB



P500002-009-30