



# 21,000 lb. Series Guy Strains - Clevis / Clevis



See Catalog Page 12-17  
For Roller and Pin details



See Note For Roller Configurations

- C Dimension is 5/8" (16 mm) for 21,000 lbs. series
- D Dimension is 0.9" (23 mm) for 21,000 lbs. series
- E Dimension is 1.4" (36 mm) for 21,000 lbs. series

5/8" dia. Fiberglass rod.

**RUS Accepted.**

Castings are hot-dip galvanized ductile iron.

Catalog Number	Length A	Length B	Weight (Each)
<b>21,000 lbs. (9525 kg) Minimum Ultimate Strength*</b>			
GS21012CC1	12" (30.5 cm)	21" (53.3 cm)	4.4 lbs. (2.0 kg)
GS21018CC1	18" (45.7 cm)	27" (68.6 cm)	4.6 lbs. (2.1 kg)
GS21024CC1	24" (61.0 cm)	33" (83.8 cm)	4.8 lbs. (2.2 kg)
GS21030CC1	30" (76.2 cm)	39" (99.1 cm)	5.0 lbs. (2.3 kg)
GS21036CC1	36" (91.4 cm)	45" (114.3 cm)	5.1 lbs. (2.3 kg)
GS21042CC1	42" (106.7 cm)	51" (129.5 cm)	5.3 lbs. (2.4 kg)
GS21054CC1	54" (137.2 cm)	63" (160.0 cm)	5.7 lbs. (2.6 kg)
GS21060CC1	60" (152.4 cm)	69" (175.3 cm)	5.8 lbs. (2.6 kg)
GS21078CC1	78" (198.1 cm)	87" (221.0 cm)	6.4 lbs. (2.9 kg)
GS21096CC1	96" (243.8 cm)	105" (266.7 cm)	6.9 lbs. (3.1 kg)
GS21120CC1	120" (304.8 cm)	129" (327.7 cm)	7.6 lbs. (3.4 kg)
GS21144CC1	144" (365.8 cm)	153" (388.6 cm)	8.3 lbs. (3.7 kg)

GS—CC1 series has 1 Roller as detailed in drawing

For 2 Rollers, replace "CC1" in number with "CC2"

For no Rollers, replace "CC1" in number with "CC"

Add "SC" suffix to the end of the catalog number to denote Silicone Coated rod

"CC1L" or "CC2L" indicates large roller

\*Recommended maximum working load is 50% of minimum ultimate ratings listed.