

4" Low Voltage MR 16

Low Voltage Housings

For complete fixture, order housing with trim.



New Construction Air-Tight IC with G8 socket

P817-AT

Ceiling opening: 4-1/2"
Plaster frame: 15-3/4" x 9-3/4"
Recessed depth: 7-1/2"
Pryouts: 1/2" and 3/4"

P817-AT HOUSING FEATURES

- UL and CUL Listed for damp locations and through wiring.
- Meets Washington State Energy Code requirements.
- Can be installed in ceilings from 1/2" to 2-1/2" thick.
- Electronic transformer.
- Rated for 8 #12 90° conductors (4 in/4 out).



New Construction Non-IC with G8 socket

P816-TG

Ceiling opening: 4-1/2"
Plaster frame: 7-7/8" x 10-3/4"
Recessed depth: 5-1/2"
Pryouts: 1/2" and 3/4"

P816-TG HOUSING FEATURES

- UL and CUL Listed for damp locations and through wiring.
- Can be installed in ceilings from 1/2" to 2-1/2" thick.
- Magnetic transformer.
- Rated for 8 #12 90° conductors (4 in/4 out).



Remodel Non-IC with G8 socket

P818-TG

Ceiling opening: 4-1/4"
Recessed depth: 5-1/2"
Pryouts: 1/2"

P818-TG HOUSING FEATURES

- Integral flange on housing and exclusive locking bars permit quick mounting on ceilings from 1/2" to 1" thick.
- UL & CUL Listed for damp locations.
- Magnetic transformer.
- Rated for 60° supply wires in end-of-run applications.
- Rated for 4 #12 90° conductors (2 in/2 out).

IC Trims & Non-IC Trims

5" outside diameter. All trims have 360° positioning. Lamps tilt 30°.



STEP BAFFLE
P8037-28 White Baffle
IC & Non-IC:
12V 50w MR16



STEP BAFFLE
P8037-31 Black Baffle
IC & Non-IC:
12V 50w MR16



STEP BAFFLE
P8037-09 Brushed Nickel
IC & Non-IC:
12V 50w MR16



SLOTTED
P8039-28 White
IC: 12V 35w MR16
Non-IC: 12V 50w MR16



PINHOLE
P8036-28 White
IC: 12V 35w MR16
Non-IC: 12V 50w MR16



WALL WASHER
P8045-31 White w/Black Baffle
IC: 12V 35w MR16
Non-IC: 12V 50w MR16



EYEBALL
P8057-28 White
IC/Non-IC:
12V 50w MR16



EYEBALL
P8057-20 Antique Bronze
IC & Non-IC:
12V 50w MR16

Lamp wattages shown are maximum.
For accessories see page 795 for details.