

# Marine Products

## Internationally Rated Conventional-Styled Devices

### Twist-Lock® Devices, Ship-To-Shore Power System

| Description  | 16A 230V          | 32A 230V, 50 Cycle |
|--|-------------------|--------------------|
| Non-metallic, white, stylized, UV resistant shore power inlet. White Centrex® cover makes the inlet weatherproof when closed. Mounting holes are 2.38 in. (60.3) on centers and match most existing mounting patterns. Rear enclosure strain/relief cap is provided. <b>IP55 SUITABILITY.</b>  | <b>HBL316NM</b>   | <b>HBL332NM</b>    |
| Traditional, stainless steel shore power inlet has easy-to-wire terminations. Interior is transparent for quick and easy visual inspection. Interior is shielded from the elements by a gasketed, self-closing cover, watertight when cover is screwed in place. Mounting holes are 2.38 in. (60.3) on centers. Mounting screws and gasket included. Protective rear enclosure/strain relief also included. <b>IP56 SUITABILITY.</b> | <b>HBL316SSX</b>  | <b>HBL332SSX</b>   |
| Yellow locking connector replacement end for HBL316CS25 and HBL316CS. <b>IP20 SUITABILITY.</b>   | <b>HBL316CRCX</b> | <b>HBL332CRCX</b>  |
| White Seal-Tite® cover with threaded sealing ring for use with HBL316CRC and HBL332CRC connector bodies. <b>IP56 SUITABILITY.</b>  | <b>HBL60CM33W</b> | <b>HBL60CM33W</b>  |
| White Seal-Tite® cover with threaded sealing ring for use with HBL316CRC and HBL332CRC connector bodies. <b>IP56 SUITABILITY.</b>  | <b>HBL60CM33</b>  | <b>HBL60CM33</b>   |



HBL316NM  
HBL332NM



HBL316SSX  
HBL332SSX



HBL316CRCX  
HBL332CRCX



HBL60CM33  
HBL60CM33W



63A  
230V



HBL363SSX

### 63A 230V Ship-To-Shore Power Systems

| Description  | Catalog Number    |
|--|-------------------|
| Traditional, stainless steel shore power inlet, including higher-quality metal threads, heat-resistant thermoset interior and box lug terminals. <b>IP56 SUITABILITY.</b>        | <b>HBL363SSX</b>  |
| Nickel plated brass plug with heat-resistant thermoset interior and box lug terminals cord grip range is .44 – 1.14 in. (11.1 - 29.0). <b>IP55 SUITABILITY.</b>                  | <b>HBL363CRP</b>  |
| Nickel plated brass connector body with heat-resistant thermoset interior and box lug terminals. Cord grip range is .44 – 1.14 in. (11.1 - 29.0). <b>IP55 SUITABILITY.</b>       | <b>HBL363CRC</b>  |
| Single receptacle with heat-resistant thermoset base. <b>IP20 SUITABILITY.</b>   | <b>HBL363CRR</b>  |
| Yellow Seal-Tite® cover for connector bodies when used with 63A shore power inlets. Stainless steel threaded sealing ring makes connections watertight. <b>IP56 SUITABILITY.</b> | <b>HBL77CM15</b>  |
| Same as HBL77CM15 except white in color.   | <b>HBL77CM15W</b> |
| Yellow Seal-Tite® cover for 63A plugs. <b>IP55 SUITABILITY.</b>  | <b>HBL77CM16</b>  |
| Same as HBL77CM16 except white in color.   | <b>HBL77CM16W</b> |



HBL363CRP



HBL363CRR



HBL77CM15



HBL77CM16W



HBL363CRR

Centrex® is a registered trademark of LANXESS Corporation.