

Cable, Cord and Hose Reels

Features and Benefits

Workstation Kits

- Adjustable and customizable to fit virtually any bench and task
- Superior rigidity and durability
- Kits include one WS30 and one WS50 rail

Accessories

- Most components which make up kits are available separately
- Can be installed easily on fixed or portable workstation kits



Straight Tool Rail Kits

Description	Length ft (m)		Catalog Number
Straight rail bench top kit. Best mounted to butcher block tops. Straight rail	6.0 (1.8)	5.0 (1.5)	HBLWGB030560
table top kit. Table brackets predrilled to fit Equipto and Lyon steel tops.	6.0 (1.8)	5.0 (1.5)	HBLWKB030560



Power Bars

Description	Catalog Number
60 in. power bar with 60 in. mounting bar	HBLWBP505A



Manifold with Brackets

Description	Width ft (m)	# of Taps	Catalog Number
Mounts to vertical columns or top rails on workstations	5 (1.5)	5	HBLWMAN05C



Balancer Trolleys

Description	Catalog Number
Balancer trolley	HBLWS50BTL
Single roller balancer trolley	HBLWS50BTS




Adjustable Cable Saddle

Description	Load lbs (kg)		Catalog Number
	Min	Max	
Hangs from balancer cable above tool to provide strain relief for electrical cable or air hose. Available in three sizes. Includes safety clip.	0.3 (7)	0.59 (14)	HBLCSF1
	0.6 (15)	0.94 (23)	HBLCSF2
	0.95 (24)	1.25 (31)	HBLCSF3



"Shock Stop" Shock Absorber

Description	Catalog Number
Minimize cable damage often caused by overtensioning tool balancers. "Shock Stop" kit is easily installed. Can be used on ERGO-2 balancer. Kit includes spring, cable stops, all hardware.	HBLBGSH



Extension Cable

Description	Length ft (m)	Catalog Number
Nylon covered steel cable with safety clip. Extends the cable length of ERGO-1 and ERGO-2 Tool Balancers.	3 (0.9)	HBLOC03
	5 (1.5)	HBLOC05
	10 (3.0)	HBLOC10
	15 (4.6)	HBLOC15



Safety Cable/Chain

Description	For use with	Length ft (m)	Catalog Number
Strongly recommended, secondary steel cable or steel link chain. Prevents balancer from accidental fall. Balancers have extra holes for cable or chain.	HBLBD01-05	1 (0.3)	HBLSCBD1*
	HBLBG03-25	1 (0.3)	HBLSCBG1**
	HBLBG03L-25L	2 (0.6)	HBLSCBG2**
	HBLTQ1057-15	3 (0.9)	HBLSCBG3**
	HBLBH03-30	3 (0.9)	HBLSCBG3**
	HBLBH40-140	3 (0.9)	HBLSCBH3**

Dimensions in Inches (mm)