

## Non-Metallic Sloped Switched Disconnect Enclosures

Description	30 Amp	60 Amp	100 Amp
Disconnect switch.	<b>HBLDS30</b>	<b>HBLDS60</b>	<b>HBLDS100</b>
Disconnect switch with HBLAC1 auxiliary contact.	<b>HBLDS30AC</b>	<b>HBLDS60AC</b>	<b>HBLDS100AC</b>
Disconnect switch for use with variable frequency drives.	<b>HBLDS30VFD</b>	<b>HBLDS60VFD</b>	<b>HBLDS100VFD</b>
Disconnect switch without conduit knockout or conduit fitting.	<b>HBLDS30NK</b>	—	—

## Non-Metallic Sloped Switched Disconnects with Jog Switch

Description	30 Amp	60 Amp	100 Amp
Disconnect switch.	<b>HBLDS30J</b>	<b>HBLDS60J</b>	<b>HBLDS100J</b>
Disconnect switch with HBLAC1 auxiliary contact.	<b>HBLDS30ACJ</b>	—	—
Disconnect switch for use with variable frequency drives.	<b>HBLDS30VFDJ</b>	—	—
Disconnect switch with Jog switch and LEDs.	<b>HBLDS30PJ</b>	<b>HBLDS60PJ</b>	<b>HBLDS100PJ</b>

## Non-Metallic Sloped Switched Disconnect Switches with LEDs

Description	30 Amp	60 Amp	100 Amp
Non-Metallic disconnect switch with LEDs	<b>HBLDS30P</b>	<b>HBLDS60P</b>	<b>HBLDS100P</b>
Non-Metallic disconnect switch with HBLAC1 auxiliary contact	<b>HBLDS30PAC</b>	<b>HBLDS60PAC</b>	<b>HBLDS100PAC</b>

Note: \*Certified by NSF, International.

LED version for use with 3Ø Y and delta configurations.

## Top Feed Non-Metallic Sloped Switched Disconnect Enclosures\*

Description	30 Amp	60 Amp	100 Amp
Disconnect switch.	<b>HBLDS30T</b>	<b>HBLDS60T</b>	<b>HBLDS100T</b>
Disconnect switch with HBLAC1 auxiliary contact.	<b>HBLDS30TAC</b>	<b>HBLDS60TAC</b>	<b>HBLDS100TAC</b>
Disconnect switch for use with variable frequency drives.	<b>HBLDS30TVFD</b>	<b>HBLDS60TVFD</b>	<b>HBLDS100TVFD</b>
Disconnect switch without conduit knockout or conduit fitting.	<b>HBLDS30TNK</b>	—	—

## Top Feed Non-Metallic Sloped Switched Disconnects with Jog Switch\*

Description	30 Amp	60 Amp	100 Amp
Disconnect switch.	<b>HBLDS30TJ</b>	<b>HBLDS60TJ</b>	<b>HBLDS100TJ</b>
Disconnect switch with HBLAC1 auxiliary contact.	<b>HBLDS30TACJ</b>	—	—
Disconnect switch for use with variable frequency drives.	<b>HBLDS30TVFDJ</b>	—	—
Disconnect switch with Jog switch and LEDs.	<b>HBLDS30TPJ</b>	<b>HBLDS60TPJ</b>	<b>HBLDS100TPJ</b>

## Top Feed Non-Metallic Sloped Switched Disconnect Switches with LEDs\*

Description	30 Amp	60 Amp	100 Amp
Non-Metallic disconnect switch with LEDs	<b>HBLDS30TP</b>	<b>HBLDS60TP</b>	<b>HBLDS100TP</b>
Non-Metallic disconnect switch with HBLAC1 auxiliary contact	<b>HBLDS30TPAC</b>	<b>HBLDS60TPAC</b>	<b>HBLDS100TPAC</b>

Note: \*Top feed versions include a single flat and drill point for top feed applications.

LED version for use with 3Ø Y and delta configurations.

## Accessories:

¾" NEMA Type 3,3R, 4X and 12 zinc Conduit Hub	<b>HUB75</b>
1 ¼" NEMA Type 3,3R, 4X and 12 zinc Conduit Hub	<b>HUB125A</b>
¾" Grounding Plate for side feed applications	<b>HBLDS34GP*</b>
Additional Pole for up to 30A applications	<b>HBL4P</b>

\*May require an additional ground block.

## Replacement Accessories

	Switch	Mounting Feet	Ground Block	Neutral Block
For 30A switches	<b>HBLDS3RS</b>	<b>HBLRFT1</b>	<b>HBL30RGB</b>	<b>HBL30RNB</b>
For 60A switches	<b>HBLDS60100RS</b>	<b>HBLRFT2</b>	<b>HBL60100RGB</b>	<b>HBL60RNB</b>
For 100A switches	<b>HBLDS60100RS</b>	<b>HBLRFT2</b>	<b>HBL60100RGB</b>	<b>HBL100RNB</b>
For <b>HBLDS33ACNK</b>	<b>HBLDS33ACRS</b>	<b>HBLRFT1</b>	<b>HBL30RGB</b>	<b>HBL30RNB</b>



HBLDS30



HBLDS30VFD



HBLDS3RS



HBLRFT1



HBLAC1



HBLAC2