




## LINKOSITY® Control Integration Components - Cables and Receptacles

Device Type	Ratings	Wires	Conductor Colors**	Length (FT)
 <b>PH</b> = Double Ended Cable with Male/Female Straight <b>PM</b> = Male Single Ended Straight <b>PN</b> = Male Single Ended 90° <b>PF</b> = Female Single Ended Straight <b>PG</b> = Female Single Ended 90° <b>PQ</b> = Double Ended Cable with Female 90° <b>PR</b> = Double Ended Cable with Male 90° <b>PS</b> = Double Ended Cable with (2) 90° Connectors   <b>RF</b> = Female Receptacle*   <b>RM</b> = Male Receptacle (Inlet)*	<b>03</b> = 3A - 2W, 4W up to 300V	<b>02</b> <b>04</b>	<b>PA</b> = Green/Yellow Black (all others)	<b>001</b> = 1' <b>005</b> = 5' <b>010</b> = 10' <b>015</b> = 15' <b>020</b> = 20' <b>025</b> = 25' <b>030</b> = 30' <b>035</b> = 35' <b>040</b> = 40' <b>045</b> = 45' <b>050</b> = 50'
	<b>R3</b> = 3A - 2W, 3W, 4W up to 300V	<b>02</b> <b>03</b> <b>04</b>		
	<b>10</b> = 10A - 2W, 3W, 4W, 5W 10A - 6W, 7W, 8W, 9W 7A - 10W, 12W up to 600V	<b>02</b> <b>03</b> <b>04</b> <b>05</b> <b>06</b> <b>07</b> <b>08</b> <b>09</b> <b>10</b> <b>12</b>	<b>PE</b> = All Blue***	

**Example: PH**

**10**

**06**

**PB**




**005**

Note: \*1/2" NPT rear thread.

\*\*Other color codes available upon request.

\*\*\*Two wire only.

## Configurations (Male face view shown, female view is opposite)

<b>03</b>		Typically used for inputs in DC control circuits
<b>R3*</b>		Typically used for outputs in DC control circuits
<b>10</b>		

Note: \*Reverse key.

## Splitters/Tees

Description	Catalog Number
LINKOSITY® M/F/F Splitter, 3A/4W	<b>TX0304000304T00</b>
LINKOSITY® M/F/F Tee, 10A, 2 Pole	<b>TX1002001002T00</b>
LINKOSITY® M/F/F Tee, 10A, 3 Pole	<b>TX1003001003T00</b>
LINKOSITY® M/F/F Tee, 10A, 4 Pole	<b>TX1004001004T00</b>
LINKOSITY® M/F/F Tee, 10A, 5 Pole	<b>TX1005001005T00</b>
LINKOSITY® M/F/F Tee, 10A, 6 Pole	<b>TX1006001006T00</b>



**TX1004001004T00**

## Closure Caps

Description	For use with	
	Female Receptacle	Male Inlet
3A Closure Cap	<b>CCM1C</b>	<b>CCF1C</b>
10A Closure Cap, 2, 3, 4, 4, 5 and 6 Pole	<b>CCMAC</b>	<b>CCFAC</b>
10A Closure Cap, 7 and 8 Pole	<b>CCMBC</b>	<b>CCFBC</b>
10A Closure Cap, 9, 10, 12 Pole	<b>CCMCC</b>	<b>CCFCC</b>



**CCFAC**